


SKF Ecowear 1000

Polyethylene – ultra high molecular weight

DIN/ISO: PE-UHMW ASTM: UHMW-PE

Property	Unit	Value	Standard
Standard color	–	Nature	
Hardness	Shore D	61	ISO 868
Density	g/cm ³	0,93	ISO 1183
Yield stress	MPa	20	ISO 527-1
Elongation at break	%	≥350	ISO 527-1
Modulus of elasticity in tension	MPa	600	ISO 527-1
Coefficient of linear expansion 20–80 °C	K ⁻¹	1,7×10 ⁻⁴	ASTM E831
Minimum service temperature	°C	–200	–
Maximum service temperature (permanent)	°C	+90	–
Maximum service temperature (short time)	°C	+125	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards.

© SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12486/1 EN · October 2014

