

Relubricatable bearings with square bore
Type 1



Relubricatable bearings with round bore
Type 2

Designation	Type	Bore/shaft diameter	Bore type	Outer diameter	Seal type
–		mm	–	mm	–
Gang disc – Relburicatable bearings					
GW208PP17 [1]	1	29,972	Square	85,738	3-lip LS
GW208PPB5	1	29,972	Square	80,000	3-lip LS
GW208PPB8	1	29,972	Square	80,000	3-lip LS
GW210PPB4	1	29,413	Square	90,000	3-lip LS
GW211PP17 [1]	1	38,887	Square	100,000	3-lip LS
GW211PP3-GX [1]	1	38,887	Square	100,000	3-lip LS
GW211PPB3	1	38,887	Square	100,000	3-lip LS
GW212PP50-GX [1]	1	45,466	Square	110,000	3-lip LS
GW214PPB4-GX	1	52,200	Square	125,000	3-lip LS
GW216PP2-GX [1]	1	58,738	Square	140,000	3-lip LS
GW315PPB11-OX	2	70,000	Round	160,000	3-lip LS
GW214PPB6-GX	2	68,278	Round	125,000	3-lip LS
GW214PPB3-OX	2	68,278	Round	125,000	3-lip LS
GW214PPB2-GX	2	70,000	Round	125,000	3-lip LS
GW214PP2-GX [1]	2	70,000	Round	125,000	3-lip LS
GW211PPB9-GX	2	55,753	Round	100,000	3-lip LS
GW211PPB2	2	55,575	Round	100,000	3-lip LS
GW211PPB14	2	51,181	Round	100,000	3-lip LS
GW211PPB13	2	45,339	Round	100,000	3-lip LS
GW211PP53 [1]	2	50,000	Round	100,000	3-lip LS
GW211PP25-GX [1]	2	45,339	Round	100,000	3-lip LS
GW209PPB4-GX	2	38,989	Round	85,000	3-lip LS
GW209PPB22	2	45,000	Round	85,000	3-lip LS
GW209PPB22-BR209RH [2]	2	38,989	Round	88,700	3-lip LS
GW211PPB21-BR211RH [2]	2	45,339	Round	101,092	3-lip LS

[1] Cylindrical outside diameter
[2] Rubber grommets over the outer diameter



Non-relubricatable bearings with square bore
Type 3



Non-relubricatable bearings with round bore
Type 4

Designation	Type	Bore/shaft diameter	Bore type	Outer diameter	Seal type
–		mm	–	mm	–
Gang disc – Non-relubricatable bearings					
W208PP5 [1]	3	29,972	Square	80,0	3-lip LS
W208PP6 [1]	3	26,162	Square	80,0	3-lip LS
W208PP8 [1]	3	29,972	Square	80,0	3-lip LS
W208PPB5	3	29,972	Square	80,0	3-lip LS
W208PPB6	3	26,162	Square	80,0	3-lip LS
W210PP4 [1]	3	29,413	Square	90,0	3-lip LS
W211PP3 [1]	3	38,887	Square	100,0	3-lip LS
W211PP5 [1]	3	38,887	Square	101,6	3-lip LS
W211PPB3	3	38,887	Square	100,0	3-lip LS
W211PPB4	4	55,575	Round	100,0	3-lip LS
W211PPB2	4	55,575	Round	100,0	3-lip LS
W211PP54 [1]	4	52,413	Round	100,0	3-lip LS
W211PP2 [1]	4	55,575	Round	100,0	3-lip LS
W210PPB5	4	45,339	Round	90,0	3-lip LS
W210PPB2	4	49,225	Round	90,0	3-lip LS
W210PP2 [1]	4	49,225	Round	90,0	3-lip LS
W209PPB2	4	45,000	Round	85,0	3-lip LS
W209PPB4	4	38,989	Round	85,0	3-lip LS
W208PPB7	4	30,172	Round	80,0	3-lip LS
W208PPB23	4	38,113	Round	80,0	3-lip LS
W208PP10 [1]	4	38,113	Round	80,0	3-lip LS
W208KPP53	4	38,100	Round	80,0	3-lip LS

[1] Cylindrical outside diameter