



SKF Competitive Interchange Poster for Heavy Duty

Wheel Seals													
Description	Application	Scotseal Classic	Scotseal PRO	Scotseal X-Treme	National Red	National Gold	STEMCO Grit Guard	STEMCO Guardian	STEMCO Voyager	STEMCO Discover	STEMCO Discover XR	REVHD REV1	REVHD REV MAX
Oil Bath Seal - Nitrile	Tractor, Steer Axle, 4,700 lb, 7,500 lb, 8,000 lb	28758	—	28759XT	370150A	—	—	308-0866	383-0166	—	—	—	—
Oil Bath Seal - Nitrile	Tractor, FF Steer Axle, 12,000 lb.	35066	35058PRO	35058XT	370001A	380001A	—	308-0836	383-0136	383-0236	383-0436	R1-S01	RM-S01
Oil Bath Seal - Nitrile	Tractor, FL Steer Axle, 16,000 lb, 20,000 lb	43764	43761PRO	43761XT	370048A	380048A	—	308-0864	383-0164	383-0264	383-0464	—	RM-S05
Oil Bath Seal - Nitrile	Tractor, Drive Axle, 34,000 lb.	38780	38776PRO	38776XT	370023A	380023A	392-9099	309-0912	393-0112	393-0212	—	—	RM-D08
Oil Bath Seal - Nitrile	Tractor, Drive Axle, 34,000 lb, 36,000 lb, 38,000 lb	45099	—	45093XT	370022A	380022A	392-9094	309-0903	393-0103	393-0203	—	—	RM-D07
Oil Bath Seal - Nitrile	Tractor, Drive Axle, 38,000 lb, 46,000 lb	47697	47691PRO	47691XT	370003A	380003A	392-9131	309-0973	393-0173	393-0273	393-0473	R1-D02	RM-D02
Oil Bath Seal - Nitrile	Tractor, Drive Axle, 40,000 lb, 44,000 lb	42672	42673PRO	42673XT	370031A	380031A	392-9112	309-0904	393-0104	393-0204	—	—	RM-D06
Oil Bath Seal - Nitrile	Trailer Axle, 19,000 lb	40136	40129PRO	40129XT	370036A	380036A	372-7098	307-0713	373-0113	373-0213	—	—	RM-T09
Oil Bath Seal - Nitrile	Trailer Axle, TN, 22,500 lb	46305	46300PRO	46300XT	370025A	380025A	372-7097	307-0743	373-0143	373-0243	373-0243	R1-T03	RM-T03
Oil Bath Seal - Nitrile	Trailer Axle, TP, Pro-Par	42623	42627PRO	42627XT	370065A	380065A	372-7099	307-0723	373-0123	373-0223	373-0223	R1-T04	RM-T04

Hubcaps															
Description	Axle	Lubrication Type	Bolt Holes	Hole Size	Bolt Circle Diameter (inches)	SKF Composite w/Side Fill	SKF Aluminum w/Side Fill	SKF Steel	SKF Gasket	SKF Center-fill Plug	STEMCO No Side Fill	STEMCO w/Side Fill	Dual Dynamics	National Aluminum	RevHD
Hubcap	Trailer, Pro-Par	Oil	Threaded	Threaded	6.250 x 8 O.D	1282	—	—	454051-4	454301-4	340-4975	—	—	340-975BK	—
Hubcap	Trailer, Pro-Par	Grease	Threaded	Threaded	6.250 x 8 O.D	1284	—	—	454051-4	—	340-4975	—	—	340-975BK	—
Hubcap, with hubodometer mount	Trailer, Pro-Par	Oil	Threaded	Threaded	6.250 x 8 O.D	1282H	—	—	454051-4	—	340-4975	—	—	340-975BK	—
Hubcap, with hubodometer mount	Trailer, TN	Oil	6	0.349	5.500-5.562	1600	—	—	453795-8	—	347-4009	—	253-H	347-009	—
Hubcap	Steer	Oil	4	0.349	3.625	1608	—	—	453868-8	453879-4	340-4065	343-4065	—	—	—
Hubcap	Steer	Oil	6	0.349	4.500	1612	1812	1711	453869-8	454301-4	340-4024	343-4024	302-P	343-024	RHO-S01
Hubcap	Steer	Grease	6	0.349	4.500	1326	—	—	453869-8	—	342-4024	—	301-G	—	—
Hubcap, no window	Trailer, TN	Grease	6	0.349	5.500-5.562	1343	1841	1743	453795-8	—	349-4009	—	202-G	342-009	RHG-T03
Hubcap, with window	Trailer, TN	Grease	6	0.349	5.500-5.562	1343W	—	—	453795-8	—	—	—	—	—	—
Hubcap	Steer	Oil	6	0.349	5.500-5.562	1613	—	1703	453795-8	453879-4	340-4249	343-4249	—	343-249	—
Hubcap	Trailer	Oil	6	0.349	5.125-5.250	1623	—	1723	453909-8	454301-4	340-4066	343-4066	—	—	—
Hubcap	Steer	Oil	3	0.416	5.250	1627	—	1727	—	454301-4	340-4002	343-4002	—	—	—
Hubcap	Trailer	Oil	6	0.349	5.500-5.562	1630	—	—	453795-8	454301-4	340-4014	343-4014	—	—	—
Hubcap	Trailer	Oil	5	0.349	5.500	1642	—	1742	453818-4	454301-4	340-4013	343-4013	282-P	343-013	—
Hubcap	Trailer, TN	Oil	6	0.349	5.500-5.562	1643	1843	1743	453795-8	454301-4	340-4009	343-4009	203-P	343-249	RHO-T03
Hubcap	Trailer	Oil	6	0.349	5.125-5.250	1665	—	1765	453909-8	454301-4	340-4042	343-4042	—	343-042	—
Hubcap	Steer	Oil	6	0.349	5.875	1669	—	—	453918-8	453813-4	340-4025	343-4025	—	343-036	—
Hubcap	Steer	Oil	6	0.286	6.625	1670	—	1770	453825-8	454301-4	340-4034	343-4034	—	—	—
Hubcap	Trailer	Oil	4	0.349	5.000	1681	—	—	453915-8	454301-4	340-4029	343-4029	—	—	—
Hubcap	Steer	Oil	6	0.349	5.500-5.562	1691	—	1790	453795-8	453879-4	340-4098	343-4098	—	343-095	—
Hubcap	Trailer, TP	Oil	6	0.349	6.750	1696	1869	1796	450799-8	454301-4	340-4195	343-4195	257-P	343-195	RHO-T04
Hubcap, no window	Trailer, TP	Grease	6	0.349	6.751	1399	1899	—	450799-8	—	—	—	255-G	342-195	RHG-T04
Hubcap, with window	Trailer, TP	Grease	6	0.349	6.752	1399W	—	—	450799-8	—	—	—	—	—	—
Hubcap	Trailer	Oil	6	0.416	6.000	1698	—	1798	453906-8	454301-4	—	—	—	—	—
Hubcap, with PSI air system	Trailer, TN, PSI	Oil	6	0.349	5.500-5.562	1943	1846	—	453795-8	—	—	343-4370	—	—	RHO-T03PSI
Hubcap, with PSI air system	Trailer, TN, PSI	Grease	6	0.349	5.500-5.562	1443	1845	—	453795-8	—	340-4370	343-4370	—	—	RHO-T03PSI
Hubcap, with PSI air system	Trailer, TP, PSI	Oil	6	0.349	5.500-5.562	1996	1896	—	453795-8	—	—	343-4372	—	—	RHO-T04PSI
Hubcap, with PSI air system	Trailer, TP, PSI	Grease	6	0.349	6.750	1499	1898	—	453795-8	—	—	343-4372	—	—	RHG-T04PSI

Lug Nuts						
Description	SKF	Securex	Tremac Sloan	Size	Outside Diameter	Pieces per package
Two-piece lug nut	MV33333-10	39702	MF110343	M22 X 1.5 (high profile)	33mm hex	10 ct. box
Two-piece lug nut	MV33333G-100	39702	MF110344	M22 X 1.5 (high profile)	33mm hex	100 ct. box
Two-piece lug nut	MV33333B-300	39702	MF110345	M22 X 1.5 (high profile)	33mm hex	300 ct. box
Two-piece lug nut	MV22273-10	39874	MF111026	M22 X 1.5 (low profile)	33mm hex	10 ct. box
Two-piece lug nut	MV22273G-130	39874	MF111026	M22 X 1.5 (low profile)	33mm hex	130 ct. box
Two-piece lug nut	MV88838-10	39514	—	M22 X 1.5	38mm hex	10 ct. box
Two-piece lug nut	MV88838-80	39514	—	M22 X 1.5	38mm hex	80 ct. box

Preset Spacer Kits					
Description	SKF Kit	CR Seal	CR Gasket	Conmet Kit	Alliance Kit
FF steer	FFXSK1	35058XT	453869-8	10081518	ABP 10081518
FL steer	FLXSK1	43761XT	453795-8	10081519	ABP 10081519
R Drive	RDXSK1	47691XT	450802-8	10081520	ABP 10081520
TN Trailer	TNXSK1	46300XT	453795-8	10081521	ABP 10081521
TP Trailer	TPXSK1	42627XT	450799-8	10081522	ABP 10081522

Pinion Seals										
Description	Axle	Position	Bore	Yolk Shaft	SKF/CR Unitized	SKF/CR Non-Unitized	SKF/CR Grease	Meritor	National	STEMCO
Pinion Seal	14X/16X 18X/38X	Forward-Rear Unit Input	4.249	3.250	32500	32410	32397	A1205R2592/A11205X2728	100494	429-0007
Pinion Seal	14X/16X	Forward-Rear Unit Output	3.751	3.000	30008	30007	29867	A1205P2590/A11205Y2729	100495	429-0005
Pinion Seal	14X	Rear-Rear Unit Input	4.936	3.000	30009	30153	30145	A1205N2588/A11205Z2730	100263	429-0010
Pinion Seal	16X/18X	Rear-Rear Unit Input	5.501	3.250	32503	33254	—	A1205Q2591/A11205A2731	100557	429-0011



Scan the QR code or visit **vehicleaftermarket.skf.com** to learn about the latest SKF innovative products and access the complete product range.

Follow SKF Aftermarket on social media for helpful technical videos and assembly instructions



SKFAutomotive



skfautomotive



SKFAftermarket

Contact SKF Customer Support to help resolve your automotive problems and aswer your questions:
VAsupport@skf.com



Loaded Trailer Hubs				
Manufacturer	Part Number	Axle	Bolt Standout	SKF
Conmet	105775	TN- Tapered	Steel Wheels	TNHUB2
Conmet	105776	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	105777	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	106227	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	106228	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	106229	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	106275	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	106276	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	106277	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	106396	TN- Tapered	Steel Wheels	TNHUB2
Conmet	106397	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	106398	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10001196	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10001197	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10001198	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10001199	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10001200	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10001201	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10001202	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10001203	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10001204	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10005478	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10005479	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10005480	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10012141	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10012142	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10012143	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10012144	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10026182	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10026183	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10026184	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10026185	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10026197	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10026198	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10026199	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10082224	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10082225	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10082228	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10082229	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10082230	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10082231	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10082249	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10082250	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10082251	TN- Tapered	Steel Wheels	TNHUB2
Conmet	10082252	TN- Tapered	Aluminum Wheels	TNHUB1
Conmet	10082253	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10082254	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Conmet	10082255	TP - Parallel/Straight	Steel Wheels	TPHUB2
Conmet	10082256	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Gunite	5720-2	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Gunite	5720-3	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Gunite	5840-1	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT789K	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT789K2	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT789RB	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT789RC	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT791K	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT793K	TP - Parallel/Straight	Steel Wheels	TPHUB2
Gunite	HT793K2	TP - Parallel/Straight	Steel Wheels	TPHUB2
Gunite	HT793RH	TP - Parallel/Straight	Steel Wheels	TPHUB2
Gunite	HT794J	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT794K	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT794K1	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT794K2	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT794K4	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT794K5	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT794RC	TN- Tapered	Steel Wheels	TNHUB2
Gunite	HT794RD	TN- Tapered	Aluminum Wheels	TNHUB1
Gunite	HT799J	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Gunite	HT799K	TP - Parallel/Straight	Steel Wheels	TPHUB2

Loaded Trailer Hubs				
Manufacturer	Part Number	Axle	Bolt Standout	SKF
Gunite	HT799K4	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Gunite	HT799RC	TP - Parallel/Straight	Steel Wheels	TPHUB2
Gunite	HT799RD	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
KIC	001-01025	TN- Tapered	Steel Wheels	TNHUB2
KIC	001-01025-L	TN- Tapered	Aluminum Wheels	TNHUB1
KIC	001-01025-LT	TN- Tapered	Aluminum Wheels	TNHUB1
KIC	001-01025T	TN- Tapered	Steel Wheels	TNHUB2
KIC	004-00130	TP - Parallel/Straight	Steel Wheels	TPHUB2
KIC	004-00130L	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
KIC	004-00130LT	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
KIC	004-00130T	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-15968-002	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-15968-007	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-15968-009	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Meritor(Dayton)	04-16040-008PST	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-16040-009PST	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Meritor(Dayton)	04-16040-010PST	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-16040-010PST	TP - Parallel/Straight	Steel Wheels	TPHUB2
Meritor(Dayton)	04-16040-011PST	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Meritor(Dayton)	04-16040-011PST	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Meritor(Dayton)	04-16048-001PST	TN- Tapered	Steel Wheels	TNHUB2
Meritor(Dayton)	04-16048-002PST	TN- Tapered	Steel Wheels	TNHUB2
Meritor(Dayton)	04-16048-002PST	TN- Tapered	Steel Wheels	TNHUB2
Meritor(Dayton)	04-16048-003PST	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	04-16048-004PST	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	04-16048-004PST	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	14-15984-1068	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	14-15984-1072	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	14-15984-1078	TN- Tapered	Steel Wheels	TNHUB2
Meritor(Dayton)	14-15984-1081	TN- Tapered	Aluminum Wheels	TNHUB1
Meritor(Dayton)	14-15984-1085	TN- Tapered	Steel Wheels	TNHUB2
Meritor(Dayton)	14-15984-1433	TN- Tapered	Aluminum Wheels	TNHUB1
Motor Wheel	410050	TP - Parallel/Straight	Steel Wheels	TPHUB2
Motor Wheel	410051	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Motor Wheel	410052	TN- Tapered	Steel Wheels	TNHUB2
Motor Wheel	410053	TN- Tapered	Aluminum Wheels	TNHUB1
Motor Wheel	413007	TP - Parallel/Straight	Steel Wheels	TPHUB2
Motor Wheel	450050	TP - Parallel/Straight	Steel Wheels	TPHUB2
Motor Wheel	450051	TP - Parallel/Straight	Aluminum Wheels	TPHUB1
Motor Wheel	450052	TN- Tapered	Aluminum Wheels	TNHUB1
Motor Wheel	453007	TP - Parallel/Straight	Steel Wheels	TPHUB2
Webb	20231--3T	TN- Tapered	Steel Wheels	TNHUB2
Webb	20231--5T	TN- Tapered	Aluminum Wheels	TNHUB1
Webb	23431--3T	TP - Parallel/Straight	Steel Wheels	TPHUB2
Webb	23431--5T	TP - Parallel/Straight	Aluminum Wheels	TPHUB1

Bearings							
SKF	TRP	Fleetrite	National	STEMCO	NTN X-Ref	Timken MileMate®	Alliance
SET401	BWSET401	FLTSET401	HD206	STMSET401	SET401	SET401	ABP SBN SET401
SET403	BWSET403	FLTSET403	HD203	STMSET403	SET403	SET403	ABP SBN SET403
SET404	BWSET404	—	HD204	—	SET404	SET404	—
SET405	BWSET405	—	HD207	—	SET405	SET405	ABP SBN SET405
SET406	BWSET406	FLTSET406	HD205	STMSET406	SET406	SET406	ABP SBN SET406
SET408	—	FLTSET408	HD210	—	SET408	SET408	ABP SBN SET408
SET411	BWSET411	—	HD209	—	SET411	SET411	ABP SBN SET411
SET412	—	—	HD202	—	SET412	SET412	—
SET413	BWSET413	FLTSET413	HD200	STMSET413	SET413	SET413	ABP SBN SET413
SET414	BWSET414	FLTSET414	HD201	STMSET414	SET414	SET414	ABP SBN SET414
SET415	BWSET415	FLTSET415	HD208	STMSET415	SET415	SET415	ABP SBN SET415
SET421	—	—	HD214	—	SET421	SET421	—
SET423	BWSET423	—	HD218	STMSET423	SET423	SET423	ABP SBN SET423
SET424	BWSET424	—	HD217	STMSET424	SET424	SET424	ABP SBN SET424
SET426	—	—	HD215	—	SET426	SET426	—
SET427	—	—	—	—	SET427	SET427	ABP SBN SET427
SET428	—	—	—	—	SET428	SET428	ABP SBN SET428
SET429	—	—	—	—	SET429	SET429	ABP SBN SET429
SET430	—	—	—	—	SET430	SET430	ABP SBN SET430
SET431	—	—	—	—	SET431	SET431	ABP SBN SET431
SET432	—	—	—	—	SET432	SET432	ABP SBN SET432



Scan the QR code or visit **vehicleaftermarket.skf.com** to learn about the latest SKF innovative products and access the complete product range.

Follow SKF Aftermarket on social media for helpful technical videos and assembly instructions



SKFAutomotive



SKFAftermarket



skfautomotive

Contact SKF Customer Support to help resolve your automotive problems and aswer your questions:
VAsupport@skf.com