

# SKF Xtra Power Lawn and Garden belts

**SKF**<sup>®</sup>



® SKF is a registered trademark of the SKF Group.

Dacromet and Dacrotized are registered trademarks of Metal Coatings International Inc. Corporation.

© SKF Group 2015

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

**PUB PT/P1 15911/1 EN** • March 2016

# Contents



**1** Introduction ..... 9



**2** SKF XP Lawn and Garden v-belts ..... 10



**3** OEM cross ref ..... 12



**4** Product fulfillment..... 34

# SKF – the knowledge engineering company

From one simple but inspired solution to a misalignment problem in a textile mill in Sweden, and fifteen employees in 1907, SKF has grown to become a global industrial knowledge leader.



Over the years, we have built on our expertise in bearings, extending it to seals, mechanics, services and lubrication systems. Our knowledge network includes 46 000 employees, 15 000 distributor partners, offices in more than 130 countries, and a growing number of SKF Solution Factory sites around the world.

## Research and development

We have hands-on experience in over forty industries based on our employees' knowledge of real life conditions. In addition, our world-leading experts and university partners pioneer advanced theoretical research and development in areas including tribology, condition monitoring, asset management and bearing life theory. Our ongoing commitment to research and development helps us keep our customers at the forefront of their industries.



## Meeting the toughest challenges

Our network of knowledge and experience, along with our understanding of how our core technologies can be combined, helps us create innovative solutions that meet the toughest of challenges. We work closely with our customers throughout the asset life cycle, helping them to profitably and responsibly grow their businesses.

## Working for a sustainable future

Since 2005, SKF has worked to reduce the negative environmental impact from our operations and those of our suppliers. Our continuing technology development resulted in the introduction of the SKF BeyondZero portfolio of products and services which improve efficiency and reduce energy losses, as well as enable new technologies harnessing wind, solar and ocean power. This combined approach helps reduce the environmental impact both in our operations and our customers' operations.

*SKF Solution Factory makes SKF knowledge and manufacturing expertise available locally to provide unique solutions and services to our customers.*




*Working with SKF IT and logistics systems and application experts, SKF Authorized Distributors deliver a valuable mix of product and application knowledge to customers worldwide.*



## Our knowledge – your success

*SKF Life Cycle Management is how we combine our technology platforms and advanced services, and apply them at each stage of the asset life cycle, to help our customers to be more successful, sustainable and profitable.*



### Working closely with you

Our objective is to help our customers improve productivity, minimize maintenance, achieve higher energy and resource efficiency, and optimize designs for long service life and reliability.



### Bearings

*SKF is the world leader in the design, development and manufacture of high performance rolling bearings, plain bearings, bearing units and housings.*

### Innovative solutions

Whether the application is linear or rotary or a combination, SKF engineers can work with you at each stage of the asset life cycle to improve machine performance by looking at the entire application. This approach doesn't just focus on individual components like bearings or seals. It looks at the whole application to see how each component interacts with each other.



### Machinery maintenance

*Condition monitoring technologies and maintenance services from SKF can help minimize unplanned downtime, improve operational efficiency and reduce maintenance costs.*



### Sealing solutions

*SKF offers standard seals and custom engineered sealing solutions to increase uptime, improve machine reliability, reduce friction and power losses, and extend lubricant life.*

### Design optimization and verification

SKF can work with you to optimize current or new designs with proprietary 3-D modelling software that can also be used as a virtual test rig to confirm the integrity of the design.



### Mechatronics

*SKF fly-by-wire systems for aircraft and drive-by-wire systems for off-road, agricultural and forklift applications replace heavy, grease or oil consuming mechanical and hydraulic systems.*



### Lubrication solutions

*From specialized lubricants to state-of-the-art lubrication systems and lubrication management services, lubrication solutions from SKF can help to reduce lubrication related downtime and lubricant consumption.*



### Actuation and motion control

*With a wide assortment of products – from actuators and ball screws to profile rail guides – SKF can work with you to solve your most pressing linear system challenges.*



# Foreword

Power transmission products play an important role in overall bearing performance and are the vital link between moving parts in equipment. By creating its own range of power transmission products, SKF can offer products that are well-matched and give engineers a wide design choice according to performance and cost considerations.

Bringing power transmission products under a single brand offers significant user benefits apart from the confidence that comes from using a well-known brand. SKF can provide a convenient single supply source for products and services with a large number of items in stock. This, in turn, offers the chance to simplify logistics to end users and reduce administrative work.

As bearings and other power transmission components work together in products used in many industries, many bearing problems and failures can be identified through the knowledge of power transmission. Examples of those industries are food and beverage, oil and gas, pulp and paper, textile, metalworking, packaging, mining, mineral processing and cement, agriculture and material handling. Combining an understanding of bearing systems with power transmission gives SKF the opportunity to enhance the support available to users.

All SKF Power Transmission products are identified by an SKF specific designation prefix. Apart from that, the designation follows international standards for easy recognition and cross-referencing. The SKF Power Transmission range covers most common types of products, which can be divided into six main categories - belts, pulleys, chains, sprockets, couplings as well as bushings and hubs.

## **About the data in this catalogue**

The data in this catalogue relates to SKF's state-of-the-art technology as of mid-2015. This data may differ from that shown in earlier catalogues because of revised methods of calculation, redesign or technological developments.

SKF reserves the right to make continuing improvements to SKF products with respect to materials, design and manufacturing methods, as well as changes necessitated by technological developments.

## **Other Power Transmission catalogues**

Product information is also available via the SKF Power Transmission products website at [www.skfptp.com](http://www.skfptp.com). The website not only provides product information, but also online calculation tools, drawings, and search and selection functions.

The main printed SKF Power Transmission catalogues are:

- SKF Transmission chain catalogue
- SKF Couplings catalogue
- SKF FX Keyless Bushings catalogue
- SKF Xtra Power Belts catalogue
- SKF Conveyor Chain catalogue

For more information about SKF Power Transmission products, contact your local SKF representative or SKF Authorized Distributor.







# SKF XP Lawn and Garden belts

A new, full range of SKF XP Lawn and Garden v-belts for those extra tough applications are now available.

Aramid corded lawn, garden and grounds keeper power equipment belts are extremely durable due to their high strength construction. Aramid is used in these belts as the tension member due to its inherent length stability and high tensile strength.

Lawn and garden equipment belts use friction and a clutching action rather than being powered by gears. Standard polyester cord will stretch and become loose over time. SKF belts that are constructed from aramid cord also have a special dry cotton wrap which provides for a consistent power transmission and reduced slippage whilst clutching, high resistance to repeated reverse flexing and high resistance to oil, heat and cracking. An ideal belt for all lawn, garden and grounds keeping equipment.


Aramid constructed belts are specifically used on applications where high levels of power transmission and long service life are required, where there are restrictions on the drive width and/or the drive is critical. This includes tillers, ride-on mowers, commercial lawn mowers and chippers/shredders, tillers and compost equipment. This equipment is commonly used by municipalities, golf courses, parks, farms and larger homes.



## SKF XP Lawn and Garden belt range nominal dimensions

Belt section	Dimensions		Height		OD: Length range
	Width				
	in.	mm	in.	mm	in.
3L	0.375	10	0.22	6	13 to 75
4L	0.500	13	0.31	8	14 to 354
5L	0.625	17	0.38	10	19 to 591

SKF XP Lawn and Garden v-belts



Section	Dimensions		OD: Length		Designation	Section	Dimensions		OD: Length		Designation	Section	Dimensions		OD: Length		Designation
	Width		mm	in.			mm	in.	mm	in.			mm	in.	mm	in.	
3L	10	3/8	381	15,0	PHG 3L150XP	4L	13	1/2	356	14,0	PHG 4L140XP	4L	13	1/2	1 676	66,0	PHG 4L660XP
	10	3/8	406	16,0	PHG 3L160XP		13	1/2	381	15,0	PHG 4L150XP		13	1/2	1 702	67,0	PHG 4L670XP
	10	3/8	432	17,0	PHG 3L170XP		13	1/2	406	16,0	PHG 4L160XP		13	1/2	1 727	68,0	PHG 4L680XP
	10	3/8	457	18,0	PHG 3L180XP		13	1/2	432	17,0	PHG 4L170XP		13	1/2	1 753	69,0	PHG 4L690XP
	10	3/8	483	19,0	PHG 3L190XP		13	1/2	457	18,0	PHG 4L180XP		13	1/2	1 778	70,0	PHG 4L700XP
	10	3/8	508	20,0	PHG 3L200XP		13	1/2	483	19,0	PHG 4L190XP		13	1/2	1 803	71,0	PHG 4L710XP
	10	3/8	533	21,0	PHG 3L210XP		13	1/2	508	20,0	PHG 4L200XP		13	1/2	1 829	72,0	PHG 4L720XP
	10	3/8	559	22,0	PHG 3L220XP		13	1/2	533	21,0	PHG 4L210XP		13	1/2	1 854	73,0	PHG 4L730XP
	10	3/8	584	23,0	PHG 3L230XP		13	1/2	546	21,5	PHG 4L215XP		13	1/2	1 880	74,0	PHG 4L740XP
	10	3/8	610	24,0	PHG 3L240XP		13	1/2	559	22,0	PHG 4L220XP		13	1/2	1 905	75,0	PHG 4L750XP
	10	3/8	635	25,0	PHG 3L250XP		13	1/2	584	23,0	PHG 4L230XP		13	1/2	1 930	76,0	PHG 4L760XP
	10	3/8	660	26,0	PHG 3L260XP		13	1/2	610	24,0	PHG 4L240XP		13	1/2	1 956	77,0	PHG 4L770XP
	10	3/8	673	26,5	PHG 3L265XP		13	1/2	635	25,0	PHG 4L250XP		13	1/2	1 981	78,0	PHG 4L780XP
	10	3/8	686	27,0	PHG 3L270XP		13	1/2	660	26,0	PHG 4L260XP		13	1/2	2 007	79,0	PHG 4L790XP
	10	3/8	711	28,0	PHG 3L280XP		13	1/2	686	27,0	PHG 4L270XP		13	1/2	2 032	80,0	PHG 4L800XP
	10	3/8	737	29,0	PHG 3L290XP		13	1/2	711	28,0	PHG 4L280XP		13	1/2	2 057	81,0	PHG 4L810XP
	10	3/8	762	30,0	PHG 3L300XP		13	1/2	737	29,0	PHG 4L290XP		13	1/2	2 083	82,0	PHG 4L820XP
	10	3/8	787	31,0	PHG 3L310XP		13	1/2	762	30,0	PHG 4L300XP		13	1/2	2 108	83,0	PHG 4L830XP
	10	3/8	813	32,0	PHG 3L320XP		13	1/2	775	30,5	PHG 4L305XP		13	1/2	2 134	84,0	PHG 4L840XP
	10	3/8	838	33,0	PHG 3L330XP		13	1/2	787	31,0	PHG 4L310XP		13	1/2	2 159	85,0	PHG 4L850XP
	10	3/8	864	34,0	PHG 3L340XP		13	1/2	813	32,0	PHG 4L320XP		13	1/2	2 184	86,0	PHG 4L860XP
	10	3/8	889	35,0	PHG 3L350XP		13	1/2	838	33,0	PHG 4L330XP		13	1/2	2 210	87,0	PHG 4L870XP
	10	3/8	914	36,0	PHG 3L360XP		13	1/2	864	34,0	PHG 4L340XP		13	1/2	2 235	88,0	PHG 4L880XP
	10	3/8	940	37,0	PHG 3L370XP		13	1/2	889	35,0	PHG 4L350XP		13	1/2	2 261	89,0	PHG 4L890XP
	10	3/8	965	38,0	PHG 3L380XP		13	1/2	914	36,0	PHG 4L360XP		13	1/2	2 286	90,0	PHG 4L900XP
	10	3/8	991	39,0	PHG 3L390XP		13	1/2	940	37,0	PHG 4L370XP		13	1/2	2 311	91,0	PHG 4L910XP
	10	3/8	1 016	40,0	PHG 3L400XP		13	1/2	965	38,0	PHG 4L380XP		13	1/2	2 337	92,0	PHG 4L920XP
	10	3/8	1 041	41,0	PHG 3L410XP		13	1/2	991	39,0	PHG 4L390XP		13	1/2	2 362	93,0	PHG 4L930XP
	10	3/8	1 054	41,5	PHG 3L415XP		13	1/2	1 016	40,0	PHG 4L400XP		13	1/2	2 388	94,0	PHG 4L940XP
	10	3/8	1 067	42,0	PHG 3L420XP		13	1/2	1 029	40,5	PHG 4L405XP		13	1/2	2 413	95,0	PHG 4L950XP
10	3/8	1 092	43,0	PHG 3L430XP	13	1/2	1 041	41,0	PHG 4L410XP	13	1/2	2 438	96,0	PHG 4L960XP			
10	3/8	1 118	44,0	PHG 3L440XP	13	1/2	1 067	42,0	PHG 4L420XP	13	1/2	2 464	97,0	PHG 4L970XP			
10	3/8	1 143	45,0	PHG 3L450XP	13	1/2	1 092	43,0	PHG 4L430XP	13	1/2	2 489	98,0	PHG 4L980XP			
10	3/8	1 168	46,0	PHG 3L460XP	13	1/2	1 118	44,0	PHG 4L440XP	13	1/2	2 515	99,0	PHG 4L990XP			
10	3/8	1 194	47,0	PHG 3L470XP	13	1/2	1 143	45,0	PHG 4L450XP	13	1/2	2 540	100,0	PHG 4L1000XP			
10	3/8	1 219	48,0	PHG 3L480XP	13	1/2	1 168	46,0	PHG 4L460XP	13	1/2	2 565	101,0	PHG 4L1010XP			
10	3/8	1 245	49,0	PHG 3L490XP	13	1/2	1 194	47,0	PHG 4L470XP	13	1/2	2 591	102,0	PHG 4L1020XP			
10	3/8	1 270	50,0	PHG 3L500XP	13	1/2	1 219	48,0	PHG 4L480XP	13	1/2	2 616	103,0	PHG 4L1030XP			
10	3/8	1 295	51,0	PHG 3L510XP	13	1/2	1 245	49,0	PHG 4L490XP	13	1/2	2 642	104,0	PHG 4L1040XP			
10	3/8	1 321	52,0	PHG 3L520XP	13	1/2	1 270	50,0	PHG 4L500XP	13	1/2	2 667	105,0	PHG 4L1050XP			
10	3/8	1 346	53,0	PHG 3L530XP	13	1/2	1 295	51,0	PHG 4L510XP	13	1/2	2 692	106,0	PHG 4L1060XP			
10	3/8	1 372	54,0	PHG 3L540XP	13	1/2	1 321	52,0	PHG 4L520XP	13	1/2	2 718	107,0	PHG 4L1070XP			
10	3/8	1 397	55,0	PHG 3L550XP	13	1/2	1 346	53,0	PHG 4L530XP	13	1/2	2 743	108,0	PHG 4L1080XP			
10	3/8	1 422	56,0	PHG 3L560XP	13	1/2	1 372	54,0	PHG 4L540XP	13	1/2	2 769	109,0	PHG 4L1090XP			
10	3/8	1 448	57,0	PHG 3L570XP	13	1/2	1 397	55,0	PHG 4L550XP	13	1/2	2 794	110,0	PHG 4L1100XP			
10	3/8	1 473	58,0	PHG 3L580XP	13	1/2	1 422	56,0	PHG 4L560XP	13	1/2	2 819	111,0	PHG 4L1110XP			
10	3/8	1 499	59,0	PHG 3L590XP	13	1/2	1 448	57,0	PHG 4L570XP	13	1/2	2 845	112,0	PHG 4L1120XP			
10	3/8	1 524	60,0	PHG 3L600XP	13	1/2	1 473	58,0	PHG 4L580XP	13	1/2	2 870	113,0	PHG 4L1130XP			
10	3/8	1 549	61,0	PHG 3L610XP	13	1/2	1 499	59,0	PHG 4L590XP	13	1/2	2 896	114,0	PHG 4L1140XP			
10	3/8	1 575	62,0	PHG 3L620XP	13	1/2	1 524	60,0	PHG 4L600XP	13	1/2	2 946	116,0	PHG 4L1160XP			
10	3/8	1 600	63,0	PHG 3L630XP	13	1/2	1 549	61,0	PHG 4L610XP	13	1/2	2 972	117,0	PHG 4L1170XP			
10	3/8	1 753	69,0	PHG 3L690XP	13	1/2	1 575	62,0	PHG 4L620XP	13	1/2	3 048	120,0	PHG 4L1200XP			
10	3/8	1 803	71,0	PHG 3L710XP	13	1/2	1 600	63,0	PHG 4L630XP	13	1/2	3 353	132,0	PHG 4L1320XP			
10	3/8	1 880	74,0	PHG 3L740XP	13	1/2	1 626	64,0	PHG 4L640XP								
10	3/8	1 905	75,0	PHG 3L750XP	13	1/2	1 651	65,0	PHG 4L650XP								
												5L	17	5/8	584	23,0	PHG 5L230XP

SKF XP Lawn and Garden v-belts

Section	Dimensions		OD: Length		Designation	Section	Dimensions		OD: Length		Designation
	Width		mm	in.			mm	in.	mm	in.	
5L	17	5/8	610	24,0	PHG 5L240XP	5L	17	5/8	2 540	100,0	PHG 5L1000XP
	17	5/8	635	25,0	PHG 5L250XP		17	5/8	2 565	101,0	PHG 5L1010XP
	17	5/8	660	26,0	PHG 5L260XP		17	5/8	2 591	102,0	PHG 5L1020XP
	17	5/8	686	27,0	PHG 5L270XP		17	5/8	2 616	103,0	PHG 5L1030XP
	17	5/8	711	28,0	PHG 5L280XP		17	5/8	2 642	104,0	PHG 5L1040XP
	17	5/8	737	29,0	PHG 5L290XP		17	5/8	2 667	105,0	PHG 5L1050XP
	17	5/8	762	30,0	PHG 5L300XP		17	5/8	2 692	106,0	PHG 5L1060XP
	17	5/8	787	31,0	PHG 5L310XP		17	5/8	2 718	107,0	PHG 5L1070XP
	17	5/8	813	32,0	PHG 5L320XP		17	5/8	2 743	108,0	PHG 5L1080XP
	17	5/8	838	33,0	PHG 5L330XP		17	5/8	2 769	109,0	PHG 5L1090XP
	17	5/8	864	34,0	PHG 5L340XP		17	5/8	2 845	112,0	PHG 5L1120XP
	17	5/8	889	35,0	PHG 5L350XP		17	5/8	2 896	114,0	PHG 5L1140XP
	17	5/8	914	36,0	PHG 5L360XP		17	5/8	2 997	118,0	PHG 5L1180XP
	17	5/8	940	37,0	PHG 5L370XP		17	5/8	3 048	120,0	PHG 5L1200XP
	17	5/8	965	38,0	PHG 5L380XP		17	5/8	3 099	122,0	PHG 5L1220XP
	17	5/8	991	39,0	PHG 5L390XP		17	5/8	3 150	124,0	PHG 5L1240XP
	17	5/8	1 016	40,0	PHG 5L400XP		17	5/8	3 200	126,0	PHG 5L1260XP
	17	5/8	1 041	41,0	PHG 5L410XP		17	5/8	3 251	128,0	PHG 5L1280XP
	17	5/8	1 067	42,0	PHG 5L420XP		17	5/8	3 302	130,0	PHG 5L1300XP
	17	5/8	1 092	43,0	PHG 5L430XP		17	5/8	3 353	132,0	PHG 5L1320XP
	17	5/8	1 118	44,0	PHG 5L440XP		17	5/8	3 404	134,0	PHG 5L1340XP
	17	5/8	1 143	45,0	PHG 5L450XP		17	5/8	3 454	136,0	PHG 5L1360XP
	17	5/8	1 168	46,0	PHG 5L460XP		17	5/8	3 505	138,0	PHG 5L1380XP
	17	5/8	1 194	47,0	PHG 5L470XP		17	5/8	3 556	140,0	PHG 5L1400XP
	17	5/8	1 219	48,0	PHG 5L480XP						
	17	5/8	1 245	49,0	PHG 5L490XP						
	17	5/8	1 270	50,0	PHG 5L500XP						
	17	5/8	1 295	51,0	PHG 5L510XP						
	17	5/8	1 321	52,0	PHG 5L520XP						
	17	5/8	1 346	53,0	PHG 5L530XP						
	17	5/8	1 372	54,0	PHG 5L540XP						
	17	5/8	1 397	55,0	PHG 5L550XP						
	17	5/8	1 422	56,0	PHG 5L560XP						
	17	5/8	1 448	57,0	PHG 5L570XP						
	17	5/8	1 473	58,0	PHG 5L580XP						
	17	5/8	1 499	59,0	PHG 5L590XP						
	17	5/8	1 524	60,0	PHG 5L600XP						
	17	5/8	1 549	61,0	PHG 5L610XP						
	17	5/8	1 575	62,0	PHG 5L620XP						
	17	5/8	1 600	63,0	PHG 5L630XP						
	17	5/8	1 626	64,0	PHG 5L640XP						
	17	5/8	1 651	65,0	PHG 5L650XP						
	17	5/8	1 676	66,0	PHG 5L660XP						
	17	5/8	1 702	67,0	PHG 5L670XP						
	17	5/8	1 727	68,0	PHG 5L680XP						
	17	5/8	1 753	69,0	PHG 5L690XP						
	17	5/8	1 778	70,0	PHG 5L700XP						
	17	5/8	1 803	71,0	PHG 5L710XP						
	17	5/8	1 829	72,0	PHG 5L720XP						
	17	5/8	1 854	73,0	PHG 5L730XP						
	17	5/8	1 880	74,0	PHG 5L740XP						
	17	5/8	1 905	75,0	PHG 5L750XP						
	17	5/8	1 930	76,0	PHG 5L760XP						
	17	5/8	1 956	77,0	PHG 5L770XP						
	17	5/8	1 981	78,0	PHG 5L780XP						
	17	5/8	2 007	79,0	PHG 5L790XP						
	17	5/8	2 032	80,0	PHG 5L800XP						
	17	5/8	2 057	81,0	PHG 5L810XP						
	17	5/8	2 083	82,0	PHG 5L820XP						
	17	5/8	2 108	83,0	PHG 5L830XP						
	17	5/8	2 134	84,0	PHG 5L840XP						
	17	5/8	2 159	85,0	PHG 5L850XP						
	17	5/8	2 184	86,0	PHG 5L860XP						
	17	5/8	2 210	87,0	PHG 5L870XP						
	17	5/8	2 235	88,0	PHG 5L880XP						
	17	5/8	2 261	89,0	PHG 5L890XP						
	17	5/8	2 286	90,0	PHG 5L900XP						
	17	5/8	2 311	91,0	PHG 5L910XP						
	17	5/8	2 337	92,0	PHG 5L920XP						
	17	5/8	2 362	93,0	PHG 5L930XP						
	17	5/8	2 388	94,0	PHG 5L940XP						
	17	5/8	2 413	95,0	PHG 5L950XP						
	17	5/8	2 438	96,0	PHG 5L960XP						
	17	5/8	2 464	97,0	PHG 5L970XP						
	17	5/8	2 489	98,0	PHG 5L980XP						
	17	5/8	2 515	99,0	PHG 5L990XP						

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Aircap	538	PHG 3L310XP	Allis Chalmers/Deutz	1602969	PHG 4L480XP	Allis Chalmers/Deutz	2087732	PHG 4L780XP
	644	PHG 3L350XP		1603075	PHG 4L930XP		2087759	PHG 4L660XP
	10661	PHG 4L400XP		1604406	PHG 4L830XP		2087778	PHG 4L660XP
	10713	PHG 4L320XP		1605816	PHG 4L840XP		2087836	PHG 4L740XP
	10717	PHG 3L300XP		1607051	PHG 4L700XP		2087883	PHG 3L340XP
	10720	PHG 5L740XP		1607812	PHG 4L820XP	Ariens/Gravely	3088	PHG 3L350XP
	10722	PHG 4L510XP		1607813	PHG 4L830XP		3089	PHG 4L360XP
	16301	PHG 4L310XP		1609767	PHG 4L520XP		5163	PHG 4L310XP
	754240	PHG 5L380XP		1610577	PHG 4L560XP		6267	PHG 4L750XP
	754241	PHG 5L350XP		1610578	PHG 4L250XP		6565	PHG 5L510XP
	754244	PHG 4L400XP		1651201	PHG 4L730XP		6566	PHG 4L460XP
	754245	PHG 4L590XP		1663009	PHG 3L280XP		9240	PHG 4L280XP
	1540241	PHG 5L350XP		1664457	PHG 4L410XP		10860	PHG 3L350XP
	1540329	PHG 5L690XP		1664946	PHG 4L570XP		12038	PHG 4L530XP
	7540145	PHG 5L690XP		1665706	PHG 4L390XP		12096	PHG 4L500XP
	7540151	PHG 5L670XP		1666654	PHG 3L320XP		12117	PHG 4L300XP
	7540198	PHG 4L620XP		1666655	PHG 4L410XP		13472	PHG 5L300XP
	7540238	PHG 5L490XP		1667200	PHG 4L340XP		13474	PHG 5L320XP
	7540244	PHG 4L400XP		1668065	PHG 4L690XP		15243	PHG 4L880XP
	7540245	PHG 4L590XP		1671788	PHG 3L340XP		15355	PHG 4L380XP
	7540326	PHG 4L620XP		1672732	PHG 3L370XP		21692	PHG 3L250XP
	7540367	PHG 4L340XP		1673667	PHG 4L950XP		22068	PHG 4L690XP
	7540195A	PHG 4L540XP		1674312	PHG 4L350XP		23639	PHG 5L670XP
	SP2	PHG 4L250XP		1675005	PHG 4L400XP		23640	PHG 5L980XP
				1676460	PHG 4L430XP		25129	PHG 4L760XP
Allis Chalmers/Deutz	1110	PHG 4L350XP		1676461	PHG 3L330XP		25659	PHG 3L240XP
	2435	PHG 4L350XP		1701251	PHG 4L420XP		26123	PHG 4L250XP
	6163	PHG 3L370XP		1701257	PHG 4L420XP		26137	PHG 3L310XP
	6184	PHG 3L390XP		1707740	PHG 4L690XP		26147	PHG 3L300XP
	14843	PHG 4L290XP		2025341	PHG 4L440XP		26149	PHG 4L680XP
	24615	PHG 4L640XP		2025364	PHG 4L820XP		26150	PHG 3L340XP
	27114	PHG 4L830XP		2025461	PHG 3L360XP		30101	PHG 5L490XP
	101136	PHG 4L640XP		2025463	PHG 4L530XP		31912	PHG 4L490XP
	105122	PHG 5L560XP		2025492	PHG 5L450XP		32322	PHG 4L720XP
	105280	PHG 5L640XP		2025641	PHG 5L490XP		32330	PHG 3L450XP
	105287	PHG 5L880XP		2025663	PHG 4L350XP		34289	PHG 4L940XP
	105340	PHG 5L960XP		2025712	PHG 5L490XP		34332	PHG 4L350XP
	106689	PHG 4L550XP		2025879	PHG 4L630XP		34346	PHG 5L600XP
	106769	PHG 4L560XP		2025893	PHG 4L480XP		34944	PHG 4L460XP
	108248	PHG 4L480XP		2026066	PHG 3L380XP		34945	PHG 4L910XP
	108458	PHG 4L450XP		2026081	PHG 4L360XP		35955	PHG 4L530XP
	118225	PHG 4L250XP		2026266	PHG 4L380XP		36004	PHG 4L470XP
	118312	PHG 4L340XP		2026268	PHG 4L390XP		36232	PHG 4L710XP
	121078	PHG 4L350XP		2026270	PHG 4L350XP		36233	PHG 4L300XP
	121398	PHG 4L430XP		2026324	PHG 4L910XP		36880	PHG 4L340XP
	152017	PHG 5L450XP		2026378	PHG 3L220XP		36987	PHG 4L720XP
	154273	PHG 5L420XP		2026499	PHG 4L550XP		41200	PHG 4L620XP
	156120	PHG 4L630XP		2026755	PHG 4L390XP		41963	PHG 4L300XP
	158573	PHG 4L310XP		2026869	PHG 3L390XP		43318	PHG 4L870XP
	161146	PHG 4L340XP		2027102	PHG 4L610XP		49029	PHG 4L450XP
	162081	PHG 4L760XP		2027114	PHG 4L850XP		72024	PHG 4L290XP
	164146	PHG 4L340XP		2027121	PHG 4L450XP		72026	PHG 5L410XP
	165048	PHG 4L850XP		2027134	PHG 4L700XP		72029	PHG 5L490XP
	170164	PHG 4L770XP		2027168	PHG 4L340XP		72038	PHG 4L530XP
	172929	PHG 3L330XP		2027581	PHG 4L470XP		72042	PHG 3L300XP
	174224	PHG 4L660XP		2027624	PHG 5L960XP		72043	PHG 3L290XP
	174364	PHG 4L490XP		2027639	PHG 5L880XP		72045	PHG 5L360XP
	174486	PHG 5L490XP		2028035	PHG 4L850XP		72046	PHG 3L280XP
	174883	PHG 4L340XP		2028241	PHG 4L310XP		72048	PHG 3L250XP
	174911	PHG 4L440XP		2028474	PHG 4L490XP		72048	PHG 3L280XP
	175361	PHG 4L290XP		2028549	PHG 4L240XP		72049	PHG 5L470XP
	176393	PHG 3L370XP		2028766	PHG 4L930XP		72050	PHG 5L440XP
	176439	PHG 4L740XP		2028988	PHG 5L490XP		72052	PHG 5L690XP
	176917	PHG 4L350XP		2029056	PHG 4L570XP		72056	PHG 4L320XP
	177452	PHG 4L620XP		2029223	PHG 4L440XP		72060	PHG 4L280XP
	200554	PHG 4L460XP		2029348	PHG 4L350XP		72061	PHG 4L350XP
	1060520	PHG 4L700XP		2029350	PHG 4L530XP		72065	PHG 4L360XP
	1061520	PHG 4L700XP		2029622	PHG 4L700XP		72066	PHG 3L340XP
	1101251	PHG 4L420XP		2029660	PHG 4L620XP		72072	PHG 4L350XP
	1101257	PHG 4L420XP		2029665	PHG 4L1000XP		72073	PHG 3L250XP
	1601238	PHG 3L340XP		2029715	PHG 4L790XP		72074	PHG 3L340XP
	1601239	PHG 3L340XP		2029748	PHG 4L340XP		72076	PHG 4L350XP
	1601405	PHG 4L400XP		2029789	PHG 4L340XP		72078	PHG 4L770XP
	1601524	PHG 4L780XP		2029828	PHG 3L370XP		72083	PHG 4L360XP
	1601672	PHG 4L610XP		2029829	PHG 4L350XP		72084	PHG 3L270XP
	1601695	PHG 4L430XP		2087648	PHG 4L720XP		72085	PHG 3L290XP
	1602157	PHG 4L730XP						

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Ariens/Gravely</b>	72086	PHG 4L400XP	<b>Ariens/Gravely</b>	383	PHG 4L240XP	<b>Ayp</b>	48530	PHG 3L430XP
	72089	PHG 4L360XP		708	PHG 5L380XP		49233	PHG 3L440XP
	72093	PHG 4L310XP		992	PHG 4L230XP		49570	PHG 4L350XP
	72095	PHG 4L460XP		1060	PHG 4L1080XP		50272	PHG 4L350XP
	72096	PHG 4L500XP		2363	PHG 4L240XP		50307	PHG 3L280XP
	72097	PHG 3L230XP		2543	PHG 4L280XP		50597	PHG 4L300XP
	72098	PHG 3L330XP		5600	PHG 5L480XP		51258	PHG 4L680XP
	72099	PHG 3L280XP		8140	PHG 4L350XP		53157	PHG 4L310XP
	72101	PHG 4L580XP		8141	PHG 4L490XP		53558	PHG 4L350XP
	72102	PHG 4L750XP		8142	PHG 4L260XP		53747	PHG 3L300XP
	72103	PHG 4L890XP		8143	PHG 4L490XP		53987	PHG 4L290XP
	72105	PHG 4L350XP		8597	PHG 4L220XP		54185	PHG 4L340XP
	72106	PHG 3L370XP		8718	PHG 5L490XP		54378	PHG 4L510XP
	72107	PHG 3L310XP		8868	PHG 4L320XP		54622	PHG 4L250XP
	72109	PHG 4L320XP		8869	PHG 4L330XP		54662	PHG 4L250XP
	72110	PHG 4L710XP		9517	PHG 5L490XP		55936	PHG 5L430XP
	72111	PHG 4L340XP		10830	PHG 4L600XP		55941	PHG 5L710XP
	72112	PHG 3L350XP		11296	PHG 4L780XP		56823	PHG 5L820XP
	72115	PHG 4L670XP		11361	PHG 5L770XP		57955	PHG 4L700XP
	72116	PHG 4L710XP		11483	PHG 5L430XP		58406	PHG 4L650XP
	72117	PHG 4L300XP		11635	PHG 4L630XP		58558	PHG 4L490XP
	72118	PHG 4L470XP		11904	PHG 4L910XP		58577	PHG 4L630XP
	72119	PHG 4L300XP		11905	PHG 4L510XP		59311	PHG 3L210XP
	72121	PHG 4L340XP		12903	PHG 4L580XP		59786	PHG 4L280XP
	72122	PHG 4L720XP		13376	PHG 5L850XP		59849	PHG 4L730XP
	72123	PHG 4L520XP		13394	PHG 5L350XP		59884	PHG 4L410XP
	72124	PHG 4L650XP		15638	PHG 5L500XP		61346	PHG 4L390XP
	72126	PHG 3L330XP		18358	PHG 5L560XP		62828	PHG 4L700XP
	72127	PHG 3L380XP		20317	PHG 4L200XP		63798	PHG 4L530XP
	72131	PHG 3L360XP		20555	PHG 4L410XP		64744	PHG 5L810XP
	72134	PHG 5L330XP		20556	PHG 4L480XP		65016	PHG 5L460XP
	72135	PHG 4L680XP		20715	PHG 4L350XP		65107	PHG 3L310XP
	72135	PHG 5L680XP		20716	PHG 4L350XP		65133	PHG 3L320XP
	72136	PHG 4L510XP		20717	PHG 4L560XP		65284	PHG 4L340XP
	72137	PHG 4L310XP		21053	PHG 4L620XP		67346	PHG 4L390XP
	72138	PHG 3L300XP		21058	PHG 4L630XP		67348	PHG 4L470XP
	72138	PHG 3L330XP		21059	PHG 4L440XP		67398	PHG 4L530XP
	72139	PHG 4L960XP		21170	PHG 4L290XP		67438	PHG 4L470XP
	72142	PHG 4L340XP		21615	PHG 4L950XP		67788	PHG 4L780XP
	72144	PHG 4L890XP		22224	PHG 4L320XP		69418	PHG 4L920XP
	72148	PHG 4L580XP		22958	PHG 5L820XP		69428	PHG 4L870XP
	72155	PHG 4L650XP		23072	PHG 4L430XP		69438	PHG 4L920XP
	72156	PHG 4L350XP		23098	PHG 4L620XP		69448	PHG 5L710XP
	72157	PHG 3L330XP		23212	PHG 4L590XP		70637	PHG 4L400XP
	72159	PHG 3L210XP		23214	PHG 4L590XP		71240	PHG 4L920XP
	72161	PHG 4L640XP		23223	PHG 4L950XP		71408	PHG 4L400XP
	72162	PHG 4L640XP		23748	PHG 4L620XP		71635	PHG 4L630XP
	72163	PHG 4L640XP		23796	PHG 4L590XP		73794	PHG 4L940XP
	72240	PHG 3L250XP		23882	PHG 4L590XP		74164	PHG 4L510XP
	72241	PHG 3L240XP		24732	PHG 4L520XP		74212	PHG 4L570XP
	5163131	PHG 4L310XP		25667	PHG 4L560XP		74277	PHG 4L610XP
	10860131	PHG 3L350XP		25686	PHG 4L550XP		74278	PHG 4L800XP
	12077131	PHG 5L410XP		26308	PHG 5L680XP		74977	PHG 3L360XP
	15242131	PHG 4L290XP		26928	PHG 5L830XP		75443	PHG 3L340XP
	15355131	PHG 4L380XP		27323	PHG 4L410XP		75671	PHG 3L380XP
	17798131	PHG 4L400XP		28594	PHG 4L350XP		75761	PHG 3L380XP
	51653131	PHG 4L310XP					76018	PHG 4L410XP
	10860P1	PHG 3L350XP	<b>Ayp</b>	32668	PHG 4L330XP		76019	PHG 4L550XP
	12077P1	PHG 5L410XP		33508	PHG 4L910XP		76274	PHG 4L590XP
	15242P1	PHG 4L290XP		37031	PHG 4L1000XP		76275	PHG 4L750XP
	15355P1	PHG 4L380XP		37168	PHG 4L870XP			
	17798P1	PHG 4L400XP		39159	PHG 4L280XP		76672	PHG 4L350XP
	34X101	PHG 5L490XP		39454	PHG 4L880XP		76806	PHG 4L350XP
	34X102	PHG 5L360XP		39455	PHG 4L630XP		77375	PHG 4L230XP
	34X104	PHG 3L320XP		40068	PHG 4L220XP		78303	PHG 4L360XP
				40899	PHG 4L350XP		78750	PHG 4L390XP
	34X105	PHG 3L250XP		41029	PHG 4L220XP		79477	PHG 3L370XP
	34X69	PHG 5L410XP					81229	PHG 3L360XP
	34X88	PHG 3L350XP		41740	PHG 4L380XP		82258	PHG 4L350XP
	34X89	PHG 4L360XP		42111	PHG 5L700XP		83663	PHG 3L330XP
	34X92	PHG 5L440XP		43797	PHG 4L560XP		83691	PHG 3L350XP
				43979	PHG 4L560XP			
				44148	PHG 4L630XP		84287	PHG 4L400XP
	5070A22	PHG 5L560XP					84352	PHG 5L810XP
	5163P1	PHG 4L310XP					88519	PHG 3L400XP
	51653P1	PHG 4L310XP		45187	PHG 4L440XP		88680	PHG 4L320XP
	A408	PHG 5L710XP		47200	PHG 4L290XP		88690	PHG 4L330XP
	A409	PHG 5L580XP		47201	PHG 4L250XP			PHG 4L330XP
				47390	PHG 4L710XP			
	M475	PHG 5L300XP		47793	PHG 4L250XP		91218	PHG 4L1120XP

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Ayp	91798	PHG 3L390XP	Ayp	507023	PHG 3L390XP	Ayp	532170140	PHG 4L1130XP
	91808	PHG 4L410XP		507750	PHG 4L280XP		532174368	PHG 5L900XP
	101342	PHG 4L930XP		508774	PHG 3L310XP		532174883	PHG 4L340XP
	110883	PHG 4L990XP		509548	PHG 4L290XP		532175436	PHG 3L320XP
	124293	PHG 4L800XP		510228	PHG 3L360XP		532178138	PHG 4L870XP
	126576	PHG 4L820XP		510271	PHG 4L350XP		532180808	PHG 5L890XP
	130801	PHG 4L950XP		511192	PHG 4L330XP		532187283	PHG 5L1430XP
	130969	PHG 4L930XP		511193	PHG 3L330XP		532191273	PHG 5L1430XP
	131006	PHG 4L990XP		511227	PHG 3L410XP		532191723	PHG 5L1430XP
	131264	PHG 4L790XP		511246	PHG 3L350XP		532193214	PHG 4L920XP
	131290	PHG 4L880XP		513727	PHG 4L550XP		532196103	PHG 5L1480XP
	132801	PHG 4L520XP		513857	PHG 3L410XP		532197242	PHG 5L1400XP
	133035	PHG 4L410XP		513957	PHG 3L230XP		532197253	PHG 4L1010XP
	137078	PHG 3L320XP		602420	PHG 4L890XP		532405143	PHG 4L1070XP
	137153	PHG 4L840XP		641414	PHG 5L810XP		532429636	PHG 4L1010XP
	137283	PHG 5L1430XP		647411	PHG 5L810XP		535126520	PHG 4L880XP
	138255	PHG 4L940XP		647414	PHG 5L810XP		8521220040	PHG 5L1430XP
	138399	PHG 4L590XP		883311	PHG 5L730XP		1001117J	PHG 4L690XP
	139573	PHG 4L840XP		976611	PHG 3L360XP		100614N	PHG 4L70XP
	140067	PHG 4L830XP		976614	PHG 3L360XP		100670N	PHG 4L790XP
	140218	PHG 4L850XP		1071249	PHG 4L500XP		100717N	PHG 4L690XP
	140294	PHG 4L820XP		1108536	PHG 5L270XP		101342N	PHG 4L940XP
	141416	PHG 4L840XP		3754141	PHG 3L330XP		102143X	PHG 4L530XP
	144200	PHG 4L890XP		4897111	PHG 4L350XP		102726X	PHG 5L470XP
	144959	PHG 4L960XP		5006471	PHG 3L380XP		103142N	PHG 4L930XP
	146527	PHG 3L320XP		5032024	PHG 4L310XP		104022X	PHG 4L430XP
	148763	PHG B83		5032027	PHG 4L280XP		105085X	PHG 4L790XP
	156971	PHG 4L820XP		7540109	PHG 4L430XP		105380X	PHG 4L880XP
	157769	PHG 3L320XP		7540121	PHG 4L310XP		105732X	PHG 4L900XP
	158818	PHG 4L840XP		7540154	PHG 4L350XP		105876X	PHG 4L930XP
	160855	PHG 4L950XP		7540177	PHG 4L320XP		106035X	PHG 4L790XP
	161588	PHG 4L830XP		7540189	PHG 4L440XP		106085X	PHG 4L790XP
	161597	PHG 4L830XP		7540196	PHG 4L300XP		1060885X	PHG 4L790XP
	161741	PHG 4L790XP		7540201	PHG 4L410XP		106095X	PHG 4L790XP
	163817	PHG 4L950XP		7540220	PHG 5L270XP		106381N	PHG 4L920XP
	165632	PHG 4L1200XP		7540221	PHG 5L520XP		106381X	PHG 4L920XP
	166060	PHG 3L380XP		7540224	PHG 5L250XP		106412X	PHG 4L690XP
	169178	PHG AA112		7540231	PHG 4L280XP		108103X	PHG 4L810XP
	170037	PHG AA105		7540232	PHG 4L200XP		108313X	PHG 4L940XP
	170140			7540255	PHG 4L350XP		110083X	PHG 4L990XP
	174368	PHG 5L900XP		7540357	PHG 4L400XP		110084X	PHG 4L930XP
	174369	PHG 5L890XP		53219478	PHG 4L850XP		110833X	PHG 4L990XP
	174978	PHG 4L850XP		90005938	PHG 3L300XP		11084X	PHG 4L940XP
	175436	PHG 3L320XP		90051458	PHG 4L390XP		1108834X	PHG 4L990XP
	178138	PHG 4L870XP		90053790	PHG 3L370XP		110883X	PHG 4L990XP
	180214	PHG 4L870XP		531007562	PHG 4L880XP		110884X	PHG 4L940XP
	180216	PHG 4L830XP		532083691	PHG 3L350XP		120418X	PHG 4L800XP
	180217			532106085	PHG 4L790XP		121979X	PHG 4L880XP
	180808	PHG 5L890XP		532110883	PHG 4L990XP		123451X	PHG 4L810XP
	187283	PHG 5L1430XP		532110884	PHG 4L940XP		123461X	PHG 4L800XP
	191273	PHG 5L1430XP		532124970	PHG 4L410XP		123554X	PHG 4L940XP
	191723	PHG 5L1430XP		532125907	PHG 4L900XP		124293X	PHG 4L800XP
	193103	PHG 5L1480XP		532126520	PHG 4L890XP		124524X	PHG 4L890XP
	193214	PHG 4L920XP		532130801	PHG 4L940XP		125520X	PHG 4L890XP
	196103	PHG 5L1480XP		532130969	PHG 4L930XP		125907X	PHG 4L900XP
	197242	PHG 5L1400XP		532131264	PHG 4L790XP		125908X	PHG 4L930XP
	197253	PHG 4L1010XP		532131290	PHG 4L880XP		125908X	PHG 4L930XP
	265111	PHG 4L230XP		532132801	PHG 4L520XP		126520X	PHG 4L880XP
	302470	PHG 4L250XP		532133035	PHG 4L410XP		126520X	PHG 4L890XP
	302706	PHG 4L380XP		532137078	PHG 3L320XP		126576X	PHG 4L820XP
	303310	PHG 3L310XP		532137153	PHG 4L840XP		126907X	PHG 4L900XP
	304200	PHG 4L200XP		532138255	PHG 4L940XP		130969MS	PHG 4L930XP
	304240	PHG 4L240XP		532139573	PHG 4L840XP		131264MS	PHG 4L790XP
	304270	PHG 4L250XP		532140067	PHG 4L830XP		1322H	PHG 5L290XP
	304280	PHG 4L280XP		532140218	PHG 4L850XP		1323H	PHG 5L700XP
	304310	PHG 4L310XP		532140294	PHG 4L820XP		138255CS	PHG 4L940XP
	304350	PHG 4L350XP		532144200	PHG 4L890XP		138255MS	PHG 4L940XP
	305698	PHG 4L730XP		532144959	PHG 4L960XP		138255WA	PHG 4L940XP
	405143	PHG 4L1070XP		532146527	PHG 3L320XP		140067CS	PHG 4L830XP
	429636	PHG 4L1010XP		532157769	PHG 3L320XP		140067MS	PHG 4L830XP
	483311	PHG 4L410XP		532161588	PHG 4L830XP		140294MS	PHG 4L820XP
	501089	PHG 4L300XP		532161597	PHG 4L830XP		144200CS	PHG 4L890XP
	501161	PHG 4L540XP		532161741	PHG 4L790XP		144200MS	PHG 4L890XP
	501330	PHG 4L310XP		532161957	PHG 4L830XP		1563R	PHG 5L500XP
	502136	PHG 4L310XP		532165632	PHG 4L1200XP		1629J	PHG 4L830XP
	504193	PHG 4L260XP		532166060	PHG 3L380XP		1692J	PHG 4L830XP



Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Ayp</b>	174368A 177J 178J 1835R 1836R  2295R 23796X 2614J 2630R 2692R  2852H 3103J 31X12 31X26 31X3  3350R 3496H 3541R 3568H 37031J  3703J 3704J 3716R 3717R 3754H  3754H1 37X14 37X15 37X16 37X17  37X2 37X23 37X27 37X34 37X5  37X50 37X51 37X54 37X55 37X59  37X6 37X7 4322M 4376J 4384H  4454J 4703H 4798J 4833H 4866J  4897H 4897H1 4965R 5091H 5092H  5125R 5165H 518J 5296M 5357H  5436H 5437R 543J 5559H 5559J  5600H 5655R 584J 5859H 5A803  6095R 6118R 634A563 6414H 6474H  6517H	PHG 5L900XP PHG 5L430XP PHG 5L530XP PHG 5L570XP PHG 5L550XP  PHG 5L820XP PHG 4L950XP PHG 3L440XP PHG 5L680XP PHG 5L830XP  PHG 5L350XP PHG 4L1000XP PHG 4L550XP PHG 4L880XP PHG 4L460XP  PHG 4L910XP PHG 4L250XP PHG 5L710XP PHG 5L290XP PHG 4L1000XP  PHG 4L1000XP PHG 5L1000XP PHG 4L870XP PHG 4L920XP PHG 3L330XP  PHG 3L330XP PHG 4L430XP PHG 4L620XP PHG 4L590XP PHG 4L950XP  PHG 4L480XP PHG 4L430XP PHG 4L830XP PHG 4L770XP PHG 4L350XP  PHG 4L540XP PHG 4L360XP PHG 4L830XP PHG 4L910XP PHG 4L790XP  PHG 4L350XP PHG 4L560XP PHG 4L400XP PHG 4L490XP PHG 5L710XP  PHG 4L640XP PHG 5L480XP PHG 4L780XP PHG 4L410XP PHG 4L780XP  PHG 4L350XP PHG 4L350XP PHG 5L640XP PHG 5L820XP PHG 5L490XP  PHG 4L680XP PHG 4L700XP PHG 4L690XP PHG 3L210XP PHG 5L530XP  PHG 3L320XP PHG 4L510XP PHG 4L670XP PHG 5L800XP PHG 4L940XP  PHG 5L480XP PHG 5L680XP PHG 3L360XP PHG 5L570XP PHG 5L420XP  PHG 4L660XP PHG 5L760XP PHG 4L350XP PHG 5L810XP PHG 5L810XP  PHG 5L990XP	<b>Ayp</b>	6774H 6941R 6942R 6943R 6944R  7074J 7075J 7080J 7140R 7335H  758H 7843M 805H 8100H 8199M  8200M 8225R 8377J 8718H 8833H  8845R 9121R 9179R 9180R 9440M  9441M 944DM 9495H 9496H 9517H  954-0498 9766H 9768M 9787M J2210  J2280 J2300 J2350 J2390 J2410  LP2154 LP383 LP548 LP708 LP958  LP992 M202 M425C M426C PP12008  PP12010 PP12012 PP13006 PP13007 PP13008  PP13010 PP21008 PP8806 PP8807 RM2543  RM2754 RP8096 SA975 SP149 SP8597  STD303310 STD303390 STD304270 STD304280 STD304300  STD304310 STD304340 STD304350 STD304390 STD304490  STD304700	PHG 5L810XP PHG 4L920XP PHG 4L870XP PHG 4L920XP PHG 5L710XP  PHG 4L650XP PHG 5L680XP PHG 4L610XP PHG 4L400XP PHG 4L450XP  PHG 4L570XP PHG 3L290XP PHG 4L550XP PHG 5L790XP PHG 5L450XP  PHG 5L560XP PHG 4L350XP PHG 4L590XP PHG 5L490XP PHG 5L730XP  PHG 4L740XP PHG 4L1120XP PHG 3L390XP PHG 4L410XP PHG A17  PHG 4L360XP PHG A17 PHG 4L870XP PHG 4L920XP PHG 5L490XP  PHG 4L670XP PHG 3L360XP PHG 4L400XP PHG 4L430XP PHG 4L210XP  PHG 4L280XP PHG 4L300XP PHG 4L350XP PHG 4L390XP PHG 4L410XP  PHG 4L200XP PHG 4L240XP PHG A16 PHG 5L380XP PHG 4L220XP  PHG 4L230XP PHG 4L420XP PHG 4L300XP PHG 4L450XP PHG 4L820XP  PHG 4L830XP PHG 4L960XP PHG 3L320XP PHG 5L900XP PHG 5L890XP  PHG 4L820XP PHG 4L1070XP PHG 4L1010XP PHG 5L1400XP PHG 4L280XP  PHG 4L280XP PHG 4L260XP PHG 5L410XP PHG A16 PHG 4L220XP  PHG 3L310XP PHG 3L390XP PHG 4L250XP PHG 4L280XP PHG 4L300XP  PHG 4L310XP PHG 4L340XP PHG 4L350XP PHG 4L390XP PHG 4L490XP  PHG 4L700XP	<b>Ayp</b>	STD321468 STD324370 STD324410 STD324420 STD340320  800250 850313 850314  38016 38017 38030 38031 38038  38075 38076 38077 38111 38211  38234 38275 38389 38439 38440  38442 38458 38463 38470 39116  65032 65082 78030 78031 108024  108025 108071 108162 108173 118071  128099 2188134 28004A 38013N 38015N  38016N 38017N 38039N 4965R 68208A  68209A  1060 9022 9095 9200 9201  9304 10737 10738 20565 30315  30329 30334 30392 30421 30422  30425 30477 37756 50028 50134  50161 60070 113574 150168 150173  170146	PHG 4L680XP PHG 4L350XP PHG 4L410XP PHG 4L420XP PHG 4L320XP  PHG 4L320XP PHG 4L280XP PHG 4L230XP  PHG 5L360XP PHG 5L440XP PHG 5L930XP PHG 5L520XP PHG 5L960XP  PHG B79 PHG B84 PHG 5L930XP PHG 5L870XP PHG 4L360XP  PHG 5L910XP PHG 5L820XP PHG 5L560XP PHG 5L690XP PHG B82  PHG 5L680XP PHG 5L620XP PHG 5L620XP PHG 5L640XP PHG 5L690XP  PHG 4L350XP PHG 4L350XP PHG 3L260XP PHG 3L360XP PHG 5L460XP  PHG 5L520XP PHG 5L530XP PHG 5L500XP PHG 5L210XP PHG 4L350XP  PHG 4L360XP PHG 5L1010XP PHG 4L310XP PHG 5L520XP PHG 5L870XP  PHG 5L360XP PHG BX42 PHG 5L820XP PHG 5L640XP PHG 4L380XP  PHG 4L410XP  PHG 4L1080XP PHG 3L220XP PHG 3L270XP PHG 3L220XP PHG 4L240XP  PHG 4L290XP PHG 4L310XP PHG 4L360XP PHG 4L240XP PHG 4L460XP  PHG 5L390XP PHG 4L700XP PHG 5L580XP PHG 5L630XP PHG 4L760XP  PHG 4L710XP PHG 4L800XP PHG 4L560XP PHG 4L210XP PHG 3L280XP  PHG 4L380XP PHG 3L320XP PHG 4L540XP PHG 5L590XP PHG 5L560XP  PHG 3L490XP



Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Bolens</b>	170399	PHG 4L440XP	<b>Bolens</b>	1714690	PHG 4L320XP	<b>Bolens</b>	1739943	PHG 3L310XP
	170647	PHG 4L440XP		1714799	PHG 4L750XP		1739944	PHG 4L350XP
	170696	PHG 4L440XP		1715010	PHG 3L340XP		1739945	PHG 4L350XP
	170738	PHG 3L470XP		1715213	PHG 4L610XP		1741135	PHG 4L710XP
	170746	PHG 3L490XP		1715611	PHG 3L250XP		1741334	PHG 4L450XP
	170829	PHG 3L380XP		1715612	PHG 3L320XP		1741568	PHG 4L950XP
	173574	PHG 4L540XP		1715614	PHG 3L280XP		1741576	PHG 4L810XP
	174576	PHG 4L810XP		1715621	PHG 3L300XP		1741577	PHG 4L830XP
	177844	PHG 4L360XP		1715740	PHG 5L430XP		1741578	PHG 4L430XP
	200555	PHG 3L460XP		1715942	PHG 4L470XP		1743816	PHG 4L980XP
	205656	PHG 4L240XP		1715972	PHG 4L380XP		1743876	PHG 4L980XP
	212261	PHG 4L870XP		1716036	PHG 3L310XP		1744493	PHG 4L800XP
	213676	PHG 4L850XP		1716161	PHG 4L310XP		1746379	PHG 3L340XP
	217773	PHG 4L400XP		1716307	PHG 4L700XP		1747188	PHG 4L970XP
	421313	PHG 4L310XP		1716407	PHG 4L700XP		1747938	PHG 4L960XP
	421321	PHG 4L360XP		1716551	PHG 4L850XP		1751597	PHG 4L910XP
	421339	PHG 4L320XP		1716557	PHG 4L850XP		1752194	PHG 3L360XP
	421412	PHG 3L210XP		1716570	PHG 4L430XP		1760958	PHG 4L620XP
	618819	PHG 4L430XP		1716571	PHG 4L340XP		1800367	PHG 4L330XP
	751597	PHG 4L910XP		1716580	PHG 4L430XP		1813220	PHG 4L350XP
	1105034	PHG 4L350XP		1717120	PHG 4L440XP		1813271	PHG 4L550XP
	1108453	PHG 4L200XP		1717195	PHG 4L580XP		1813561	PHG 4L550XP
	1108455	PHG 4L220XP		1717837	PHG 4L600XP		1894063	PHG 3L280XP
	1108456	PHG 4L320XP		1717861	PHG 4L560XP		1894272	PHG 3L350XP
	1108460	PHG 4L250XP		1719203	PHG 4L320XP		1894335	PHG 3L360XP
	1108461	PHG 4L280XP		1719269	PHG 3L250XP		7523058	PHG 4L280XP
	1108462	PHG 4L290XP		1719731	PHG 4L630XP		7524026	PHG 4L300XP
	1108463	PHG 4L300XP		1719783	PHG 4L410XP		7524058	PHG 4L460XP
	1108464	PHG 4L310XP		1720131	PHG 4L440XP		17413342	PHG 4L450XP
	1108466	PHG 4L330XP		1720572	PHG 4L300XP		18161410	PHG 5L350XP
	1108467	PHG 4L340XP		1720573	PHG 4L300XP		18183220	PHG 4L350XP
	1108470	PHG 4L350XP		1720726	PHG 4L330XP		65800530	PHG 4L550XP
	1108473	PHG 4L400XP		1720727	PHG 4L460XP		95800500	PHG 4L350XP
	1108474	PHG 4L410XP		1720938	PHG 3L360XP		658500530	PHG 4L550XP
	1108475	PHG 4L420XP		1721574	PHG 4L620XP		958500500	PHG 4L350XP
	1108476	PHG 4L430XP		1721967	PHG 4L520XP		754-0326A	PHG 4L620XP
	1108481	PHG 4L480XP		1722074	PHG 5L350XP		754-04003	PHG 3L320XP
	1108485	PHG 4L520XP		1722095	PHG 5L440XP		754-04003A	PHG 3L200XP
	1108501	PHG 4L680XP		1722238	PHG 4L650XP		92006D	PHG 4L220XP
	1108536	PHG 5L270XP		1722258	PHG 4L310XP		92016D	PHG 4L240XP
	1108539	PHG 5L300XP		1722344	PHG 4L620XP		954-04285	PHG 5L350XP
	1108547	PHG 5L380XP		1722523	PHG 4L490XP		B237453	PHG 4L290XP
	1108552	PHG 5L430XP		1722639	PHG 4L350XP		P406416	PHG 4L420XP
	1108554	PHG 5L450XP		1723056	PHG 4L540XP		T236321	PHG 4L570XP
	1108576	PHG 5L670XP		1723060	PHG 4L510XP		T239661	PHG 3L360XP
	1108743	PHG 4L400XP		1723661	PHG 3L410XP		W51350	PHG 5L350XP
	1113533	PHG 3L330XP		1724035	PHG 4L680XP		W562905P1	PHG 5L290XP
	1113852	PHG 4L570XP		1724072	PHG 4L350XP		W5290	PHG 5L290XP
	1124148	PHG 4L750XP		1724148	PHG 4L750XP		W51290	PHG 5L290XP
	1185434	PHG 3L370XP		1724261	PHG 4L510XP			
	1185481	PHG 3L320XP		1724729	PHG 4L350XP	<b>Briggs &amp; Stratton</b>	1245	PHG 5L240XP
	1185487	PHG 3L320XP		1725253	PHG 4L340XP		1254	PHG 4L490XP
	1236321	PHG 4L570XP		1725407	PHG 4L350XP		1256	PHG 4L330XP
	1705033	PHG 4L220XP		1725603	PHG 4L430XP		1257	PHG 4L650XP
	1705034	PHG 4L350XP		1726701	PHG 4L770XP		10716	PHG 4L350XP
	1705326	PHG 4L350XP		1726929	PHG 4L380XP		11361	PHG 4L760XP
	1706907	PHG 4L240XP		1728133	PHG 4L920XP		11483	PHG 5L430XP
	1707233	PHG 4L260XP		1729716	PHG 5L460XP		11904	PHG 4L910XP
	1708425	PHG 4L280XP		1731719	PHG 4L510XP		12903	PHG 4L580XP
	1709698	PHG 5L430XP		1732126	PHG 4L710XP		16297	PHG 5L770XP
	1711844	PHG 4L360XP		1732171	PHG 3L430XP		20117	PHG 4L560XP
	1711845	PHG 5L440XP		1732582	PHG 4L310XP		20551	PHG 4L440XP
	1711916	PHG 4L390XP		1732726	PHG 4L710XP		20555	PHG 4L440XP
	1712687	PHG 4L470XP		1732880	PHG 4L430XP		20556	PHG 4L800XP
	1713067	PHG 4L290XP		1733439	PHG 4L350XP		20558	PHG 4L640XP
	1713533	PHG 3L330XP		1736248	PHG 4L640XP		20715	PHG 4L350XP
	1713714	PHG 4L430XP		1736259	PHG 4L340XP		20716	PHG 4L350XP
	1713716	PHG 4L350XP		1736279	PHG 4L360XP		20717	PHG 4L560XP
	1713852	PHG 4L570XP		1736903	PHG 4L1000XP		21049	PHG 4L550XP
	1713853	PHG 4L570XP		1737187	PHG 5L950XP		21058	PHG 4L630XP
	1714106	PHG 4L210XP		1737347	PHG 4L690XP		21059	PHG 4L440XP
	1714107	PHG 4L460XP		1737459	PHG 4L590XP		21508	PHG 4L630XP
	1714115	PHG 4L330XP		1737574	PHG 4L540XP		21614	PHG 4L850XP
	1714285	PHG 4L230XP		1738496	PHG 4L650XP		23072	PHG 4L430XP
	1714286	PHG 4L480XP		1738511	PHG 4L660XP		23098	PHG 4L620XP
	1714513	PHG 3L230XP		1739080	PHG 4L790XP		23148	PHG 4L620XP
							23347	PHG 4L820XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Briggs & Stratton	23496	PHG 4L740XP	Briggs & Stratton	037X89MA	PHG 4L890XP	Briggs & Stratton	37X68	PHG 4L1010XP
	23796	PHG 4L590XP		037X92	PHG 4L530XP		37X69	PHG 4L800XP
	23853	PHG 4L430XP		037X92MA	PHG 4L530XP		37X7	PHG 4L560XP
	23882	PHG 4L590XP		037X93	PHG 5L1090XP		37X70	PHG 4L770XP
	24116	PHG 4L950XP		037X93MA	PHG 5L1090XP		37X71	PHG 4L560XP
	24176	PHG 4L950XP		037X94	PHG 3L340XP		37X75	PHG 4L910XP
	24256	PHG 4L880XP		037X94MA	PHG 3L340XP		37X80	PHG 4L860XP
	75121	PHG 4L480XP		037X96	PHG 4L890XP		37X86	PHG 4L840XP
	75147	PHG 3L390XP		037X96MA	PHG 4L890XP		37X87	PHG 4L970XP
	75370	PHG 3L260XP		1713549SM	PHG 4L700XP		37X88	PHG 4L880XP
	199612	PHG 4L970XP		1719911SM	PHG 4L1170XP		37X89	PHG 4L860XP
	201153	PHG 4L620XP		1732955SM	PHG 4L940XP		37X9	PHG 4L440XP
	700123	PHG 5L350XP		1734048SM	PHG 4L1030XP		37X92	PHG 4L530XP
	703761	PHG 3L310XP		1734130SM	PHG 4L700XP		37X93	PHG 5L1090XP
	7100883	PHG 3L210XP		1737441YP	PHG 4L880XP		37X94	PHG 3L340XP
	0037X3	PHG 4L460XP		1751417YP	PHG AX36		37X96	PHG 4L890XP
	0037X3MA	PHG 4L460XP		20557	PHG 4L460XP		579932MA	PHG 3L330XP
	037X12	PHG 4L550XP		21615	PHG 4L950XP		7035500YP	PHG 4L840XP
	037X12MA	PHG 4L550XP		21649	PHG 4L550XP		7101749MA	PHG 4L970XP
	037X22	PHG 4L990XP		23748	PHG 4L620XP		7101794YP	PHG 4L890XP
	037X22MA	PHG 4L990XP		23749	PHG 4L990XP		710193	PHG 4L840XP
	037X26	PHG 4L880XP		27X27	PHG 4L830XP		710209	PHG 4L860XP
	037X26MA	PHG 4L880XP		333721MA	PHG 10PJ350		710213	PHG 4L880XP
	037X38	PHG 4L400XP		37X1	PHG 4L560XP		710216	PHG 4L470XP
	037X38MA	PHG 4L400XP		37X10	PHG 4L850XP		710217	PHG 4L890XP
	037X40	PHG 4L620XP		37X100	PHG 3L340XP		7103362YP	PHG 3L320XP
	037X40MA	PHG 4L620XP		37X100MA	PHG 3L340XP		7103364YP	PHG 3L320XP
	037X43	PHG 4L830XP		37X101	PHG 3L340XP		710341	PHG 4L970XP
	037X43MA	PHG 4L830XP		37X101MA	PHG 3L340XP		7104084YP	PHG 3L330XP
	037X45	PHG 4L910XP		37X106MA	PHG 4L890XP		710531	PHG 4L950XP
	037X45MA	PHG 4L910XP		37X11	PHG 4L950XP		760976MA	PHG 3L350XP
	037X57	PHG 4L540XP		37X110	PHG 4L440XP		761788MA	PHG 4L390XP
	037X57A	PHG 4L540XP		37X110MA	PHG 4L440XP		885495YP	PHG 4L810XP
	037X57MA	PHG 4L540XP		37X112MA	PHG 5L660XP		885895YP	PHG 4L800XP
	037X61	PHG 4L950XP		37X12	PHG 4L550XP		954-04259A	PHG 4L340XP
	037X61AMA	PHG 4L950XP		37X13	PHG 3L410XP		954-04285	PHG 5L350XP
	037X61MA	PHG 4L950XP		37X131MA	PHG 4L410XP		954-0469A	PHG 5L910XP
	037X61WMA	PHG 4L950XP		37X135MA	PHG 3L350XP		954-05001	PHG 4L430XP
	037X62	PHG 4L860XP		37X14	PHG 4L430XP		MT1736421YP	PHG 4L380XP
	037X62A	PHG 4L860XP		37X15	PHG 4L620XP		MT333721MA	PHG 10PJ350
	037X62MA	PHG 4L860XP		37X16	PHG 4L590XP		MT37X132	PHG 3L350XP
	037X62WMA	PHG 4L860XP		37X17	PHG 4L940XP		MT579932	PHG 3L330XP
	037X63	PHG 4L830XP		37X21	PHG 4L620XP		MT579932MA	PHG 3L330XP
	037X63A	PHG 4L830XP		37X22	PHG 4L990XP		MT585416	PHG 4L380XP
	037X63MA	PHG 4L830XP		37X23	PHG 4L430XP		MT585416MA	PHG 4L380XP
	037X65	PHG 4L300XP		37X25	PHG 3L380XP		MU037X74MA	PHG 4L570XP
	037X65MA	PHG 4L300XP		37X26	PHG 4L880XP		MU037X87	PHG 4L970XP
	037X66	PHG 4L470XP		37X27	PHG 4L830XP		MU037X87MA	PHG 4L970XP
	037X66MA	PHG 4L470XP		37X28	PHG 4L480XP		MU1742461YP	PHG 4L570XP
	037X68	PHG 4L1010XP		37X29	PHG 3L390XP		MU37X110	PHG 4L440XP
	037X68MA	PHG 4L1010XP		37X3	PHG 4L460XP		MU37X110MA	PHG 4L450XP
	037X69	PHG 4L800XP		37X31	PHG 4L930XP		MU37X57	PHG 4L540XP
	037X69MA	PHG 4L800XP		37X32	PHG 4L450XP		MU37X65	PHG 4L300XP
	037X70	PHG 4L770XP		37X34	PHG 4L770XP			
	037X70A	PHG 4L770XP		37X36	PHG 4L550XP			
	037X70MA	PHG 4L770XP		37X37	PHG 4L500XP	Bunton	4733	PHG 5L570XP
	037X74MA	PHG 4L570XP		37X38	PHG 4L400XP		6851	PHG 4L320XP
	037X75	PHG 4L910XP		37X39	PHG 4L830XP		H121	PHG 4L540XP
	037X75A	PHG 4L910XP		37X40	PHG 4L620XP		L148	PHG 4L280XP
	037X75MA	PHG 4L910XP		37X43	PHG 4L830XP		L19	PHG 4L360XP
	037X75WMA	PHG 4L910XP		37X45	PHG 4L910XP		L20	PHG 4L350XP
	037X80	PHG 4L860XP		37X46	PHG 4L250XP		L21	PHG 4L390XP
	037X80MA	PHG 4L860XP		37X48	PHG 4L730XP		L643	PHG 4L500XP
	037X86	PHG 4L840XP		37X5	PHG 4L350XP		P78153	PHG 5L470XP
	037X86A	PHG 4L840XP		37X50	PHG 4L540XP		PL0019	PHG 4L360XP
	037X86MA	PHG 4L840XP		37X51	PHG 4L360XP		PL0020	PHG 4L350XP
	037X87	PHG 4L970XP		37X55	PHG 4L910XP		PL0021	PHG 4L380XP
	037X87MA	PHG 4L970XP		37X56	PHG 4L820XP		PL0148	PHG 4L280XP
	037X88	PHG 4L880XP		37X57	PHG 4L540XP		PL029	PHG 5L440XP
	037X88A	PHG 4L880XP		37X59	PHG 4L790XP		PL0511	PHG 5L540XP
	037X88HDMA	PHG 4L880XP		37X6	PHG 4L350XP		PL0543	PHG 4L430XP
	037X88MA	PHG 4L880XP		37X61	PHG 4L950XP		PL0619	PHG 5L440XP
	037X88WMA	PHG 4L880XP		37X62	PHG 4L860XP		PL0661	PHG 5L580XP
	037X89	PHG 4L890XP		37X63	PHG 4L830XP		PL0679	PHG 5L660XP
	037X89A	PHG 4L890XP		37X65	PHG 4L300XP		PL0848	PHG 5L400XP
	037X89HDMA	PHG 4L890XP		37X66	PHG 4L470XP		PL0861	PHG 5L460XP
							PL8002	PHG 5L440XP

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Bunton</b>	PL8153	PHG 5L470XP	<b>Craftsman</b>	139573	PHG 4L840XP	<b>Craftsman</b>	438485	PHG 3L320XP
<b>Craftsman</b>	23749	PHG 4L990XP		140067	PHG 4L830XP		48044MA	PHG 5L820XP
	46989	PHG 4L550XP		140218	PHG 4L850XP		49570	PHG 4L350XP
	47846	PHG 5L1140XP		140294	PHG 4L820XP		49570MA	PHG 4L350XP
	48922	PHG 6PJ350		144200	PHG 4L890XP		49581	PHG SPA932
	50273	PHG 3L340XP		144959	PHG 4L960XP		49581MA	PHG SPA932
	51249	PHG 3L340XP		144959D	PHG 4L950XP		50272	PHG 4L350XP
	110883	PHG 4L990XP		146527	PHG 3L320XP		50307	PHG 3L280XP
	137589	PHG 4L860XP		147883	PHG 4L340XP		50441	PHG 5L820XP
	161588	PHG 4L830XP		148763	PHG B83		51304	PHG SPA932
	165631	PHG 4L1110XP		156971	PHG 4L820XP		5262J	PHG 4L390XP
	165813	PHG 4L850XP		157769	PHG 3L320XP		532138255	PHG 4L950XP
	170140	PHG 4L1120XP		160855	PHG 4L950XP		585416MA	PHG 4L380XP
	179092	PHG A32		161597	PHG 4L830XP		585436MA	PHG 4L380XP
	180213	PHG 4L830XP		1629J	PHG 4L830XP		62828	PHG 4L700XP
	180215	OE Only		1665450SM	PHG 4L870XP		6474H	PHG 5L810XP
	191723	PHG 5L1430XP		1666801SM	PHG 4L800XP		7022252YP	PHG 4L730XP
	199612	PHG 4L970XP		16710765M	PHG 4L980XP		7074J	PHG 4L650XP
	313821	PHG 3L340XP		169178	PHG AA112		71001025M	PHG 4L580XP
	319596	PHG 6PJ350		17213935M	PHG 4L940XP		7103789YP	PHG 5L1660XP
	325890	PHG 3L350XP		17220395M	PHG 4L720XP		73794	PHG 4L940XP
	333721	PHG 10PJ350		1726470SM	PHG 4L380XP		754-0101A	PHG 3L350XP
	333914	PHG 10PJ350		1726471SM	PHG 4L730XP		754-0343	PHG 3L310XP
	401603	PHG 4L950XP		1726472SM	PHG 4L910XP		754-0346	PHG 3L300XP
	402008	OE Only		17268415M	PHG 4L940XP		754-0367	PHG 4L340XP
	402009	OE Only		1727773SM	PHG 4L700XP		754-04013	PHG 3L210XP
	405075	PHG 4L840XP		17278695M	PHG 4L830XP		754-04050	PHG AX33
	416954	PHG A32		17322045M	PHG 4L910XP		754-04102	PHG 3L250XP
	419271	OE Only		17322245M	PHG 4L540XP		754-04131	PHG 4L420XP
	419744	PHG A32		17329565M	PHG 4L1180XP		754-04139	PHG 4L720XP
	429636	PHG 4L1010XP		17329665M	PHG 4L1180XP		754-04145	PHG 4L640XP
	581264	PHG 4L350XP		17333245M	PHG 3L330XP		754-04194	PHG 4L450XP
	585416	PHG 4L380XP		17341315M	PHG 4L730XP		754-04194A	PHG 4L450XP
	585436	PHG 4L380XP		1736421YP	PHG 4L380XP		754-04195	PHG AX35
	760928	PHG 3L350XP		1736516VP	PHG 4L1320XP		754-04204	PHG AX34
	1726470	PHG 4L380XP		174368	PHG 5L900XP		754-0430	PHG 3L350XP
	1726471	PHG 4L730XP		174883	PHG 4L340XP		754-0430B	PHG 3VX350
	2002648	PHG 4L580XP		1751423YP	PHG 4L890XP		754-0453	PHG 5L360XP
	4143733	PHG 5L1510XP		1752103YP	PHG 5L850XP		754-0460	PHG 3L390XP
	90003526	PHG 4L300XP		175436	PHG 3L320XP		754-0493	PHG 5L580XP
	532197253	PHG 4L1010XP		177J	PHG 5L430XP		754-0494	PHG 5L420XP
	532405143	PHG 4L1070XP		178138	PHG 4L870XP		754-0754	PHG 5L520XP
	532429636	PHG 4L1010XP		178J	PHG 5L530XP		760928MA	PHG 3L350XP
	120302X	PHG 4L900XP		180214	PHG 4L870XP		770061MA	PHG 3L340XP
	754-0131	PHG 3L350XP		180217	PHG 4L870XP		83691	PHG 3L350XP
	754-0222A	PHG 4L440XP		180808	PHG 5L890XP		88519	PHG 3L400XP
	754-04014	PHG 3L270XP		183688	PHG 3L340XP		954-0101A	PHG 3L350XP
	754-04201A	PHG 3L360XP		191273	PHG 5L1430XP		954-0101A	PHG 4L350XP
	954-04050	PHG 4L350XP		193214	PHG 4L920XP		954-0201	PHG 4L410XP
	954-04202	PHG 3L360XP		194346	PHG 4L970XP		954-0222A	PHG 4L440XP
	954-04260	PHG 3L340XP		196103	PHG 5L1480XP		954-0241A	PHG 5L350XP
	037X22MA	PHG 4L990XP		197242	PHG 5L1400XP		954-0346	PHG 3L300XP
	037X38MA	PHG 4L400XP		197253	PHG 4L1010XP		954-0367	PHG 4L340XP
	037X40MA	PHG 4L620XP		2692R	PHG 5L830XP		954-04013	PHG 3L210XP
	037X43MA	PHG 4L830XP		313821MA	PHG 3L340XP		954-04014	PHG 3L270XP
	037X44MA	PHG 4L500XP		319596MA	PHG 6PJ350		954-04043B	PHG 4L570XP
	037X45MA	PHG 4L910XP		325890MA	PHG 3L350XP		954-04044A	PHG 4L1340XP
	037X57MA	PHG 4L540XP		3526MA	PHG 4L300XP		954-04050	PHG AX33
	037X61MA	PHG 4L950XP		37X110	PHG 4L440XP		954-04060B	PHG 4L970XP
	037X62MA	PHG 4L860XP		37X110MA	PHG 4L440XP		954-04062	PHG 4L770XP
	037X65MA	PHG 4L300XP		37X111	PHG 4L450XP		954-04083	PHG 5L1380XP
	106085X	PHG 4L790XP		37X111MA	PHG 4L450XP		954-04102	PHG 3L250XP
	106381X	PHG 4L920XP		37X120MA	OE Only		954-04104A	PHG 4L450XP
	108429X	PHG 4L390XP		37X130MA	PHG 10PJ350		954-04131	PHG 4L420XP
	110883X	PHG 4L990XP		37X26	PHG 4L880XP		954-04137A	PHG 4L1140XP
	110884X	PHG 4L940XP		37X38	PHG 4L400XP		954-04139	PHG 4L720XP
	123796X	PHG 4L950XP		37X57	PHG 4L540XP		954-04145A	PHG 4L640XP
	125907X	PHG 4L900XP		37X65	PHG 4L300XP		954-04158	PHG 3L320XP
	130801	PHG 4L950XP		39454	PHG 4L880XP		954-04185	PHG 4L890XP
	130969	PHG 4L930XP		39454MA	PHG 4L880XP		954-04194A(x6)	PHG 4L450XP
	131006	PHG 4L990XP		405143	PHG 4L1070XP		954-04195	PHG AX35
	131264	PHG 4L790XP		40899	PHG 4L350XP		954-04201	PHG 3VX360
	131290	PHG 4L880XP		41740	PHG 4L380XP		954-04201A	PHG 3VX360
	137078	PHG 3L320XP		41740MA	PHG 4L380XP		954-04204	PHG AX34
	137153	PHG 4L840XP		43066	PHG 5L710XP		954-04207	PHG 4L790XP
	138255	PHG 4L950XP		43066MA	PHG 5L710XP		954-04208	PHG 5L410XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Craftsman</b>	954-04219 954-04240 954-04244A 954-04249 954-04249A  954-04252 954-04263 954-04265 954-0430B 954-04318  954-04331 954-0453 954-0460 954-0467A 954-0493  954-0494 954-0754 STD324695 STD324830 STD324940  STD324990 STD325810 STD325811 TH3H340 TH5H710	PHG 4L1030XP PHG 4L1630XP PHG 4L770XP PHG 5L710XP PHG 5L710XP  PHG 4L630XP PHG 5L400XP PHG 4L330XP PHG 3VX350 PHG 5L450XP  PHG 5L350XP PHG 5L360XP PHG 3L390XP PHG 5L910XP PHG 5L580XP  PHG 5L420XP PHG 5L520XP PHG 4L700XP PHG 4L830XP PHG 4L940XP  PHG 4L990XP PHG 5L810XP PHG 5L810XP PHG 3L340XP PHG 5L710XP	<b>Cub Cadet</b>	00050441P 1004752 473468R2 488077R1 489399R1  490489R2 493649R1 50441P 754-0295 754-0330  754-0339 754-0349 754-0352 754-04001A 754-04002  754-04033 754-04033A 754-04041 754-04043 754-04043A  754-04043B 754-04044 754-04044A 754-04045 754-04048	PHG 5L820XP PHG 4L1200XP PHG 4L720XP PHG 4L480XP PHG 4L800XP  PHG 4L810XP PHG 4L730XP PHG 5L820XP PHG 4L1110XP PHG 4L900XP  PHG 4L790XP PHG A77 PHG 4L480XP PHG 5L700XP PHG 5L320XP  PHG 4L1180XP PHG 4L1180XP PHG 5L1110XP PHG 4L580XP PHG 4L580XP  PHG 4L580XP PHG 4L1340XP PHG 4L1340XP PHG 4L1090XP PHG 5L1300XP	<b>Cub Cadet</b>	954-0266A 954-04001 954-04002 954-04032B 954-04033  954-04033A 954-04043 954-04043A 954-04043B 954-04044  954-04044A 954-04045 954-04048 954-04057 954-04060  954-04060A 954-04060B  954-04244A 954-0467 954-0467A 954-0475 954-0498  954-0498 954-0640 954-0642 954-0644 954-0645  954-0645A 954-3036 954-3038 954-3092A 954-4062 954-4077  WM-18879 WM-53418  1611 1714 1765 1860 2412  2426 2469 4812 6111 6360  6938 6939 7725 9236	PHG 4L850XP PHG 5L700XP PHG 5L320XP PHG 3L360XP PHG 4L1180XP  PHG 4L1180XP PHG 4L570XP PHG 4L570XP PHG 4L570XP PHG 4L1340XP  PHG 4L1340XP PHG 4L1090XP PHG 5L1300XP PHG 5L350XP PHG 4L960XP  PHG 4L960XP PHG 4L970XP PHG 4L1220XP PHG 4L1140XP PHG 5L1430XP  PHG 4L720XP PHG 4L910XP PHG 4L640XP PHG 4L1220XP PHG 4L1220XP  PHG 3L320XP PHG 4L790XP PHG 5L410XP PHG 4L1030XP PHG 4L1630XP  PHG 4L770XP PHG 5L910XP PHG 5L910XP PHG 4L670XP  PHG 4L660XP PHG 5L790XP PHG 5L1380XP PHG 4L600XP PHG 4L670XP  PHG 4L670XP PHG 4L630XP PHG 4L610XP PHG 4L1070XP PHG 4L1120XP  PHG 5L1110XP PHG 4L620XP PHG 4L640XP PHG 4L780XP PHG 5L1340XP  PHG 5L1330XP PHG 5L1580XP  PHG 5L780XP PHG 4L520XP PHG 4L260XP PHG 4L570XP PHG 5L740XP  PHG 5L440XP PHG 4L450XP PHG 4L660XP PHG 5L780XP PHG 5L850XP  PHG 5L380XP PHG 5L390XP PHG 5L720XP PHG 5L930XP  PHG 4L500XP PHG 5L620XP  PHG 5L820XP PHG 5L440XP  PHG 4L440XP  PHG 4L290XP PHG 4L350XP PHG 5L880XP
<b>Cub Cadet</b>	50441 106465 106990 106991 135469  700399 702391 704752 705011 705012  708349 720103 1000399 1001315 1002391  1002391 1002932 1003968 1004315 1004752  1004752 1005011 1005012 1005374 1005375  1005376 1005377 1005378 1007015 1007937  1008349 1008349 1009719 1009719 1009787  2000103 2000154 2000611 2000653 2002648  2004377 2005168 754-0271 754-04047 754-3038  754-3068 954-0197 954-04082A 954-04250 954-04262  954-0460	PHG 5L820XP PHG 4L510XP PHG 4L450XP PHG 4L550XP PHG 5L890XP  PHG 4L1070XP PHG 5L630XP PHG 5L1190XP PHG 5L830XP PHG 5L840XP  PHG 4L550XP PHG 4L810XP PHG 4L1070XP PHG 5L840XP PHG 5L620XP  PHG 5L630XP PHG 4L1170XP PHG 5L830XP PHG 5L840XP PHG 4L1170XP  PHG 5L1190XP PHG 5L830XP PHG 5L840XP PHG 4L1050XP PHG 4L1140XP  PHG 4L1220XP PHG 5L910XP PHG 5L870XP PHG 4L510XP PHG 5L1230XP  PHG 4L550XP PHG 5L550XP PHG 5L550XP PHG 5L590XP PHG 5L800XP  PHG 4L810XP PHG 4L830XP PHG 5L1550XP PHG 4L910XP PHG 4L580XP  PHG B107 PHG 5L860XP PHG 3L390XP PHG 4L1140XP PHG 4L610XP  PHG 5L1100XP PHG 4L1170XP PHG 3L320XP PHG 4L630XP PHG 5L910XP  PHG 3L390XP	754-04055 754-04057 754-04060 754-04060A 754-04060B  754-04062 754-04064 754-04077 754-04118 754-04122  754-04142 754-04153 754-04153A 754-04165 754-04188  754-04219 754-04240 754-04297 754-0441 754-0460  754-0461 754-0640 754-0644 754-0645 754-0645A  754-3005 754-3009 754-3010 754-3011 754-3018  754-3019 754-3024 754-3025 754-3026 754-3026A  754-3027 754-3029 754-3030 754-3035 754-3036  754-3037 754-3039 754-3041 754-3055 754-3055A  754-3068 754-3073 754-3075 954-0178 954-0201  954-0241A	PHG 5L1110XP PHG 5L350XP PHG 4L960XP PHG 4L960XP PHG 4L960XP  PHG 4L770XP PHG 5L680XP PHG 5L1340XP PHG 5L1220XP PHG 4L900XP  PHG 4L910XP PHG 4L1220XP PHG 4L1220XP PHG 4L780XP PHG 4L180XP  PHG 4L1030XP PHG 4L1620XP PHG 4L850XP PHG 4L760XP PHG 3L390XP  PHG 4L780XP PHG 5L790XP PHG 4L600XP PHG 4L670XP PHG 4L670XP  PHG 4L860XP PHG 4L680XP PHG 4L300XP PHG 4L690XP PHG 4L860XP  PHG 4L710XP PHG 4L910XP PHG 4L770XP PHG 4L600XP PHG 4L600XP  PHG 4L860XP PHG 4L590XP PHG 4L590XP PHG 4L900XP PHG 4L630XP  PHG 4L800XP PHG 4L1030XP PHG 4L1050XP PHG 5L1130XP PHG 5L1130XP  PHG 5L1110XP PHG 4L620XP PHG 5L780XP PHG 4L410XP  PHG 4L800XP PHG 4L1030XP PHG 4L1050XP PHG 5L1130XP PHG 5L1130XP  PHG 5L1110XP PHG 4L620XP PHG 5L780XP PHG 4L410XP  PHG 5L350XP	<b>Dixon</b>	20560 20939  363210 363211  716910  213076 213077 232300		

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Exmark</b>	303078 303079 303080 323017 323051  323200 323225 323300 403018 403024  403025 413094 543548 603045 603306  603809 303080A DH3012	PHG 5L360XP PHG B41 PHG 5L890XP PHG 5L850XP PHG 5L440XP  PHG 5L880XP PHG 5L520XP PHG 5L880XP PHG 3L360XP PHG 5L940XP  PHG 5L520XP PHG 5L1040XP PHG 4L370XP PHG 4L1110XP PHG 5L810XP  PHG 5L600XP PHG 5L890XP PHG 5L520XP	<b>Gilson</b>	18263 24602 24615 26345 26873  27093 27666 35545 36019 36770  36806 37156 37169 37230 37756  200414 200416 200554 200555 200624	PHG 4L440XP PHG 4L990XP PHG 4L640XP PHG 4L300XP PHG 4L670XP  PHG 4L470XP PHG 4L1020XP PHG 4L400XP PHG 3L200XP PHG 4L350XP  PHG 5L530XP PHG 4L560XP PHG 4L360XP PHG 4L380XP PHG 4L560XP  PHG 4L830XP PHG 4L320XP PHG 4L460XP PHG 3L460XP PHG 5L800XP	<b>Gravely</b>	7225800 954-771	PHG AX51 PHG 3L350XP
						<b>Haban</b>	10467	PHG 4L520XP
						<b>Homelite</b>	9304 66455 66818 105340 108248  108428 108505 108508 114364 120178  123073 158573 161098 162081 165048	PHG 4L290XP PHG 4L510XP PHG 4L380XP PHG 5L960XP PHG 4L800XP  PHG 4L480XP PHG 4L700XP PHG 4L780XP PHG 4L900XP PHG 4L350XP  PHG 4L910XP PHG 4L310XP PHG 4L390XP PHG 4L760XP PHG 4L850XP
<b>Ford</b>	2435 200555 240684 240773	PHG 4L320XP PHG 3L460XP PHG 3L460XP PHG 4L740XP		200625 200626 200804 200973 200982	PHG 4L560XP PHG 5L400XP PHG 4L740XP PHG 4L780XP PHG 4L780XP		174364 174731 174883 176393 176439	PHG 4L490XP PHG 4L530XP PHG 4L340XP PHG 3L370XP PHG 4L740XP
<b>Gilson</b>	930 1040 1110 1409 1434  1526 2434 2435 3053 3660  3866 4051 4052 4638 6163  6184 7740 7838 9303 9304  9305 9308 10463 10755 10855  10897 10923 11144 11193 11792  11793 11901 11943 12023 12570  12684 13009 13072 13436 14156  14159 14167 14168 14365 14790  14843 16146 16348 16366 16386  17518 17569 17653 18055	PHG 4L520XP PHG 4L320XP PHG 4L350XP PHG 5L520XP PHG 3L280XP  PHG 4L220XP PHG 4L340XP PHG 4L350XP PHG 4L440XP PHG 4L250XP  PHG 4L260XP PHG 3L310XP PHG 4L550XP PHG 4L300XP PHG 3L370XP  PHG 3L390XP PHG 4L380XP PHG 3L340XP PHG 3L250XP PHG 4L290XP  PHG 4L520XP PHG 4L250XP PHG 4L350XP PHG 4L430XP PHG 4L300XP  PHG 4L510XP PHG 4L300XP PHG 4L350XP PHG 5L890XP PHG 5L960XP  PHG 5L900XP PHG 4L360XP PHG 5L350XP PHG 3L210XP PHG 5L560XP  PHG 5L960XP PHG 4L410XP PHG 4L720XP PHG 4L540XP PHG 4L400XP  PHG 4L400XP PHG 4L650XP PHG 4L510XP PHG 4L510XP PHG 4L380XP  PHG 4L290XP PHG 4L390XP PHG 4L380XP PHG 4L350XP PHG 4L400XP  PHG 5L600XP PHG 4L430XP PHG 4L470XP PHG 4L300XP		200983 207925 208301 208525 208526  208527 208626 208827 209310 209373  209375 209581 209630 211173 211650  212086 212221 212261 212776 213676  214110 216594 239024 239025 240684  240773 243110 2004H 208527 4816G  83EA335 GB213676 H09 H34  H843  381100 381914 382000 382037 382049  382730 382750 382800 383000  41545 49029 72224 72250 72258	PHG 5L810XP PHG 3L320XP PHG 4L330XP PHG 3L250XP PHG 3L380XP  PHG 4L480XP PHG 3L270XP PHG 4L800XP PHG 4L390XP PHG 4L410XP  PHG 4L440XP PHG 4L860XP PHG 4L390XP PHG 4L400XP PHG 3L330XP  PHG 4L400XP PHG 4L390XP PHG 4L870XP PHG 4L660XP PHG 4L850XP  PHG 4L580XP PHG 4L1020XP PHG 5L990XP PHG 5L830XP PHG 3L460XP  PHG 4L740XP PHG 4L500XP PHG 4L830XP PHG 4L480XP PHG 4L870XP  PHG 5L580XP PHG 4L850XP PHG 4L860XP PHG 5L520XP PHG 3L280XP  PHG 4L290XP  PHG 5L290XP PHG 4L360XP PHG 5L330XP PHG 5L650XP PHG 5L820XP  PHG 5L350XP PHG 5L390XP PHG 5L520XP PHG 5L900XP  PHG 4L350XP PHG AX45 PHG AX45 PHG AX35 PHG AX51	<b>Gravely</b>	7618175003 22431723772 22431727003 22431736003 22431738003	PHG 5L670XP PHG 3L350XP PHG 5L390XP PHG 4L350XP PHG 4L330XP
						<b>Homko</b>	20317 20582	PHG 4L200XP PHG 4L430XP
						<b>Honda</b>	12151 40206 41562 47562 47765  68851 68851 74313 75624 78838  101316 103641 106375 126151 2487494	PHG 4L780XP PHG 4L730XP PHG 4L920XP PHG 4L820XP PHG 4L830XP  PHG 4L700XP PHG 4L690XP PHG 4L520XP PHG 4L390XP PHG 3L240XP  PHG 3L280XP PHG 4L310XP PHG 4L960XP PHG 4L930XP PHG 4L520XP  PHG 4L730XP PHG 4L640XP PHG 4L390XP PHG 4L650XP  PHG 4L200XP PHG 4L430XP  PHG 4L320XP PHG 4L320XP PHG 5L370XP PHG 5L370XP PHG 5L360XP  PHG 5L300XP PHG 5L310XP PHG 3L350XP PHG 5L400XP PHG 5L380XP  PHG 3L350XP PHG 5L360XP PHG 5L330XP PHG 3L320XP PHG 5L630XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
<b>Honda</b>	22431738701	PHG 4L320XP	<b>Huskee / Husky</b>	4461177	PHG 4L770XP	<b>Huskee / Husky</b>	754-0326A	PHG 4L620XP
	22431747000	PHG 5L390XP		4461185	PHG 4L780XP		754-0338	PHG 4L770XP
	22432732013	PHG 5L280XP		4461193	PHG 4L790XP		754-04003	PHG 3L320XP
	22432732671	PHG 5L290XP		4461208	PHG 4L800XP		754-04074A	PHG 4L780XP
	22432736003	PHG 5L330XP		4461216	PHG 4L810XP		754-0456	PHG 3L290XP
	22432736701	PHG 5L330XP		4461224	PHG 4L820XP		754-0462	PHG 5L1380XP
	22432738831	PHG 5L370XP		4461232	PHG 4L830XP		754-0637A	PHG 3L310XP
	76181150003	PHG 5L660XP		4461240	PHG 4L840XP		754-4001A	PHG 5L690XP
	76181750003	PHG 5L660XP		4461258	PHG 4L850XP		954-04074A	PHG 4L780XP
	76181750030	PHG 5L660XP		4461266	PHG 4L860XP		954-04285	PHG 5L350XP
	22431738A01	PHG 4L330XP		4461274	PHG 4L870XP	<b>Husqvarna</b>	183688	PHG 3L340XP
	22432738A01	PHG 5L340XP		4461282	PHG 4L880XP		194346	PHG 4L970XP
	22432738C31	PHG 5L360XP		4461290	PHG 4L900XP		196857	PHG 3L330XP
	761811510030	PHG 5L710XP		4461305	PHG 4L920XP		303241	PHG 4L900XP
	76181763A000	PHG 5L730XP		4461313	PHG 4L940XP		310275	PHG 4L820XP
	761821510130	PHG 5L530XP		4461321	PHG 4L960XP		53216520	PHG 4L890XP
	761827510130	PHG 5L530XP		4461339	PHG 4L980XP		506033003	PHG 3L340XP
	761847517010	PHG 5L630XP		4461347	PHG 4L1000XP		506070520	PHG 3VX350
	M35	PHG 3L350XP		4461355	PHG 5L350XP		506347420	PHG 3VX340
				4461371	PHG 5L370XP		506372720	PHG 3VX350
<b>Huskee / Husky</b>	2435	PHG 4L350XP		4461389	PHG 5L380XP		510201201	PHG 5L1590XP
	4460618	PHG 4L210XP		4461402	PHG 5L400XP		510201301	PHG 5L1830XP
	4460626	PHG 4L220XP		4461410	PHG 5L410XP		522795901	PHG 5L1630XP
	4460634	PHG 4L230XP		4461428	PHG 5L420XP		522811301	PHG 5L1480XP
	4460642	PHG 4L240XP		4461436	PHG 5L430XP		522829601	PHG 5L1760XP
	4460650	PHG 4L250XP		4461444	PHG 5L440XP		522999901	PHG 5L1130XP
	4460668	PHG 4L260XP		4461452	PHG 5L450XP		531002630	PHG 5L360XP
	4460676	PHG 4L250XP		4461460	PHG 5L460XP		531002635	PHG 5L320XP
	4460684	PHG 4L280XP		4461478	PHG 5L470XP		531030352	PHG 3L340XP
	4460692	PHG 4L290XP		4461486	PHG 5L480XP		531300766	PHG A93
	4460707	PHG 4L300XP		4461494	PHG 5L490XP		531300767	PHG 5L970XP
	4460715	PHG 4L310XP		4461509	PHG 5L500XP		531300771	PHG 5L890XP
	4460723	PHG 4L320XP		4461517	PHG 5L510XP		531300773	PHG 4L830XP
	4460731	PHG 4L330XP		4461525	PHG 5L520XP		532002614	PHG 3L440XP
	4460749	PHG 4L340XP		4461533	PHG 5L530XP		532104022	PHG 4L430XP
	4460757	PHG 4L350XP		4461541	PHG 5L540XP		532123461	PHG 4L800XP
	4460765	PHG 4L360XP		4461567	PHG 5L560XP		532123796	PHG 4L950XP
	4460773	PHG 4L350XP		4461583	PHG 5L580XP		532124293	PHG 4L800XP
	4460781	PHG 4L380XP		4461606	PHG 5L600XP		532124525	PHG 4L890XP
	4460799	PHG 4L390XP		4461622	PHG 5L620XP		532131006	PHG 4L990XP
	4460804	PHG 4L400XP		4461630	PHG 5L630XP		532132672	PHG 4L510XP
	4460812	PHG 4L410XP		4461648	PHG 5L640XP		532138399	PHG 4L590XP
	4460820	PHG 4L420XP		4461656	PHG 5L650XP		532141416	PHG 4L840XP
	4460838	PHG 4L430XP		4461664	PHG 5L660XP		532148763	PHG B83
	4460846	PHG 4L440XP		4461672	PHG 5L670XP		532156971	PHG 4L820XP
	4460854	PHG 4L450XP		4461680	PHG 5L680XP		532160855	OE Only
	4460862	PHG 4L460XP		4461698	PHG 5L690XP		532161850	PHG 4L850XP
	4460870	PHG 4L470XP		4461703	PHG 5L700XP		532165555	OE Only
	4460888	PHG 4L480XP		4461711	PHG 5L710XP		532165631	PHG 4L1110XP
	4460896	PHG 4L490XP		4461729	PHG 5L720XP		532165813	PHG 4L850XP
	4460901	PHG 4L500XP		4461737	PHG 5L730XP		532169778	OE Only
	4460919	PHG 4L510XP		4461745	PHG 5L740XP		532170140	PHG 4L1130XP
	4460927	PHG 4L520XP		4461753	PHG 5L750XP		532174369	PHG 5L890XP
	4460935	PHG 4L530XP		4461761	PHG 5L760XP		532174383	PHG 4L840XP
	4460943	PHG 4L540XP		4461779	PHG 5L770XP		532179092	PHG AX32
	4460951	PHG 4L550XP		4461787	PHG 5L780XP		532194346	PHG 4L820XP
	4460969	PHG 4L560XP		4461795	PHG 5L790XP		532300773	PHG 4L830XP
	4460977	PHG 4L570XP		4461800	PHG 5L800XP		532405029	PHG 4L1070XP
	4460985	PHG 4L580XP		4461818	PHG 5L810XP		532408007	PHG 5L380XP
	4460993	PHG 4L590XP		4461826	PHG 5L820XP		532408010	PHG 5L370XP
	4461004	PHG 4L600XP		4461834	PHG 5L830XP		532408381	PHG 4L960XP
	4461012	PHG 4L610XP		4461842	PHG 5L840XP		532416954	PHG AX32
	4461020	PHG 4L620XP		4461850	PHG 5L850XP		532419271	PHG 4L880XP
	4461038	PHG 4L630XP		4461868	PHG 5L850XP		532419744	PHG A32
	4461046	PHG 4L640XP		4461876	PHG 5L880XP		532420807	PHG 4L810XP
	4461054	PHG 4L650XP		4461884	PHG 5L900XP		532427304	PHG 4L370XP
	4461062	PHG 4L660XP		4461892	PHG 5L940XP		532428454	PHG 4L290XP
	4461070	PHG 4L670XP		4461907	PHG 5L960XP		532437261	PHG 4L290XP
	4461088	PHG 4L680XP		4461915	PHG 5L980XP		532441597	PHG 4L720XP
	4461096	PHG 4L690XP		4461923	PHG 5L1000XP		533048044	PHG 5L820XP
	4461101	PHG 4L700XP		4461931	PHG 4L1030XP		533303241	PHG 4L900XP
	4461119	PHG 4L710XP		4461949	PHG 4L1050XP		539000334	PHG 4L310XP
	4461127	PHG 4L720XP		4461957	PHG 4L1070XP		539000336	PHG 4L440XP
	4461135	PHG 4L730XP		4461965	PHG 4L1140XP		539000339	PHG 5L360XP
	4461143	PHG 4L740XP		4461973	PHG 4L1170XP		539100439	PHG 4L350XP
	4461151	PHG 4L750XP		4461981	PHG 5L1030XP		539101228	PHG 5L460XP
	4461169	PHG 4L760XP						

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Husqvarna	539102548	PHG 5L1120XP	Jacobson	312795	PHG 5L320XP	Jacobson	392445	PHG 4L280XP
	539102549	PHG 5L1430XP		313254	PHG 3L250XP		392456	PHG 3L370XP
	539102903	PHG 5L1230XP		313267	PHG 4L290XP		501294	PHG 3L330XP
	539103241	PHG 5L600XP		313582	PHG 5L250XP		545294	PHG 4L640XP
	539103687	PHG 5L1520XP		313775	PHG 4L200XP		546341	PHG 5L250XP
	539104336	PHG 5L1800XP		314012	PHG 4L400XP		546342	PHG 5L310XP
	539105477	PHG 4L400XP		314042	PHG 3L230XP		546343	PHG 4L520XP
	539105644	PHG B131		314564	PHG 4L290XP		JA990738	PHG 4L520XP
	539107709	PHG 5L1430XP		314600	PHG 5L660XP		JA991488	PHG 4L730XP
	539109242	PHG 5L1360XP		315375	PHG 5L780XP		JA992251	PHG 4L640XP
	539109243	PHG 5L1350XP		315402	PHG 4L320XP		REM1415	PHG 4L200XP
	539110410	PHG 4L1050XP		316910	PHG 4L430XP	John Deere	2058	PHG 4L300XP
	539110411	PHG A54		317375	PHG 4L310XP		AM100465	PHG 5L330XP
	539110413	PHG A54		324136	PHG 4L200XP		AM108054	PHG 4L560XP
	539111305	PHG 4L340XP		325074	PHG 4L840XP		AM31159	PHG 4L280XP
	539111949	PHG 5L1520XP		325221	PHG 5L640XP		AM32172	PHG 4L350XP
	539112529	PHG 5L1750XP		325275	PHG 4L430XP		AM32636	PHG 4L360XP
	539114557	PHG 5L1540XP		325887	PHG 4L590XP		AM35380	PHG 4L410XP
	539116424	PHG 5L1220XP		325910	PHG 3L330XP		D28125	PHG 4L740XP
	539117245	PHG 5L1220XP		325983	PHG 5L280XP		GC00081	PHG 3L350XP
	539117811	PHG 5L1060XP		325984	PHG 5L330XP		GX10062	PHG 4L1060XP
	539120772	PHG 4L430XP		326227	PHG 3L350XP		GX10063	PHG 4L1420XP
	539173589	PHG 4L840XP		326308	PHG 4L690XP		GX20006	PHG A88
	574285901	PHG 5L1700XP		326946	PHG 5L690XP		GX20072	PHG 4L1040XP
	574286001	PHG 5L2010XP		328821	PHG 4L830XP		GX20241	PHG 4L920XP
	574845601	PHG 5L1270XP		328825	PHG 4L840XP		GX20305	PHG 4L1390XP
	574845602	PHG 5L1350XP		328826	PHG 4L780XP			
	574845603	PHG 5L1430XP		328892	PHG 4L830XP		GX21395	PHG 5L1590XP
	576667201	PHG AX85		328973	PHG 4L630XP		GX21407	PHG 4L890XP
	601000194	PHG 4L900XP		329184	PHG 4L840XP		GX21833	PHG A140
	601000921	PHG 5L1290XP		329193	PHG 4L900XP		GX21986	PHG 4L870XP
	601001437	PHG 3L330XP		329205	PHG 4L450XP		GX22036	PHG 4L920XP
	601001737	PHG 4L350XP		329207	PHG 4L360XP		GX22269	PHG 3L380XP
	601001762	PHG 3L350XP		329253	PHG 4L900XP		LVU21853	PHG 5L1160XP
	601002148	PHG 4L330XP		330447	PHG 4L670XP		M110312	PHG 5L650XP
	606000226	PHG 3VX330		330448	PHG 4L280XP		M110313	PHG 5L1110XP
	102655X	PHG 4L380XP		330463	PHG 4L760XP		M110367	PHG 5L890XP
	532125907	PHG 4L900XP		330503	PHG 4L970XP		M110599	PHG 3L300XP
	532130969	PHG 4L930XP		330559	PHG 5L460XP		M110766	PHG 3L360XP
	532137153	PHG 4L840XP		330599	PHG 4L350XP		M110776	PHG 3L360XP
	532138255	PHG 4L940XP		330675	PHG 4L280XP		M110797	PHG 4L380XP
	532140218	PHG 4L850XP		330790	PHG 4L360XP		M110978	PHG 4L1020XP
	532140294	PHG 4L820XP		331325	PHG 3L400XP		M111534	PHG 5L1300XP
	532144959	PHG 4L960XP		331325	PHG 4L820XP		M111564	PHG BB123
	532174368	PHG 5L900XP		331594	PHG 4L320XP		M112006	PHG 4L630XP
	532178138	PHG 4L870XP		331672	PHG 4L480XP		M112490	PHG 4L990XP
	532191273	PHG 5L1430XP		331807	PHG 3L240XP		M114763	PHG 4L850XP
	532194346	PHG 4L970XP		331808	PHG 3L320XP		M115776	PHG 4L1070XP
	532196103	PHG 5L1480XP		331846	PHG 4L510XP		M117608	PHG 4L590XP
	532197242	PHG 5L1400XP		331847	PHG 4L800XP		M117636	PHG B129
	532197253	PHG 4L1010XP		331876	PHG 4L690XP		M118048	PHG 5L850XP
	532405143	PHG 4L1070XP		332051	PHG 4L290XP		M118685	PHG 5L1200XP
	532429636	PHG 4L1010XP		332111	PHG 4L440XP		M118756	PHG 5L1230XP
Jacobson	1024	PHG 4L570XP		333719	PHG 5L620XP		M118760	PHG 4L980XP
	2058	PHG 4L300XP		335453	PHG 4L410XP		M119539	PHG 4L1370XP
	304393	PHG A17		335832	PHG 4L380XP		M119656	PHG 5L620XP
	307522	PHG 4L420XP		335856	PHG 4L390XP		M119713	PHG 5L860XP
	307870	PHG 4L350XP		336055	PHG 3L320XP		M120381	PHG BB123
	307913	PHG 4L220XP		336219	PHG 4L300XP		M122674	PHG 4L920XP
	309082	PHG 3L380XP		336262	PHG 4L320XP		M122907	PHG 5L500XP
	309507	PHG 3L220XP		336263	PHG 4L250XP		M123281	PHG 4L1440XP
	310046	PHG 3L360XP		336481	PHG 5L430XP		M125218	PHG 4L960XP
	310119	PHG 4L320XP		336488	PHG 5L430XP		M126009	PHG 4L860XP
	310391	PHG 4L250XP		342307	PHG 4L860XP		M126012	PHG 5L950XP
	310538	PHG 5L360XP		342660	PHG 5L770XP		M126536	PHG 4L1440XP
	310917	PHG 4L350XP		342780	PHG 4L200XP		M127523	PHG 5L900XP
	311419	PHG 4L280XP		343359	PHG 5L720XP		M127524	PHG 4L910XP
	311496	PHG 4L570XP		344218	PHG 4L650XP		M12907	PHG 5L500XP
	311621	PHG 5L790XP		348720	PHG 4L720XP		M136927	PHG 4L1080XP
	311649	PHG 5L250XP		349006	PHG 5L410XP		M138583	PHG AA113
	311650	PHG 5L330XP		349079	PHG 4L770XP		M139970	PHG 4L1310XP
	311735	PHG 3L420XP		358577	PHG 4L310XP		M140502	PHG 4L950XP
	311749	PHG 4L530XP		390008	PHG 4L470XP		M143019	PHG AX62
	312104	PHG 4L350XP		390188	PHG 4L440XP		M143888	PHG 5L1110XP
	312529	PHG 3L240XP		390422	PHG 4L320XP		M144044	PHG 4L920XP
	312571	PHG 5L290XP		392410	PHG 4L410XP		M144570	PHG 4L970XP
				392433	PHG 5L510XP		M147044	PHG 4L900XP



OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
John Deere	M148269	PHG 4L1310XP	John Deere	M77672	PHG 5L610XP	John Deere	TCU18117	PHG 5L1360XP
	M151276	PHG 5L970XP		M77673	PHG 5L630XP		TCU18602	PHG 5L1480XP
	M151649	PHG 4L1440XP		M77674	PHG 4L200XP		TCU18603	PHG 5L1560XP
	M152284	PHG 4L930XP		M77675	PHG 4L210XP		TCU19609	PHG 5L1500XP
	M152398	PHG 4L1510XP		M77988	PHG 4L600XP		TCU20002	PHG 4L540XP
	M153160	PHG BB154		M800048	PHG 4L320XP		TCU20822	PHG B42
	M154157	PHG A40		M81035	PHG 4L350XP		TCU21814	PHG B48
	M154294	PHG 4L1190XP		M81036	PHG 4L330XP		TCU22550	PHG 4L720XP
	M154601	PHG 4L1410XP		M81037	PHG 4L320XP		TCU26297	PHG 5L1800XP
	M154621	PHG 4L1440XP		M81055	PHG 4L350XP		TCU26904	PHG 5L1590XP
	M154958	PHG 5L1110XP		M81056	PHG 4L330XP		TCU26905	PHG 5L1700XP
	M154960	PHG 5L1200XP		M81057	PHG 4L320XP		TCU26906	PHG 5L1820XP
	M155343	PHG 4L600XP		M811281	PHG 4L320XP		TCU26908	PHG 5L1730XP
	M155368	PHG 5L1900XP		M81805	PHG 4L490XP		TCU26909	PHG 5L1860XP
	M155525	PHG 4L1410XP		M82167	PHG 4L510XP	Kees/Yazoo	1248	PHG 4L260XP
	M156261	PHG 5L1640XP		M82258	PHG 5L400XP		60119	PHG 5L440XP
	M158130	PHG 4L1500XP		M82460	PHG 4L660XP		103032	PHG 5L360XP
	M158131	PHG 4L1520XP		M82461	PHG 4L390XP		363143	PHG 5L890XP
	M160571	PHG 4L1070XP		M82462	PHG 4L660XP		483012	PHG 5L520XP
	M160956	PHG 4L590XP		M82612	PHG 4L360XP		483013	PHG 5L940XP
	M163540	PHG 4L1100XP		M82718	PHG 4L900XP		483023	PHG 5L370XP
	M163989	PHG 5L1110XP		M82719	PHG 4L490XP		205-505	PHG AA80
	M163990	PHG 5L1200XP		M82720	PHG 4L450XP		532-138498	PHG 4L960XP
	M40015	PHG 5L350XP		M82721	PHG 4L870XP		532-140294	PHG 4L820XP
	M40222	PHG 4L280XP		M82734	PHG 4L600XP		532-191273	PHG 5L1430XP
	M40223	PHG 4L870XP		M83837	PHG 4L880XP		539-103241	PHG 4L600XP
	M40224	PHG 4L570XP		M84075	PHG 4L790XP		539-103687	PHG 5L1520XP
	M40757	PHG 4L770XP		M84136	PHG 4L1010XP		539-107709	PHG 5L1430XP
	M41335	PHG 3L320XP		M84223	PHG 4L620XP		539-107710	PHG 4L650XP
	M41555	PHG 3L320XP		M84225	PHG 4L620XP		VB62F	PHG 5L390XP
	M41592	PHG 4L400XP		M85442	PHG 4L440XP	Lawn Chief	1540	PHG 5L400XP
	M41642	PHG 4L620XP		M86060	PHG 4L430XP		10737	PHG 4L310XP
	M41668	PHG 4L980XP		M86421	PHG 4L530XP		20716	PHG 4L350XP
	M41960	PHG 4L1020XP		M86422	PHG 4L630XP		20717	PHG 4L560XP
	M41985	PHG 3L360XP		M86996	PHG 4L870XP		21615	PHG 4L950XP
	M42226	PHG 5L250XP		M88184	PHG 4L600XP		49405	PHG 4L880XP
	M42485	PHG 4L460XP		M88462	PHG 4L660XP		111215	PHG 4L820XP
	M43106	PHG 3L390XP		M89112	PHG 4L880XP		135194	PHG 4L890XP
	M43489	PHG 4L570XP		M89832	PHG 4L790XP		135863	PHG 4L400XP
	M43569	PHG 4L500XP		M90958	PHG 4L550XP		136176	PHG 5L780XP
	M43586	PHG 4L680XP		M91147	PHG 4L630XP		136705	PHG 4L340XP
	M43795	PHG 4L410XP		M91270	PHG 4L470XP		136762	PHG 4L680XP
	M43820	PHG 4L740XP		M91330	PHG 4L640XP		136887	PHG 4L430XP
	M44121	PHG 5L670XP		M91470	PHG 5L470XP	Lawn-Boy	2499	PHG 4L360XP
	M44178	PHG 3L290XP		M93748	PHG 5L460XP		11193	PHG 5L890XP
	M44272	PHG 4L800XP		M94020	PHG 4L490XP		14790	PHG 4L380XP
	M44483	PHG 4L480XP		M94049	PHG 5L430XP		16146	PHG 4L390XP
	M44498	PHG 4L600XP		M94829	PHG 4L310XP		16366	PHG 4L350XP
	M45254	PHG 4L860XP		M95121	PHG 4L430XP		16386	PHG 4L400XP
	M45489	PHG 4L570XP		M95122	PHG 4L830XP		18055	PHG 4L300XP
	M45862	PHG 4L470XP		M97340	PHG 3L330XP		25090	PHG 4L600XP
	M45863	PHG 4L560XP		PT12668	PHG 5L540XP		45589	PHG 4L350XP
	M45998	PHG 4L830XP		PT13490	PHG 3L330XP		103347	PHG 5L510XP
	M46758	PHG 4L360XP		PT15219	PHG 5L460XP		207925	PHG 3L320XP
	M47043	PHG 4L790XP		PT15220	PHG 4L460XP		208626	PHG 3L270XP
	M47159	PHG 4L300XP		PT15260	PHG 3L350XP		212776	PHG 4L660XP
	M47765	PHG 4L840XP		PT2303	PHG 3L370XP		235000	PHG 5L500XP
	M47766	PHG 4L800XP		PT5300	PHG 4L570XP		240773	PHG 4L740XP
	M47770	PHG 4L580XP		PT5302	PHG 4L390XP		245477	PHG 4L840XP
	M48520	PHG 4L250XP		PT7513	PHG 3L220XP		602956	PHG 3L290XP
	M49920	PHG 4L990XP		PT8666	PHG 5L540XP		602957	PHG 3L310XP
	M71026	PHG 4L840XP		PT8669	PHG 4L430XP		603682	PHG 4L240XP
	M71135	PHG 4L740XP		PT8676	PHG 4L500XP		605711	PHG 4L610XP
	M71529	PHG 4L650XP		PT8679	PHG 5L370XP		605837	PHG 4L1120XP
	M72031	PHG 4L600XP		PT8697	PHG 5L320XP		606248	PHG 4L330XP
	M72683	PHG 4L990XP		PT8698	PHG 5L460XP		606250	PHG 4L520XP
	M72685	PHG 4L990XP		PT8716	PHG 4L460XP		606508	PHG 4L480XP
	M73223	PHG 4L800XP		RG60874	PHG A39		607198	PHG 4L400XP
	M73478	PHG 4L590XP		TCU13195	PHG 5L1160XP		607270	PHG 4L320XP
	M73604	PHG 3L340XP		TCU13196	PHG 5L1320XP		607271	PHG 4L440XP
	M74747	PHG 4L1050XP		TCU13198	PHG 5L1410XP		607980	PHG 4L620XP
	M75353	PHG 4L640XP		TCU16036	PHG C173		608016	PHG 4L540XP
	M75746	PHG 4L410XP		TCU16093	PHG 5L1570XP		608017	PHG 4L650XP
	M77167	PHG 3L340XP		TCU16122	PHG 4L1000XP		608474	PHG 4L620XP
	M77670	PHG 4L390XP		TCU16495	PHG 5L1260XP		608475	PHG 4L700XP
	M77671	PHG 5L420XP		TCU17289	PHG 4L400XP			

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation			
Lawn-Boy	608476 610040 611803 612652 6080147  6080157 6080257 240773L 608014T 608015T  608025T GB235000	PHG 4L560XP PHG 3L440XP PHG 3L320XP PHG 3L320XP PHG 4L350XP  PHG 4L530XP PHG 4L680XP PHG 4L740XP PHG 4L350XP PHG 4L530XP  PHG 4L680XP PHG 5L500XP	Mc Lane	1060 41300 4L300	PHG 4L1080XP PHG 4L300XP PHG 4L300XP	Montgomery Ward	52538 100162 102625 106123 106390	PHG 4L240XP PHG 4L220XP PHG 4L530XP PHG 4L260XP PHG 4L360XP			
Massey	2058 1023435M1 1023436M1 1023564M1 1023608M1  1023850M 1023886M1 1025542M1 1025557M1 1025796M1  1029730M1 1030050M1 1030063M1 1032843M1 3021192M1  511277M2 511277M3 511485M1 514132M1 51432M1  514806M1 514891M1 518125M1 518223M1 519958M1  523733M1 523734M1 530669M1	PHG 4L300XP PHG 4L340XP PHG 4L290XP PHG 4L250XP PHG 4L290XP  PHG 5L350XP PHG 5L620XP PHG 4L500XP PHG 4L750XP PHG 3L300XP  PHG 5L630XP PHG 4L490XP PHG 5L330XP PHG 4L720XP PHG 4L960XP  PHG 4L500XP PHG 4L500XP PHG 3L320XP PHG 4L300XP PHG 4L200XP  PHG 4L350XP PHG 4L820XP PHG 4L400XP PHG 4L280XP PHG 4L770XP  PHG 4L360XP PHG 4L580XP PHG 4L350XP	Merry Tiller	329 594 862 1023 1530  1637 1984 2031 2059 2270  2278 2313 2391 2404 3292  48350	PHG 4L450XP PHG 4L340XP PHG 4L400XP PHG 4L430XP PHG 4L350XP  PHG 3L390XP PHG 4L450XP PHG 4L500XP PHG 4L500XP PHG 4L410XP  PHG 4L410XP PHG 3L450XP PHG 4L360XP PHG 3L300XP PHG 4L340XP  PHG 4L350XP	Mighty Mac	300001 300038 300113 7010318 7010319  3L450 4L500	PHG 4L380XP PHG 4L550XP PHG 4L530XP PHG 4L420XP PHG 4L540XP  PHG 3L450XP PHG 4L500XP	Montgomery Ward	154307 156120 156231 165112 165129  165130 165132 165133 165138 165139  165141 165142 165143 165151 165153  165154 165159 165160 165161 165163  165164 165165 165166 165167 165168  165169 165171 165172 165173 165174  165175 165179 165181 165182 165183  165184 170921 173420 173461 173948  200413 200414 200416 200624 200625  200626 200804 200982 200983 203832  203839 208526 208626 209581 209630	PHG 4L350XP PHG 4L630XP PHG 4L420XP PHG 4L190XP PHG 4L260XP  PHG 4L290XP PHG 4L250XP PHG 4L350XP PHG 4L400XP PHG 4L560XP  PHG 4L400XP PHG 4L10XP PHG 4L560XP PHG 4L630XP PHG 4L620XP  PHG 4L640XP PHG 4L580XP PHG 4L400XP PHG 5L610XP PHG 4L650XP  PHG 4L390XP PHG 4L670XP PHG 4L640XP PHG 5L10XP PHG 4L350XP  PHG 4L550XP PHG 5L630XP PHG 4L670XP PHG 5L630XP PHG 5L480XP  PHG 5L450XP PHG 5L780XP PHG 4L390XP PHG 4L540XP PHG 4L570XP  PHG 4L550XP PHG 4L240XP PHG 5L930XP PHG 4L1000XP PHG 4L570XP  PHG 4L390XP PHG 4L830XP PHG 5L320XP PHG 5L800XP PHG 4L560XP  PHG 5L400XP PHG 4L740XP PHG 4L780XP PHG 5L810XP PHG 4L320XP  PHG 4L390XP PHG 3L380XP PHG 3L270XP PHG 4L860XP PHG 4L390XP
Maxim	1346 1557 272201 272212 272216  272217 272220 272222 272223 272224  272229 272234 272235 272236 272237  272240 272241 359328 230272205 320272201  320272204 320272205 320272213 320272214 320272216  320272217 320312212 320359328 320372204 272205  L346 L557 M35932580	PHG 3L460XP PHG 5L570XP PHG 4L510XP PHG 4L640XP PHG 4L310XP  PHG 4L760XP PHG 4L280XP PHG 4L560XP PHG 4L640XP PHG 4L530XP  PHG 4L310XP PHG 5L880XP PHG 5L670XP PHG 5L570XP PHG 4L400XP  PHG 4L320XP PHG 4L350XP PHG 4L500XP PHG 4L400XP PHG 4L510XP  PHG 4L380XP PHG 4L400XP PHG 4L470XP PHG 4L750XP PHG 4L310XP  PHG 4L760XP PHG 4L640XP PHG 4L500XP PHG 4L380XP PHG 4L400XP  PHG 3L460XP PHG 5L570XP PHG 4L500XP	Montgomery Ward	1060 1409 1434 2006 2119  2435 4638 4825 7757 9303  9305 9581 10111 10755 11144  11723 11792 11793 11901 11943  12023 12510 12570 12684 13072  13436 13487 14146 14365 14790  14843 16146 16366 16386 17518  17569 17653 18055 18263 19037  24602 35545 36770 36806 37756  37757 41969 41980 41993	PHG 4L1080XP PHG 5L520XP PHG 3L280XP PHG 4L280XP PHG 4L210XP  PHG 4L350XP PHG 4L300XP PHG 4L600XP PHG 4L830XP PHG 3L250XP  PHG 4L520XP PHG 4L860XP PHG 4L290XP PHG 4L430XP PHG 4L410XP  PHG 4L230XP PHG 5L960XP PHG 5L900XP PHG 4L360XP PHG 5L350XP  PHG 3L210XP PHG 5L560XP PHG 5L560XP PHG 5L960XP PHG 4L720XP  PHG 4L540XP PHG 4L350XP PHG 4L390XP PHG 4L510XP PHG 4L380XP  PHG 4L290XP PHG 4L390XP PHG 4L350XP PHG 4L400XP PHG 4L600XP  PHG 4L430XP PHG 4L470XP PHG 4L300XP PHG 4L400XP PHG 4L210XP  PHG 4L990XP PHG 4L400XP PHG 4L350XP PHG 5L530XP PHG 4L560XP  PHG 4L830XP PHG 5L500XP PHG 4L670XP PHG 4L590XP	210752	PHG 4L700XP				

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Montgomery Ward</b>	210753	PHG 4L310XP	<b>Montgomery Ward</b>	1108466	PHG 4L330XP	<b>Mott</b>	102	PHG 4L610XP
	211650	PHG 3L330XP		1540198	PHG 4L620XP		186	PHG 5L470XP
	211664	PHG 4L360XP		1651066	PHG 4L640XP		P127	PHG 4L250XP
	212776	PHG 4L660XP		1714286	PHG 4L480XP		P322	PHG 3L210XP
	214110	PHG 4L580XP		1714513	PHG 3L230XP		P49	PHG 5L580XP
	217773	PHG 4L400XP		1723661	PHG 3L410XP		P50	PHG 5L320XP
	265123	PHG 4L330XP		7540104	PHG 4L320XP		P638	PHG 5L390XP
	265140	PHG 5L560XP		7540105	PHG 4L300XP			
	308458	PHG 5L360XP		7540107	PHG 4L300XP	<b>Mtd</b>	954-04285	PHG 5L350XP
	484620	PHG 3L280XP		7540109	PHG 4L430XP		6434	PHG 5L510XP
	503849	PHG 4L490XP		7540112	PHG 5L800XP		6511	PHG 4L680XP
	503855	PHG 4L550XP		7540113	PHG 5L480XP		8431	PHG 5L670XP
	504250	PHG 5L500XP		7540114	PHG 4L240XP		23144	PHG 4L920XP
	504251	PHG 5L510XP		7540121	PHG 4L310XP		23145	PHG 4L460XP
	504253	PHG 5L530XP		7540136	PHG 5L310XP		249730	PHG 3L360XP
	754101	PHG 4L350XP		7540138	PHG 5L500XP		1651020	PHG 4L180XP
	754104	PHG 4L320XP		7540142	PHG 3L310XP		1731273	PHG 4L350XP
	754105	PHG 4L300XP		7540143	PHG 3L280XP		106409C1	PHG 4L860XP
	754107	PHG 4L300XP		7540144	PHG 5L550XP			
	754109	PHG 4L430XP		7540145	PHG 5L690XP		106465C1	PHG 4L510XP
	754112	PHG 5L800XP		7540157	PHG 5L280XP		106990C1	PHG 4L450XP
	754113	PHG 5L480XP		7540163	PHG 4L280XP		126496C1	PHG 4L330XP
	754114	PHG 4L240XP		7540167	PHG 5L640XP		132013C1	PHG 4L300XP
	754121	PHG 4L310XP		7540173	PHG 5L370XP		132401C1	PHG 4L690XP
	754136	PHG 5L310XP		7540177	PHG 4L320XP		132407C1	PHG 4L690XP
	754138	PHG 5L500XP		7540180	PHG 5L540XP		140080C1	PHG 4L320XP
	754142	PHG 3L310XP		7540182	PHG 5L810XP		3766230R1	PHG 3L310XP
	754143	PHG 3L280XP		7540185	PHG 4L490XP		386160R1	PHG 3L300XP
	754144	PHG 5L550XP		7540186	PHG 4L820XP		401960R1	PHG 3L310XP
	754145	PHG 5L690XP		7540188	PHG 5L510XP		408077R1	PHG 4L480XP
	754151	PHG 5L670XP		7540191	PHG 4L650XP		413462R4	PHG 4L810XP
	754157	PHG 5L280XP		7540195	PHG 4L540XP		464351R1	PHG 4L300XP
	754163	PHG 4L280XP		7540198	PHG 4L620XP		471599R2	PHG 4L770XP
	754167	PHG 5L640XP		7540203	PHG 5L610XP		473468R2	PHG 4L720XP
	754173	PHG 5L370XP		7540204	PHG 4L670XP		477599R2	PHG 4L770XP
	754177	PHG 4L320XP		7540205	PHG 3L320XP		481099R2	PHG 4L830XP
	754180	PHG 5L540XP		7540206	PHG 4L500XP		489399R1	PHG 4L800XP
	754181	PHG 4L1000XP		7540207	PHG 4L420XP		549108R1	PHG 4L380XP
	754182	PHG 5L810XP		7540208	PHG 4L550XP		549609R1	PHG 4L500XP
	754185	PHG 4L490XP		7540217	PHG 5L790XP		549822R1	PHG 4L680XP
	754186	PHG 4L820XP		7540219	PHG 4L260XP		579821R1	PHG 4L310XP
	754188	PHG 5L510XP		7540222	PHG 4L440XP		59701C1	PHG 4L770XP
	754194	PHG 4L450XP		7540223	PHG 4L440XP		59702C1	PHG 4L850XP
	754195	PHG 4L540XP		7540229	PHG 3L360XP		61083C1	PHG 4L320XP
	754198	PHG 4L620XP		7540242	PHG 4L520XP		61083C1	PHG 4L320XP
	754203	PHG 5L610XP		7540244	PHG 4L320XP		61084C1	PHG 4L590XP
	754204	PHG 4L670XP		7540245	PHG 4L400XP		61084C1	PHG 4L590XP
	754205	PHG 3L320XP		7540250	PHG 4L590XP		61084C1	PHG 4L590XP
	754206	PHG 4L500XP		7540252	PHG 4L530XP		706-15711	PHG 4L350XP
	754207	PHG 4L420XP		7540256	PHG 4L330XP		745-0267	PHG 4L590XP
	754208	PHG 4L550XP		7540257	PHG 3L380XP		751-0101A	PHG 4L350XP
	754217	PHG 5L790XP		7540265	PHG 4L350XP		754-0100	PHG A16
	754219	PHG 4L260XP		7540267	PHG 4L590XP		754-0101	PHG 3L350XP
	754222	PHG 4L440XP		7540271	PHG 3L390XP		754-0101A	PHG 3L350XP
	754223	PHG 3L360XP		7540273	PHG 3L340XP		754-0101B	PHG 4L350XP
	754240	PHG 5L380XP		7540278	PHG 4L300XP		754-0103	PHG 4L270XP
	754241	PHG 5L350XP		7540285	PHG 4L340XP		754-0104	PHG 4L320XP
	754242	PHG 4L320XP		7540292	PHG 4L260XP		754-0105	PHG 4L300XP
	754244	PHG 4L400XP		7540299	PHG 4L260XP		754-0106	PHG 4L250XP
	754245	PHG 4L590XP		7540936	PHG 4L470XP		754-0107	PHG 4L300XP
	754250	PHG 4L530XP		8021077	PHG 4L390XP		754-0108	PHG 4L460XP
	754252	PHG 4L330XP		8161244	PHG 4L380XP		754-0109	PHG 4L430XP
	754256	PHG 3L290XP		54MA19	PHG 4L350XP		754-0111	PHG 4L450XP
	754257	PHG 3L380XP		E027	PHG 4L250XP		754-0112	PHG 5L800XP
	754264	PHG 4L520XP		L141029	PHG 4L210XP		754-0113	PHG 5L480XP
	754265	PHG 4L350XP		L141038	PHG 4L330XP		754-0114	PHG 4L240XP
	754267	PHG 4L590XP		L19P21290	PHG 3L350XP		754-0115	PHG 5L610XP
	754273	PHG 3L340XP		L21P1290	PHG 3L290XP		754-0116	PHG 4L420XP
	754278	PHG 4L300XP		L21P21290	PHG 3L370XP			
	754285	PHG 4L340XP		L5055	PHG 3L220XP		754-0117	PHG 4L320XP
	754292	PHG 4L260XP		L5399	PHG 3L210XP		754-0118	PHG 5L630XP
	754935	PHG 4L310XP		S1A119	PHG 4L330XP		754-0121	PHG 4L310XP
	754936	PHG 4L470XP		S1A164	PHG 4L310XP		754-0124	PHG 4L570XP
	1008304	PHG 3L370XP		Y22	PHG 4L300XP		754-0125	PHG 4L1050XP
	1009102	PHG 3L290XP	<b>Moto-Mower</b>	2492	PHG 4L250XP		754-0126	PHG 4L200XP
	1020699	PHG 3L270XP		1020699	PHG 3L270XP		754-0127	PHG 5L660XP
							754-0128	PHG 5L350XP

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Mtd	754-0129	PHG 4L260XP	Mtd	754-0224	PHG 5L250XP	Mtd	754-0342	PHG 4L670XP
	754-0131	PHG 3L350XP		754-0225	PHG 4L1070XP		754-0343	PHG 3L310XP
	754-0133	PHG 3L320XP		754-0226	PHG 4L820XP		754-0344	PHG 4L730XP
	754-0134	PHG 3L330XP		754-0227	PHG 5L630XP			
	754-0135	PHG 4L340XP					754-0346	PHG 3L300XP
				754-0228	PHG 5L620XP		754-0347	PHG 4L630XP
	754-0136	PHG 5L310XP		754-0229	PHG 4L520XP		754-0348	PHG 4L530XP
	754-0137	PHG 4L300XP		754-0230	PHG 4L560XP		754-0349	PHG A77
	754-0138	PHG 5L500XP		754-0231	PHG 4L280XP		754-0350	PHG 5L640XP
	754-0139	PHG 3L380XP		754-0232	PHG 4L200XP			
	754-0140	PHG 4L310XP					754-0351	PHG 4L610XP
				754-0233	PHG 4L210XP		754-0352	PHG 4L480XP
	754-0141	PHG 5L520XP		754-0234	PHG 4L410XP		754-0355	PHG 4L670XP
	754-0142	PHG 3L310XP		754-0235	PHG 4L530XP		754-0364	PHG 5L830XP
	754-0143	PHG 3L280XP		754-0236	PHG 4L850XP		754-0365	PHG 4L830XP
	754-0144	PHG 5L550XP		754-0238	PHG 4L920XP			
	754-0145	PHG 4L690XP					754-0367	PHG 4L340XP
				754-0239	PHG 4L290XP		754-0369	PHG 3L330XP
	754-0145A	PHG 4L690XP		754-0240	PHG 5L380XP		754-0370	PHG 5L490XP
	754-0146	PHG 4L330XP		754-0241	PHG 5L350XP		754-0371	PHG 5L740XP
	754-0147	PHG 5L520XP		754-0241A	PHG 5L350XP		754-0371A	PHG 5L740XP
	754-0151	PHG 5L670XP		754-0242	PHG 4L320XP			
	754-0154	PHG 4L350XP					754-04001	PHG 5L690XP
				754-0243	PHG 4L460XP		754-04014	PHG 3L270XP
	754-0155	PHG 3L400XP		754-0244	PHG 4L400XP		754-04032	PHG 3L360XP
	754-0157	PHG 5L280XP		754-0245	PHG 4L590XP		754-04032A	PHG 3L360XP
	754-0158	PHG 5L350XP		754-0246	PHG 4L590XP		754-04032B	PHG 3L360XP
	754-0163	PHG 4L280XP		754-0247	PHG 4L560XP			
	754-0164	PHG 4L630XP					754-04041	PHG 5L1110XP
				754-0248	PHG 4L890XP		754-04043	PHG 4L580XP
	754-0165	PHG 4L340XP		754-0249	PHG 5L300XP		754-04048	PHG 5L1300XP
	754-0166	PHG 5L620XP		754-0250	PHG 4L530XP		754-04060	PHG 4L960XP
	754-0167	PHG 5L640XP		754-0251	PHG 4L510XP		754-04060B	PHG 4L960XP
	754-0169	PHG 3L360XP		754-0252	PHG 4L330XP			
	754-0170	PHG 5L500XP					754-04064	PHG 5L680XP
				754-0253	PHG 4L430XP		754-04074A	PHG 4L780XP
	754-0171	PHG 4L320XP		754-0254	PHG A17		754-04077	PHG 5L1340XP
	754-0173	PHG 5L370XP		754-0255	PHG 4L370XP		754-04093	PHG 3L350XP
	754-0177	PHG 4L320XP		754-0256	PHG 3L290XP		754-04118	PHG 5L1220XP
	754-0178	PHG 5L820XP		754-0257	PHG 3L380XP			
	754-0179	PHG 5L500XP					754-04122	PHG 4L900XP
				754-0260	PHG 5L510XP		754-04137	PHG 4L1140XP
	754-0180	PHG 5L540XP		754-0261	PHG 4L560XP		754-04142	PHG 4L910XP
	754-0181	PHG 4L1000XP		754-0264	PHG 4L520XP		754-04153	PHG 4L1220XP
	754-0182	PHG 5L810XP		754-0265	PHG 4L290XP		754-04219	PHG 4L1030XP
	754-0183	PHG 5L290XP		754-0266	PHG 4L850XP			
	754-0184	PHG 4L520XP					754-04240	PHG 4L1620XP
				754-0267	PHG 4L590XP		754-0427	PHG 5L710XP
	754-0185	PHG 4L490XP		754-0268	PHG 5L510XP		754-0428	PHG 4L420XP
	754-0186	PHG 4L820XP		754-0269	PHG 3L380XP		754-0429	PHG 3L460XP
	754-0187	PHG B22		754-0271	PHG 3L390XP		754-0430	PHG 3L350XP
	754-0188	PHG 5L510XP		754-0273	PHG 3L340XP			
	754-0189	PHG 4L440XP					754-0432	PHG 3L360XP
				754-0274	PHG 4L440XP		754-0433	PHG 5L690XP
	754-0190	PHG 4L390XP		754-0275	PHG 4L380XP		754-0434	PHG 4L580XP
	754-0191	PHG 4L650XP		754-0276	PHG 4L480XP		754-0438	PHG 4L510XP
	754-0192	PHG 4L340XP		754-0277	PHG 4L710XP		754-0439	PHG 4L600XP
	754-0193	PHG 4L350XP		754-0278	PHG 4L300XP			
	754-0194	PHG 4L450XP					754-0440	PHG 4L990XP
				754-0279	PHG 5L650XP		754-0441	PHG 4L760XP
	754-0195	PHG 4L540XP		754-0280	PHG 5L530XP		754-0443	PHG AA90
	754-0196	PHG 4L300XP		754-0280A	PHG 5L530XP		754-0446	PHG 5L450XP
	754-0197	PHG A115		754-0281	PHG 5L440XP		754-0453	PHG 5L360XP
	754-0198	PHG 4L620XP		754-0282	PHG 4L390XP			
	754-0200	PHG 4L480XP					754-0455	PHG 4L1030XP
				754-0283	PHG 4L950XP		754-0456	PHG 3L290XP
	754-0201	PHG 4L410XP		754-0284	PHG 5L410XP		754-0461	PHG 4L780XP
	754-0202	PHG 4L850XP		754-0285	PHG 4L340XP		754-0465	PHG 3L360XP
	754-0203	PHG 5L610XP		754-0287	PHG 4L290XP		754-0467	PHG 5L910XP
	754-0204	PHG 4L670XP		754-0290	PHG 4L470XP			
	754-0205	PHG 3L320XP					754-0467A	PHG 5L910XP
				754-0291	PHG 4L880XP		754-0468	PHG 5L420XP
	754-0206	PHG 4L500XP		754-0292	PHG 4L260XP		754-0472	PHG 5L830XP
	754-0207	PHG 4L420XP		754-0293	PHG 4L740XP		754-0474	PHG 5L1020XP
	754-0210	PHG 5L600XP		754-0294	PHG 4L890XP		754-0475	PHG 5L1090XP
	754-0211	PHG 5L460XP		754-0295	PHG 4L1110XP			
	754-0212	PHG 5L450XP					754-0476	PHG 5L1000XP
				754-0299	PHG 4L490XP		754-0485	PHG 5L970XP
	754-0213	PHG 4L530XP		754-0325	PHG 4L570XP		754-0486	PHG 5L670XP
	754-0214	PHG 4L500XP		754-0326	PHG 4L620XP		754-0486A	PHG 5L670XP
	754-0215	PHG 4L1070XP		754-0326A	PHG 4L620XP		754-0497	PHG 4L600XP
	754-0216	PHG 3L290XP		754-0327	PHG 5L280XP			
	754-0217	PHG 5L790XP					754-0498	PHG 4L670XP
				754-0328	PHG 5L490XP		754-0637	PHG 3L310XP
	754-0218	PHG 5L590XP		754-0329	PHG 5L690XP		754-0637A	PHG 3L310XP
	754-0219	PHG 4L260XP		754-0329A	PHG 5L690XP		754-0340	PHG 5L840XP
	754-0220	PHG 5L270XP		754-0330	PHG 4L900XP		754-0642	PHG 5L1380XP
	754-0221	PHG 5L520XP		754-0338	PHG 4L770XP			
	754-0222	PHG 4L440XP					754-0935	PHG 4L310XP
				754-0339	PHG 4L790XP		754-0936	PHG 4L470XP
	754-0223	PHG 3L360XP		754-0340	PHG 5L840XP		754-0937	PHG 5L690XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Mtd	754-0938 754-1038	PHG 5L590XP PHG 5L500XP	Mtd	954-0280A	PHG 5L530XP	Mtd	GW-7540350	PHG 5L640XP
	754-170 754-178 754-184 754-212 754-219A	PHG 5L500XP PHG 5L820XP PHG 4L520XP PHG 5L470XP PHG 4L880XP		954-0281 954-0293 954-0329A 954-0339A 954-0343	PHG 4L440XP PHG 4L740XP PHG 5L690XP PHG 4L790XP PHG 3L310XP	Noma/Amf/Dynamark	383 385 958 992 2363	PHG 4L240XP PHG 4L480XP PHG 4L220XP PHG 4L230XP PHG 4L440XP
	754-227 754-244 754-245 754-264 754-277	PHG 5L630XP PHG 4L400XP PHG 4L590XP PHG 4L520XP PHG 4L710XP		954-0346 954-0349 954-0350 954-0355 954-0363	PHG 3L300XP PHG 4L790XP PHG 5L640XP PHG 4L670XP PHG 5L660XP		2543 3145 4231 8271 8597	PHG 4L280XP PHG 3L230XP PHG 4L410XP PHG 4L250XP PHG 4L220XP
	754-3002 754-3003 754-3004 754-3006 754-3007	PHG 4L720XP PHG 5L890XP PHG 4L780XP PHG 5L930XP PHG 4L590XP		954-0364 954-0367 954-0369 954-0370 954-0371	PHG 5L680XP PHG 4L340XP PHG 3L330XP PHG 5L490XP PHG 5L740XP		8869 20317 20319 20368 20582	PHG 4L330XP PHG 4L200XP PHG 4L200XP PHG 4L290XP PHG 4L430XP
	754-3012 754-3018 754-3021 754-3023 754-3024	PHG 4L320XP PHG 4L860XP PHG 4L910XP PHG 5L940XP PHG 4L910XP		954-0371A 954-04001A 954-04014 954-04032 954-04032A	PHG 5L740XP PHG 5L690XP PHG 3L270XP PHG 3L360XP PHG 3L360XP		20998 21865 23164 24551 24829	PHG 4L420XP PHG 4L260XP PHG 4L250XP PHG 4L250XP PHG 4L300XP
	754-3025 754-3026 754-3027 754-3029 754-3035	PHG 4L900XP PHG 4L600XP PHG 4L860XP PHG 4L590XP PHG 4L900XP		954-04032B 954-04033 954-04041 954-04043 954-04043A	PHG 3L360XP PHG 4L1180XP PHG 5L1110XP PHG 4L570XP PHG 4L570XP		25807 25812 25883 26659 27323	PHG 5L330XP PHG A17 PHG 5L430XP PHG 5L720XP PHG 4L410XP
	754-3036 754-3037 754-3038 754-3050 754-3053	PHG 4L630XP PHG 4L800XP PHG 4L610XP PHG 4L660XP PHG 4L1070XP		954-04045 954-04048 954-04060 954-04064 954-04074A	PHG 4L1090XP PHG 5L1300XP PHG 4L960XP PHG 5L680XP PHG 4L780XP		28148 28165 28594 29198 29281	PHG 4L260XP PHG 4L260XP PHG 4L350XP PHG 4L250XP PHG 5L750XP
	754-3066 754-342 754-4001A 754-4045 754-4048	PHG 5L620XP PHG 4L680XP PHG 5L690XP PHG 4L1090XP PHG 5L1310XP		954-04077 954-04118 954-04122 954-04142 954-04165	PHG 5L1340XP PHG 4L1220XP PHG 4L900XP PHG 4L910XP PHG 4L780XP		29454 29798 30839 30997 30998	PHG 4L880XP PHG 4L250XP PHG 5L730XP PHG 4L470XP PHG 4L420XP
	754-4062 754-4064 942-04062 954-0016 954-0101A	PHG 4L780XP PHG 5L680XP PHG 4L770XP PHG 5L830XP PHG 3L350XP		954-04176A 954-04219 954-04240 954-04259A 954-0427	PHG AX32 PHG 4L1030XP PHG 4L1630XP PHG 4L340XP PHG 5L710XP		31053 32131 32132 32668 32986	PHG 4L250XP PHG 4L390XP PHG 4L390XP PHG 4L330XP PHG 5L820XP
	954-0109 954-0111 954-0114 954-0125 954-0131	PHG 4L430XP PHG 4L450XP PHG 4L240XP PHG 4L1050XP PHG 3L350XP		954-04285 954-0430 954-0430A 954-0430B 954-0432	PHG 5L350XP PHG 3L350XP PHG 3L350XP PHG 3L350XP PHG 3L360XP		36607 39454 39455 39456 40899	PHG 5L630XP PHG 4L880XP PHG 4L350XP PHG 5L690XP PHG 4L350XP
	954-0138 954-0145 954-0145A 954-0151 954-0155	PHG 5L500XP PHG 4L690XP PHG 4L690XP PHG 5L670XP PHG 3L400XP		954-0433 954-0434 954-0439 954-0440 954-0441	PHG 5L690XP PHG 4L580XP PHG 4L600XP PHG 4L990XP PHG 4L760XP		41200 41390 41405 41505 41740	PHG 4L200XP PHG 4L710XP PHG 4L350XP PHG 4L350XP PHG 4L380XP
	954-0177 954-0178 954-0180 954-0181 954-0194	PHG 4L320XP PHG 5L820XP PHG 5L540XP PHG 4L990XP PHG 4L450XP		954-0446 954-0453 954-0456 954-0461 954-0465	PHG 5L450XP PHG 5L360XP PHG 3L290XP PHG 4L780XP PHG 3L360XP		42035 42111 42132 42846 42858	PHG 3L400XP PHG 5L700XP PHG 4L350XP PHG 4L500XP PHG 4L390XP
	954-0197 954-0198 954-0201 954-0216 954-0224	PHG 4L1170XP PHG 4L620XP PHG 4L410XP PHG 3L290XP PHG 5L250XP		954-0467 954-0467A 954-0468 954-0472 954-0474	PHG 5L910XP PHG 5L910XP PHG 5L420XP PHG 5L830XP PHG 5L1020XP		42881 43066 43124 43919 43979	PHG 5L710XP PHG 5L710XP PHG 4L290XP PHG 4L560XP PHG 4L560XP
	954-0225 954-0226 954-0228 954-0230 954-0234	PHG 4L1070XP PHG 4L820XP PHG 5L620XP PHG 4L560XP PHG 4L410XP		954-0476 954-0483 954-0485 954-0486 954-0486A	PHG 5L1000XP PHG 3L380XP PHG 5L970XP PHG 5L670XP PHG 5L670XP		44039 44148 44150 44190 44264	PHG 4L440XP PHG 4L630XP PHG 4L410XP PHG 4L320XP PHG 4L980XP
	954-0240 954-0241 954-0241A 954-0255 954-0264	PHG 5L380XP PHG 5L350XP PHG 5L350XP PHG 4L370XP PHG 4L520XP		954-0497 954-0498 954-0637 954-0935 954-0405	PHG 4L600XP PHG 4L670XP PHG 3L310XP PHG 4L310XP PHG 4L1090XP		44313 45106 45181 45186 45187	PHG 4L520XP PHG 4L630XP PHG 4L440XP PHG 4L630XP PHG 4L440XP
	954-0266 954-0266A 954-0271 954-0280	PHG 4L850XP PHG 4L850XP PHG 3L390XP PHG 5L530XP		954-0408 954-04062 954-04064 A610 GW-1733439	PHG 5L1310XP PHG 4L780XP PHG 5L680XP PHG 5L310XP PHG 4L350XP		45216 45217 45509 46466	PHG 4L430XP PHG 4L390XP PHG 4L530XP PHG 5L830XP

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Noma/Amf/Dynamark	47200	PHG 4L290XP	Noma/Amf/Dynamark	318372	PHG 5L850XP	Razor	7540128	PHG 5L350XP
	47201	PHG 4L250XP		319005	PHG 5L810XP		7540937	PHG 5L590XP
	47390	PHG 4L710XP		320534	PHG 4L740XP	Roof	426	PHG 4L560XP
	47611	PHG 4L880XP		321147	PHG 4L540XP		428	PHG 5L710XP
	48044	PHG 5L820XP		321206	PHG 4L450XP		428	PHG 5L620XP
	48259	PHG 3L450XP		1501000	PHG 4L900XP		430	PHG 4L340XP
	48529	PHG 3L450XP		1501001	PHG 4L880XP		431	PHG 5L450XP
	48530	PHG 3L430XP		1501105	PHG 5L510XP		452	
	49018	PHG 5L840XP		1501245	PHG 4L870XP		512	PHG 4L290XP
	49045	PHG 4L880XP		90005938	PHG 3L300XP		1350	PHG 5L1000XP
	49233	PHG 3L440XP		511275M1	PHG 4L1020XP		1351	PHG 5L570XP
	49405	PHG 4L880XP		511277M2	PHG 4L500XP	Scag	48081	PHG 5L800XP
	49570	PHG 4L350XP		511277M3	PHG 4L500XP		48083	PHG 5L890XP
	49580	PHG 4L410XP		514132M1	PHG 4L300XP		48085	PHG 4L380XP
	49818	PHG 5L840XP		514806M1	PHG 4L350XP		48087	PHG 5L530XP
	49870	PHG 5L840XP		527711M1	PHG 4L920XP		48088	PHG 5L1030XP
	50131	PHG 4L840XP		L450	PHG 4L500XP		48089	PHG 5L890XP
	50137	PHG 4L840XP		L489	PHG 4L890XP		48203	PHG 4L400XP
	50170	PHG 5L750XP		LP2154	PHG 4L200XP		48204	PHG 5L820XP
	50272	PHG 4L350XP		LP383	PHG 4L240XP		48207	PHG 5L860XP
	50307	PHG 3L280XP		LP708	PHG 5L380XP		48265	PHG 5L630XP
	50591	PHG 4L300XP		PA8271	PHG 4L250XP		48278	PHG 5L780XP
	50597	PHG 4L300XP		PA8408	PHG 4L220XP		48285	PHG 5L560XP
	50731	PHG 4L840XP		RM2543	PHG 4L280XP		48286	PHG 5L930XP
	50737	PHG 4L840XP		RP8094	PHG 4L240XP		48295	PHG 5L680XP
	50754	PHG 4L650XP		RP8095	PHG 4L250XP		48344	PHG 4L350XP
	50755	PHG 4L380XP		RP8096	PHG 4L260XP		48359	PHG 5L940XP
	50834	PHG 4L300XP		SP149	PHG A16		48472	PHG 4L530XP
	50876	PHG 3L380XP	Penney'S	20556	PHG 4L480XP		48530	PHG 5L1030XP
	50877	PHG 3L410XP		20558	PHG 4L640XP		48553	PHG 5L500XP
	50935	PHG 5L770XP		105340	PHG 5L960XP		48581	PHG 4L570XP
	51214	PHG 4L850XP		241749	PHG 4L410XP		48587	PHG 4L570XP
	51458	PHG 4L390XP		241750	PHG 4L310XP		48749	PHG 4L580XP
	51855	PHG 4L410XP		248940	PHG 3L330XP		48760	PHG 4L610XP
	51865	PHG 4L260XP		532120302	PHG 4L900XP		48799	PHG 5L1150XP
	52450	PHG 3L290XP	Poulan (Also See Ayp)	532140910	PHG 4L780XP		48912	PHG 5L1170XP
	52467	PHG 4L870XP		532408007	PHG 5L380XP		48996	PHG 5L1350XP
	52714	PHG 4L850XP		532427304	PHG 4L370XP		481557	PHG 5L1230XP
	52842	PHG 4L960XP		532437261	PHG 4L290XP		481558	PHG 5L1400XP
	53162	PHG 4L500XP		539117245	PHG 5L1220XP		481749	PHG 4L590XP
	53301	PHG 3L430XP		532083691	PHG 3L350XP		481880	PHG 5L860XP
	53307	PHG 3L430XP		532106085	PHG 4L790XP		481980	PHG 5L1620XP
	53363	PHG 4L690XP		532110883	PHG 4L990XP		482009	PHG 4L520XP
	53443	PHG 3L340XP		532110884	PHG 4L940XP		482090	PHG 5L1070XP
	53499	PHG 4L300XP		532123461	PHG 4L810XP		482091	PHG 5L530XP
	53790	PHG 3L370XP		532123796	PHG 4L950XP		482138	PHG 5L500XP
	53833	PHG 4L810XP		532124293	PHG 4L800XP		482140	PHG 5L550XP
	54758	PHG 4L820XP		532124525	PHG 4L890XP		482171	PHG 4L600XP
	54830	PHG 4L710XP		532131264	PHG 4L790XP		482281	PHG 5L1210XP
	55442	PHG 4L580XP		532137078	PHG 3L320XP		482529	PHG 5L1480XP
	55450	PHG 4L420XP		532139573	PHG 4L840XP		482530	PHG 5L1550XP
	55914	PHG 3L310XP		532140067	PHG 4L830XP		482652	PHG 5L1760XP
	57556	PHG 4L890XP		532141416	PHG 4L840XP		482716	PHG 4L610XP
	58110	PHG 5L750XP		532144200	PHG 4L890XP		482876	PHG BX41
	72046	PHG 3L310XP		532419271	PHG 4L880XP		483001	PHG 5L1320XP
	72106	PHG 3L370XP		532419744	PHG A32		483002	PHG 5L1490XP
	72119	PHG 4L300XP		539114557	PHG 5L1540XP		483084	PHG BX62
	72126	PHG 3L360XP	Razor	754103	PHG 4L250XP		483157	PHG BX62
	72127	PHG 3L410XP		754104	PHG 4L320XP		483165	PHG BX77
	88690	PHG 4L330XP		754109	PHG 4L430XP		483166	PHG BX78
	300149	PHG 4L470XP		754118	PHG 5L630XP		483172	PHG BX63
	300515	PHG 4L340XP		754121	PHG 4L310XP		483239	PHG BX47
	300600	PHG 5L780XP		754124	PHG 4L570XP		483240	PHG BX52
	300650	PHG 5L780XP		754127	PHG 5L660XP		483241	PHG 5L1170XP
	300741	PHG 4L690XP		754128	PHG 5L350XP		483242	PHG 5L1250XP
	300747	PHG 4L690XP		754937	PHG 5L590XP		483243	PHG 5L1350XP
	300842	PHG 5L790XP		1540125	PHG 4L1050XP		483314	PHG AX79
	302291	PHG 5L640XP		7540103	PHG 4L250XP		483325	PHG 5L1410XP
	302719	PHG 4L910XP		7540104	PHG 4L320XP		483326	PHG 5L1480XP
	305184	PHG 5L830XP		7540109	PHG 4L430XP		483518	PHG 5L930XP
	305667	PHG 5L760XP		7540118	PHG 5L630XP		483741	PHG 5L1370XP
	305698	PHG 4L730XP		7540121	PHG 4L310XP		483969	PHG 4L860XP
	309715	PHG 4L440XP		7540124	PHG 4L570XP		484088	PHG 5L1520XP
	314108	PHG 5L850XP		7540127	PHG 5L660XP		484159	PHG 5L770XP
	314120	PHG 4L870XP					484372	PHG 5L830XP
	314572	PHG 4L800XP					48202A	PHG 48202

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
Scag	483012 A48081 A48083 A48286	PHG 5L520XP PHG 5L800XP PHG 5L890XP PHG 5L930XP	Simplicity	174486 174687 174731	PHG 5L490XP PHG 4L730XP PHG 4L530XP	Simplicity	2118488 2121228	PHG 3L340XP PHG 4L370XP
Simplicity	54273 101136 101137 105067 105115	PHG 5L420XP PHG 4L640XP PHG 4L680XP PHG 5L510XP PHG 4L620XP		174883 174911 175361 175439 176393	PHG 4L340XP PHG 4L440XP PHG 4L290XP PHG 4L740XP PHG 3L370XP		2158389 2163011 2172420 2174687 16907967	PHG 4L290XP PHG 4L720XP PHG 4L930XP PHG 4L730XP PHG 4L520XP
	105122 105280 105287 105340 106055	PHG 5L560XP PHG 5L640XP PHG 5L880XP PHG 5L960XP PHG 5L580XP		176439 176917 177126 177452 1601672	PHG 4L740XP PHG 4L350XP PHG 4L790XP PHG 4L620XP PHG 4L610XP		1601672SM 1607967SM 1608954SM 1610-98 1650502SM	PHG 4L610XP PHG 4L520XP PHG 4L330XP PHG 4L390XP PHG 4L460XP
	106390 106689 106723 106769 108099	PHG 4L360XP PHG 4L550XP PHG 4L790XP PHG 4L560XP PHG 4L440XP		1607813 1608954 1608957 1608960 1615005	PHG 4L830XP PHG 4L330XP PHG 4L490XP PHG 4L350XP PHG 4L400XP		16569605SM 1657044SM 1664457SM 1664644SM 1664789SM	PHG 4L840XP PHG 4L930XP PHG 4L410XP PHG 4L1030XP PHG 4L890XP
	108151 108175 108248 108389 108407	PHG 4L630XP PHG 4L560XP PHG 4L480XP PHG 4L990XP PHG 4L470XP		1651201 1655069 1656655 1657806 1663009	PHG 4L730XP PHG 4L910XP PHG 4L410XP PHG 4L360XP PHG 3L280XP		1664946SM 1665024SM 1665706SM 1666654SM 1666655SM	PHG 4L570XP PHG 4L540XP PHG 4L390XP PHG 3L320XP PHG 4L410XP
	108458 109061 114224 118068 118225	PHG 4L450XP PHG 4L280XP PHG 4L660XP PHG 4L340XP PHG 4L250XP		1664457 1664644 1664946 1665450 1665666	PHG 4L410XP PHG 4L1020XP PHG 4L570XP PHG 4L870XP PHG 5L770XP		1668066SM 1669394SM 1669937SM 1669937SM 1674308SM	PHG 4L1200XP PHG 5L500XP PHG 5L540XP PHG 3L310XP PHG 4L370XP
	118312 118494 121078 121216 121228	PHG 4L340XP PHG 3L340XP PHG 4L350XP PHG 4L380XP PHG 4L310XP		1665706 1666324 1666654 1666655 1666801	PHG 4L390XP PHG 4L690XP PHG 3L320XP PHG 4L410XP PHG 4L800XP		1674312SM 1674898SM 1674899SM 1675704SM 1676460SM	PHG 4L370XP PHG 5L500XP PHG 5L560XP PHG 3L340XP PHG 4L430XP
	121398 122039 122060 122069 122120	PHG 4L430XP PHG 3L320XP PHG 3L360XP PHG 4L530XP PHG 3L340XP		1667200 1667506 1668065 1669394 1669937	PHG 4L340XP PHG 4L390XP PHG 4L690XP PHG 5L500XP PHG 5L540XP		1676461SM 1678354SM 1678600SM 1700415SM 1701257SM	PHG 4L330XP PHG 4L420XP PHG 3L630XP PHG 3L320XP PHG 4L420XP
	122146 123073 124025 147883 152017	PHG 3L380XP PHG 4L910XP PHG 4L300XP PHG 4L340XP PHG 5L450XP		1671788 1672732 1673667 1674308 1674312	PHG 3L460XP PHG 3L310XP PHG 4L950XP PHG 4L350XP PHG 4L350XP		1703371SM 1703372SM 1703466SM 1703836SM 1707381SM	PHG 4L1450XP PHG 4L1450XP PHG 4L1260XP PHG 4L910XP PHG 4L860XP
	153091 154273 154307 155307 156120	PHG 4L440XP PHG 5L420XP PHG 4L350XP PHG 4L350XP PHG 4L630XP		1674898 1674899 1676460 1676461 1678354	PHG 5L500XP PHG 5L560XP PHG 4L430XP PHG 3L330XP PHG 4L420XP		1707740SM 1711777SM 1712481SM 1712482SM 1712595SM	PHG 4L690XP PHG 4L1170XP PHG 4L600XP PHG 4L780XP PHG BX108
	156231 157230 157424 157524 157683	PHG 4L420XP PHG 3L220XP PHG 3L390XP PHG 3L390XP PHG 4L290XP		1679915 1700415 1701257 1705563 1707381	PHG 3L390XP PHG 3L320XP PHG 4L420XP PHG 4L740XP PHG 4L860XP		1712596SM 1712937SM 1713515SM 1715127SM 1715128SM	PHG AX120 PHG AX110 PHG 4L780XP PHG 4L350XP PHG 4L360XP
	158389 158460 158573 161098 161146	PHG 4L290XP PHG 4L310XP PHG 4L310XP PHG 4L390XP PHG 4L340XP		1707740 2025341 2025364 2025463 2025492	PHG 4L690XP PHG 4L440XP PHG 4L820XP PHG 4L530XP PHG 5L450XP		1715591SM 1717393SM 1718017SM 1719233SM 1720234SM	PHG 3L340XP PHG 4L360XP PHG 4L1140XP PHG 4L1140XP PHG 4L1140XP
	162081 164146 165048 165806 166172	PHG 4L760XP PHG 4L340XP PHG 4L850XP PHG 4L360XP PHG 4L470XP		2025641 2025712 2029350 2029665 2029748	PHG 5L420XP PHG 5L490XP PHG 4L530XP PHG 4L1000XP PHG 4L340XP		1720402SM 1721532SM 1723391SM 1725371SM 1725416SM	PHG 4L1140XP PHG 4L830XP PHG 4L820XP PHG 3L320XP PHG 4L430XP
	166570 167031 170164 170771 170921	PHG 4L390XP PHG 4L830XP PHG 4L770XP PHG 4L360XP PHG 4L240XP		2029789 2029828 2029829 2087648 2087732	PHG 4L340XP PHG 3L370XP PHG 4L350XP PHG 4L720XP PHG 4L780XP		1728008SM 1732086SM 1732249SM 1733324SM 1734114SM	PHG 4L890XP PHG 4L890XP PHG 4L420XP PHG 3L320XP PHG 4L700XP
	172066 172420 172929 173461 173948	PHG 5L290XP PHG 4L930XP PHG 3L330XP PHG 4L1000XP PHG 4L570XP		2087759 2087836 2087883 2108099 2108209	PHG 4L660XP PHG 4L740XP PHG 3L340XP PHG 4L440XP PHG 4L820XP		1737220VP 1753941YP 1753942YP 2108248SM 2108458SM	PHG 4L1320XP PHG 4L440XP PHG 4L440XP PHG 4L480XP PHG 4L480XP
	174224 174364	PHG 4L660XP PHG 4L490XP		2108300 2108450 2118068	PHG 4L420XP PHG 4L850XP PHG 4L340XP		2121078SM 2121216SM 2121398SM 2154273SM	PHG 4L350XP PHG 4L380XP PHG 3L330XP PHG 5L420XP



Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-	-	-	-
<b>Simplicity</b>	2156120SM	PHG 4L630XP	<b>Snapper</b>	76353	PHG 5L850XP	<b>Toro/Wheel</b>	9431	PHG 4L390XP
	2158573SM	PHG 4L310XP		76496	PHG 5L890XP		9691	PHG 4L700XP
	2161098SM	PHG 4L390XP		76497	PHG 5L440XP		9750	PHG 5L690XP
	2165048SM	PHG 4L850XP		76498	PHG 5L360XP		9782	PHG 4L690XP
	2168171SM	PHG 3L480XP		76676	PHG 5L520XP		9783	PHG 4L710XP
	2170164SM	PHG 4L770XP		76677	PHG 5L940XP		10242	PHG 4L770XP
	2170771SM	PHG 3L360XP		76680	PHG 5L360XP		13881	PHG 4L290XP
	2170921SM	PHG 4L240XP		76680	PHG 5L940XP		27115	PHG 4L360XP
	2172444SM	PHG 4L1160XP		76880	PHG 5L370XP		27140	PHG 4L290XP
	2174364SM	PHG 4L490XP		77094	PHG 4L290XP		27156	PHG 4L340XP
	2174915SM	PHG 4L860XP		79168	PHG 4L960XP		27158	PHG 4L340XP
	2175361SM	PHG 4L290XP		79190	PHG 5L1000XP		27168	PHG 5L430XP
	2176439SM	PHG 4L740XP		79196	PHG 4L1070XP		27173	PHG 4L350XP
	2176917SM	PHG 4L370XP		79333	PHG 5L570XP		27174	PHG 4L340XP
	2177452SM	PHG 4L620XP		222069	PHG 3L240XP		27181	PHG 4L390XP
	5022148SM	PHG 5L1500XP		2813861	PHG 3L330XP		27185	PHG 4L500XP
	5022667SM	PHG 5L1390XP		7012508	PHG 3L240XP		27191	PHG 5L480XP
	5023256SM	PHG 4L1510XP		7029604	PHG 3L330XP		27193	PHG 4L610XP
	5023297SM	PHG 5L1470XP		7076496	PHG 5L890XP		27195	PHG 4L350XP
	5023496SM	PHG 5L1420XP		7076497	PHG 5L440XP		27199	PHG 4L610XP
	5102145YP	PHG 4L1450XP		7076498	PHG 5L360XP		31182	PHG 3L300XP
	5103391YP	PHG 5L1760XP		7076677	PHG 5L940XP		31560	PHG 4L500XP
	8161244	PHG 4L380XP		7076680	PHG 5L360XP		31662	PHG 4L230XP
	LM-16029-69	PHG 4L800XP	<b>Toro/Wheel</b>	874	PHG 5L770XP		31663	PHG 3L270XP
	LM-16079-67	PHG 4L520XP		1473	PHG 4L320XP		32733	PHG 4L250XP
	LM-80210-77	PHG 4L390XP		1526	PHG 4L220XP		34577	PHG 4L470XP
	SSA101	PHG SPA850		1550	PHG 4L420XP		34663	PHG 3L280XP
				1552	PHG 4L350XP		36348	PHG 4L430XP
<b>Snapper</b>	10034	PHG 4L290XP		1552	PHG 4L350XP		36593	PHG 4L410XP
	10056	PHG 4L250XP		1554	PHG 4L240XP		37274	PHG 3L320XP
	10108	PHG 4L240XP		1555	PHG 4L440XP		38093	PHG 4L260XP
	10109	PHG 4L400XP		1561	PHG 4L300XP		38095	PHG 4L340XP
	10419	PHG 4L260XP		1563	PHG 4L390XP		38166	PHG 4L400XP
	10467	PHG 4L340XP		1569	PHG 4L290XP		50104	PHG 4L510XP
	10678	PHG 4L680XP		1576	PHG 4L700XP		51583	PHG 4L240XP
	10708	PHG 4L450XP		1577	PHG 4L280XP		57000	PHG 4L430XP
	10729	PHG 4L430XP		1578	PHG 3L370XP		70073	PHG 4L340XP
	10747	PHG 4L560XP		1580	PHG 4L310XP		70074	PHG 3L310XP
	10748	PHG 4L340XP		1586	PHG 4L760XP		70161	PHG 4L600XP
	10836	PHG 3L390XP		1588	PHG 4L590XP		70162	PHG 5L320XP
	10849	PHG 3L250XP		1589	PHG 4L570XP		70354	PHG 4L330XP
	10851	PHG 4L440XP		1595	PHG 4L670XP		70530	PHG 3L350XP
	11946	PHG 4L280XP		1595	PHG 4L670XP		70550	PHG 3L270XP
	11948	PHG 4L300XP		1596	PHG 4L510XP		70551	PHG 3L380XP
	11969	PHG 4L510XP		1597	PHG 3L250XP		70657	PHG 3L320XP
	12020	PHG 4L350XP		1599	PHG 4L280XP		70694	PHG 4L300XP
	12053	PHG 4L450XP		2058	PHG 4L300XP		70737	PHG 5L360XP
	12248	PHG 4L250XP		5950	PHG 4L280XP		70824	PHG 4L310XP
	12249	PHG 4L350XP		6489	PHG 4L780XP		70827	PHG 4L310XP
	12508	PHG 3L240XP		6506	PHG 4L320XP		70946	PHG 4L300XP
	12524	PHG 5L900XP		6551	PHG 3L310XP		72166	PHG 3L320XP
	12561	PHG 4L540XP		6552	PHG 3L300XP		73476	PHG 4L620XP
	13436	PHG 4L540XP		6573	PHG 4L380XP		73887	PHG 4L290XP
	13936	PHG 3L380XP		6737	PHG 4L690XP		73888	PHG 4L460XP
	13937	PHG 4L390XP		6738	PHG 3L380XP		73890	PHG 4L450XP
	13938	PHG 3L370XP		6771	PHG 4L710XP		73975	PHG 4L500XP
	14225	PHG 4L1000XP		6993	PHG 4L220XP		74228	PHG 4L480XP
	14353	PHG 4L620XP		7358	PHG 4L660XP		74231	PHG 4L330XP
	14560	PHG 4L990XP		7430	PHG 4L280XP		74232	PHG 4L710XP
	14637	PHG 3L330XP		7473	PHG 5L820XP		74233	PHG 4L710XP
	14716	PHG 4L360XP		7776	PHG 4L870XP		76740	PHG 4L430XP
	14717	PHG 4L390XP		8005	PHG 4L720XP		79160	PHG 4L570XP
	14801	PHG 4L940XP		8133	PHG 4L740XP		85660	PHG 3L330XP
	15151	PHG 4L340XP		8160	PHG 5L830XP		100129	PHG 5L500XP
	15152	PHG 4L350XP		8231	PHG 4L700XP		101137	PHG 4L680XP
	15757	PHG 5L690XP		8334	PHG 5L850XP		102607	PHG 4L890XP
	19534	PHG 4L350XP		8412	PHG 4L860XP		102743	PHG 5L670XP
	19551	PHG 4L430XP		8430	PHG 4L590XP		102868	PHG 4L1050XP
	19581	PHG 4L960XP		8677	PHG 4L520XP		103345	PHG 3L250XP
	19607	PHG 4L390XP		8687	PHG 4L520XP		103522	PHG 4L850XP
	20560	PHG 4L500XP		8911	PHG 4L830XP		104290	PHG 4L290XP
	21354	PHG 4L220XP		8975	PHG 4L580XP		104388	PHG 4L550XP
	23226	PHG 4L310XP		8976	PHG 4L550XP		104633	PHG 4L360XP
	23282	PHG 4L350XP		9151	PHG 5L960XP		104865	PHG 4L550XP
	29604	PHG 3L330XP		9360	PHG 4L950XP		105476	PHG 4L800XP
	76085	PHG 4L350XP		9430	PHG 4L360XP		105477	PHG 4L400XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Toro/Wheel	106516	PHG 4L830XP	Toro/Wheel	263340	PHG 4L330XP	Toro/Wheel	115-4972	PHG 5L1850XP
	106518	PHG 4L870XP		263540	PHG 4L340XP		115-7407	PHG 5L1750XP
	106523	PHG 4L410XP		269610	PHG 4L400XP		115-7426	PHG 5L1830XP
	106533	PHG 4L400XP		269670	PHG 4L400XP		115-9613	PHG 4L750XP
	106571	PHG 4L800XP		271100	PHG 4L500XP		117-9607	PHG 4L1640XP
	106751	PHG 4L800XP		271102	PHG 5L850XP		119-8819	PHG 4L1130XP
	107298	PHG 4L720XP		271104	PHG 4L380XP		119-8820	PHG 4L1410XP
	107320	PHG 4L600XP		282650	PHG 4L1020XP		119-8821	PHG 4L810XP
	107740	PHG 4L630XP		285250	PHG 4L530XP		1-603045	PHG 4L1120XP
	107939	PHG 5L830XP		362920	PHG 4L610XP		17-0850	PHG 4L400XP
	108195	PHG 4L670XP		368070	PHG 3L340XP		19-2650	PHG 4L370XP
	108427	PHG 4L880XP		411420	PHG 4L660XP		23-9080	PHG 4L400XP
	108501	PHG 5L820XP		420880	PHG 4L230XP		26-9670	PHG 4L400XP
	108502	PHG 5L830XP		420881	PHG 4L220XP		26-9670-09	PHG 4L400XP
	108503	PHG 4L590XP		420882	PHG 4L220XP		26-9672	PHG 4L300XP
	108834	PHG 4L980XP		420883	PHG 4L240XP		27-0230	PHG 4L400XP
	109428	PHG 4L760XP		496950	PHG 4L580XP		3-7274	PHG 3L320XP
	110082	PHG 4L480XP		499100	PHG 3L400XP		51-3530	PHG 4L510XP
	110141	PHG 4L410XP		512490	PHG 4L530XP		54-2750	PHG 5L700XP
	110420	PHG 4L480XP		513530	PHG 4L510XP		54-2750-09	PHG 5L700XP
	111710	PHG 4L530XP		513600	PHG 4L630XP		5-4505	PHG 3L320XP
	111720	PHG 4L530XP		541360	PHG 4L490XP		88-6250	PHG 4L870XP
	111730	PHG 4L350XP		541380	PHG 4L740XP		91-2258	PHG 3L350XP
	111740	PHG 4L600XP		541390	PHG 4L560XP		99-4647	PHG B143
	113072	PHG 4L1020XP		542751	PHG 5L690XP		A43	PHG 4L450XP
	113105	PHG 4L330XP		565570	PHG 4L540XP		A52	PHG 4L540XP
	113141	PHG 4L760XP		574750	PHG 4L580XP		H0364	PHG 4L330XP
	113288	PHG 4L530XP		576690	PHG 4L820XP		MW10366	PHG 4L360XP
	113912	PHG 4L440XP		576990	PHG 4L820XP		MW10367	PHG 4L330XP
	114020	PHG 4L480XP		577000	PHG 4L430XP		MWJ0366	PHG 4L360XP
	114421	PHG 4L530XP		623900	PHG 3L350XP		WV5403A	PHG 5L290XP
	114433	PHG 4L830XP		944399	PHG 5L740XP	Troy-Bilt	9245	PHG 4L220XP
	114567	PHG 4L480XP		1133303	PHG 4L340XP		20565	PHG 4L240XP
	114718	PHG 4L460XP		5770000	PHG 4L430XP		239661	PHG 3L360XP
	114833	PHG 4L820XP		10-0230	PHG 4L400XP		1722095	PHG 5L440XP
	114860	PHG 4L930XP		10-3345	PHG 3L250XP		1751601	PHG 3L310XP
	114895	PHG 5L830XP		103-4761	PHG AX51		1769767	PHG 4L660XP
	116160	PHG 5L720XP		104-3126	PHG 5L580XP		1770334	PHG 4L580XP
	116183	PHG 5L510XP		104-3127	PHG 5L580XP		1813271	PHG 4L550XP
	116332	PHG 5L650XP		105-6963	PHG 4L1410XP		1813561	PHG 4L550XP
	116527	PHG 4L430XP		105-6977	PHG 4L1470XP		1894272	PHG 3L350XP
	116666	PHG 5L770XP		105-7790	PHG 5L2260XP		1894335	PHG 3L360XP
	116667	PHG 4L850XP		105-8783	PHG 5L2420XP		1902235	PHG 5L290XP
	118068	PHG 4L340XP		106-2173	PHG 4L1170XP		754-04003	PHG 3L320XP
	118116	PHG 3L360XP		106-2174	PHG 4L280XP		754-04093	PHG 3L350XP
	118225	PHG 4L250XP		106-6998	PHG 4L1170XP		754-04101	PHG 3L310XP
	118312	PHG 4L340XP		106-7350	PHG 5L2640XP		754-04107	PHG 5L1350XP
	124180	PHG 4L410XP		106-7369	PHG 4L1060XP		754-04142	PHG 4L910XP
	124780	PHG 4L470XP		107-1735	PHG 4L1320XP		754-04219	PHG 4L1030XP
	126220	PHG 4L330XP		108-5915	PHG 5L2020XP		754-04240	PHG 4L1620XP
	126420	PHG 4L410XP		108-7190	PHG 4L1450XP		754-0637A	PHG 3L310XP
	126430	PHG 4L460XP		108-7192	PHG 4L1380XP		954-04142	PHG 4L910XP
	126520	PHG 4L330XP		109-3388	PHG 4L750XP		954-04165	PHG 4L780XP
	126550	PHG 4L540XP		109-3661	PHG 4L1540XP		954-04176A	PHG AX32
	128260	PHG 4L450XP		109-5364	PHG 4L1460XP		954-04219	PHG 4L1030XP
	188890	PHG 4L450XP		109-8069	PHG 4L750XP		954-04240	PHG 4L1630XP
	192220	PHG 4L440XP		110-6774	PHG AX60		954-04259A	PHG 4L340XP
	192790	PHG 4L410XP		110-6871	PHG 4L1120XP		954-0456	PHG 3L290XP
	196960	PHG 4L350XP		110-6892	PHG 4L1400XP		954-05001	PHG 4L430XP
	200170	PHG 4L530XP		112-0301	PHG 5L900XP		GW56035	PHG 4L220XP
	200554	PHG 4L460XP		112-0305	PHG 5L420XP		GW-9245	PHG 4L220XP
	200555	PHG 3L460XP		112-0317	PHG 4L790XP		T1769767	PHG 4L660XP
	205990	PHG 3L500XP		112-0332	PHG 5L1340XP	Western	1110	PHG 4L350XP
	208527	PHG 4L480XP		112-0933	PHG 5L1370XP		1205	PHG 4L220XP
	208626	PHG 3L270XP		112-5800	PHG 4L1090XP		1210	PHG 4L250XP
	225360	PHG 4L630XP		112-5834	PHG 4L900XP		1212	PHG 3L360XP
	230220	PHG 3L370XP		112-5951	PHG 4L780XP		1216	PHG 4L730XP
	239050	PHG 4L400XP		112-6147	PHG 4L780XP		1218	PHG 4L350XP
	239080	PHG 4L400XP		112-6171	PHG 4L1220XP		1221	PHG 3L260XP
	248940	PHG 3L330XP		114-0453	PHG 4L1410XP		1227	PHG 4L420XP
	249730	PHG 3L360XP		114-0454	PHG 4L1480XP		1409	PHG 5L520XP
	250105	PHG 4L400XP		114-4420	PHG 5L2020XP		1526	PHG 4L220XP
	250106	PHG 3L460XP		114-5858	PHG 5L1960XP		2227	PHG 4L420XP
	251028	PHG 3L340XP		114-5859	PHG 5L2190XP		2435	PHG 4L350XP
	258340	PHG 3L330XP		115-2649	PHG 4L1490XP		3660	PHG 4L250XP
	262770	PHG 4L500XP		115-4971	PHG 5L1800XP			

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
Western	4320 4638	PHG 4L340XP PHG 4L300XP	Western	754173	PHG 5L370XP	Western	7540239	PHG 4L290XP
	6163 6184 9304 9305 10755	PHG 3L370XP PHG 3L390XP PHG 4L290XP PHG 4L520XP PHG 4L430XP		754177 754178 754179 754180 754182	PHG 4L320XP PHG 5L820XP PHG 5L500XP PHG 5L540XP PHG 5L810XP		7540242 7540244 7540245 7540248	PHG 4L320XP PHG 4L400XP PHG 4L590XP PHG 4L890XP
	10897 10923 11144 13009 14790	PHG 4L510XP PHG 4L300XP PHG 4L410XP PHG 4L410XP PHG 4L380XP		754183 754184 754185 754188 754189	PHG 5L290XP PHG 4L520XP PHG 4L490XP PHG 5L510XP PHG 4L440XP		7540255 7540936 7540937 60D56 60D57	PHG 4L350XP PHG 4L470XP PHG 5L590XP PHG 4L310XP PHG 4L300XP
	14843 16146 16149 16348 16366	PHG 4L290XP PHG 4L390XP PHG 4L390XP PHG 4L380XP PHG 4L350XP		754191 754195 754196 754198 754200	PHG 4L650XP PHG 4L540XP PHG 4L300XP PHG 4L620XP PHG 4L480XP	Yamaha	754-0101 P54239 P54242	PHG 3L350XP PHG 4L290XP PHG 4L320XP
	16386 17569 18055 18263 20715	PHG 4L400XP PHG 4L430XP PHG 4L300XP PHG 4L400XP PHG 4L310XP		754219 754239 754242 754244 754245	PHG 4L260XP PHG 4L290XP PHG 4L320XP PHG 4L400XP PHG 4L590XP		5511 7855521 7Y64624200 7Y64624210 LA85	PHG 5L740XP PHG 5L640XP PHG 5L320XP PHG 5L330XP PHG 4L850XP
	20716 20717 23645 26345 27093	PHG 4L350XP PHG 4L560XP PHG 4L300XP PHG 4L300XP PHG 4L470XP		754935 754936 754937 7540103 7540104	PHG 4L310XP PHG 4L470XP PHG 5L590XP PHG 4L210XP PHG 4L320XP	Yardman	LB103 LB64 LB66 LB67	PHG 5L1030XP PHG 5L650XP PHG 5L660XP PHG 5L680XP
	33622 35545 37169 37230 55019	PHG 3L260XP PHG 4L400XP PHG 4L360XP PHG 4L380XP PHG 4L330XP		7540105 7540107 7540108 7540109 7540111	PHG 4L300XP PHG 4L300XP PHG 4L460XP PHG 4L430XP PHG 4L450XP		2006 40041 40207 165120 165143	PHG 4L280XP PHG 4L400XP PHG 4L450XP PHG A16 PHG 4L560XP
	57051 200555 200982 200983 208526	PHG 4L540XP PHG 3L460XP PHG 4L780XP PHG 4L780XP PHG 3L380XP		7540112 7540113 7540114 7540115 7540116	PHG 5L800XP PHG 5L480XP PHG 4L240XP PHG 5L610XP PHG 4L420XP		165159 165160 165161 165165 165166	PHG 4L580XP PHG 4L400XP PHG 5L610XP PHG 4L670XP PHG 4L640XP
	209581 211650 211664 216594 233163	PHG 4L860XP PHG 3L330XP PHG 4L360XP PHG 4L1020XP PHG 4L430XP		7540118 7540121 7540124 7540127 7540134	PHG 5L630XP PHG 4L310XP PHG 4L570XP PHG 5L660XP PHG 3L330XP		165168 165176 165179 165181 165183	PHG 4L350XP PHG 4L500XP PHG 5L780XP PHG 4L390XP PHG 4L570XP
	754101 754103 754104 754105 754107	PHG 4L350XP PHG 4L250XP PHG 4L320XP PHG 4L300XP PHG 4L300XP		7540118 7540121 7540124 7540127 7540134	PHG 5L630XP PHG 4L310XP PHG 4L570XP PHG 5L660XP PHG 3L330XP		540142 740255 754109 754136 754143	PHG 3L310XP PHG 4L350XP PHG 4L430XP PHG 4L510XP PHG 3L280XP
	754108 754109 754111 754112 754113	PHG 4L460XP PHG 4L430XP PHG 4L450XP PHG 5L800XP PHG 5L480XP		7540136 7540138 7540139 754109 754111	PHG 5L310XP PHG 5L500XP PHG 3L380XP PHG 4L430XP PHG 4L450XP		754144 754146 754154 754165 754169	PHG 5L550XP PHG 4L330XP PHG 4L350XP PHG 4L340XP PHG 3L360XP
	754114 754115 754116 754118 754121	PHG 4L460XP PHG 4L430XP PHG 4L450XP PHG 5L800XP PHG 5L480XP		7540143 7540144 7540145 7540146 7540147	PHG 3L280XP PHG 5L550XP PHG 5L690XP PHG 4L330XP PHG 5L520XP		754181 754189 754190 754195 754197	PHG 4L1000XP PHG 4L440XP PHG 4L390XP PHG 4L540XP PHG 4L1170XP
	754124 754127 754134 754136 754138	PHG 4L240XP PHG 5L610XP PHG 4L420XP PHG 5L630XP PHG 4L310XP		7540154 7540157 7540163 7540164 7540165	PHG 4L350XP PHG 5L280XP PHG 4L280XP PHG 4L630XP PHG 4L340XP		754201 754204 754207 754208 754214	PHG 4L410XP PHG 4L670XP PHG 4L420XP PHG 4L550XP PHG 4L500XP
	754139 754143 754144 754145 754146	PHG 4L570XP PHG 5L660XP PHG 3L330XP PHG 5L310XP PHG 5L500XP		7540166 7540169 7540173 7540177 7540178	PHG 5L620XP PHG 3L360XP PHG 5L370XP PHG 4L320XP PHG 5L820XP		754220 754221 754222 754230 754231	PHG 5L270XP PHG 5L520XP PHG 4L440XP PHG 4L560XP PHG 4L280XP
	754147 754151 754154 754157 754163	PHG 3L380XP PHG 3L280XP PHG 5L550XP PHG 5L690XP PHG 4L330XP		7540179 7540180 7540182 7540183 7540184	PHG 5L500XP PHG 5L540XP PHG 5L810XP PHG 5L290XP PHG 4L520XP		754246 754250 754251 754254 754255	PHG 4L590XP PHG 4L530XP PHG 4L510XP PHG 4L190XP PHG 4L350XP
	754164 754165 754166 754169	PHG 5L520XP PHG 5L670XP PHG 4L350XP PHG 5L280XP PHG 4L280XP		7540185 7540188 7540189 7540191 7540195	PHG 4L490XP PHG 5L510XP PHG 4L440XP PHG 4L650XP PHG 4L540XP		754256 754260 754267 754268 754275	PHG 3L290XP PHG 4L510XP PHG 4L590XP PHG 5L510XP PHG 4L380XP
		PHG 4L630XP PHG 4L340XP PHG 5L620XP PHG 3L360XP		7540196 7540198 7540200 7540219 7540229	PHG 4L300XP PHG 4L620XP PHG 4L480XP PHG 4L260XP PHG 4L520XP		1650120 1651066 7540104	PHG A16 PHG 4L640XP PHG 4L320XP

OEM cross ref

Manufacturer	OEM Ref	SKF Designation	Manufacturer	OEM Ref	SKF Designation
-	-	-	-	-	-
<b>Yardman</b>	7540108	PHG 4L460XP	<b>Yardman</b>	7540338	PHG 4L770XP
	7540109	PHG 4L430XP			
	7540114	PHG 4L240XP		7540347	PHG 4L630XP
	7540125	PHG 4L1050XP		7540365	PHG 4L830XP
	7540136	PHG 5L310XP		7540372	PHG 4L810XP
	7540142	PHG 3L310XP		7540441	PHG 4L760XP
	7540143	PHG 3L280XP		7544154	PHG 4L350XP
	7540144	PHG 5L550XP		7651066	PHG 4L640XP
	7540145	PHG 5L690XP		16510666	PHG 4L640XP
	7540146	PHG 4L330XP		754-0101	PHG 3L350XP
	7540154	PHG 4L350XP		754-0101A	PHG 3L350XP
	7540165	PHG 4L340XP		7540373A	PHG 5L730XP
	7540167	PHG 5L640XP		754C142	PHG 3L310XP
	7540169	PHG 3L360XP		954-04259A	PHG 4L340XP
	7540177	PHG 4L320XP			
	7540178	PHG 5L820XP			
	7540185	PHG 4L490XP			
	7540187	PHG B22			
	7540188	PHG 5L510XP			
	7540189	PHG 4L400XP			
	7540195	PHG 4L540XP			
	7540196	PHG 4L300XP			
	7540198	PHG 4L620XP			
	7540200	PHG 4L480XP			
	7540201	PHG 4L410XP			
	7540204	PHG 4L670XP			
	7540205	PHG 3L320XP			
	7540206	PHG 4L500XP			
	7540207	PHG 4L420XP			
	7540208	PHG 4L550XP			
	7540211	PHG 5L460XP			
	7540212	PHG 5L450XP			
	7540214	PHG 4L500XP			
	7540216	PHG 3L290XP			
	7540218	PHG 5L590XP			
	7540219	PHG 4L260XP			
	7540220	PHG 5L270XP			
	7540221	PHG 5L520XP			
	7540222	PHG 4L440XP			
	7540223	PHG 3L360XP			
	7540224	PHG 5L250XP			
	7540225	PHG 4L820XP			
	7540227	PHG 5L630XP			
	7540229	PHG 4L520XP			
	7540231	PHG 4L280XP			
	7540234	PHG 4L410XP			
	7540235	PHG 4L350XP			
	7540236	PHG 4L850XP			
	7540244	PHG 4L400XP			
	7540245	PHG 4L590XP			
	7540246	PHG 4L590XP			
	7540247	PHG 4L550XP			
	7540248	PHG 4L890XP			
	7540249	PHG 5L300XP			
	7540250	PHG 4L530XP			
	7540251	PHG 4L510XP			
	7540252	PHG 4L330XP			
	7540253	PHG 4L430XP			
	7540254	PHG A17			
	7540255	PHG 4L350XP			
	7540256	PHG 3L290XP			
	7540257	PHG 3L380XP			
	7540260	PHG 5L510XP			
	7540261	PHG 4L560XP			
	7540267	PHG 4L590XP			
	7540268	PHG 5L510XP			
	7540271	PHG 3L390XP			
	7540274	PHG 4L440XP			
	7540275	PHG 4L380XP			
	7540278	PHG 4L300XP			
	7540285	PHG 4L340XP			
	7540290	PHG 4L470XP			
	7540291	PHG 4L880XP			
	7540292	PHG 4L260XP			
	7540326	PHG 4L620XP			
	7540327	PHG 5L280XP			

# Product fulfillment

By developing its own range of solutions for power transmission, SKF is able to offer well-matched products thus giving engineers a wide choice for better performance at an optimal cost.



## Belts

- Oil and heat resistance/anti-static properties (except SKF Cogged Raw Edge Belts).
- Globally sourced rubber along with stringently controlled tension members provide the superior performance expected from SKF.
- State-of-the-art electronic rubber blending/mixing processes maintain superior quality.
- Tight tolerance stability during the manufacturing process along with superior raw material eliminates the requirement to match individual belts to a single drive.



## Pulleys

- Pulleys are all statically balanced to provide true running tolerances at higher speeds.
- Dynamic balancing is also available on request.
- Pulleys, with an outside diameter equal to or less than 300 mm are boxed. Pulleys with an outside diameter greater than 300 mm or over 30 kg are placed on a wooden pallet.



<b>Dacrotized</b>	Suitable for corrosive conditions.
<b>Nickel-plated</b>	Improved wear resistance. Recommended for outdoor conditions, such as exposure to rain.
<b>Zinc-plated</b>	A cost-effective way to increase corrosion resistance.
<b>Stainless steel</b>	Used in food processing applications, high/low temperature conditions (-20 to 400 °C/ -4 to 752 °F) and in corrosive environments.



### Chains

- From the raw material to the finished product, our chains are superior by design: 100 % pre-stressing, 100 % pre-loading and running prior to packaging.
- SKF uses a heavy pre-lubrication process to enable optimum storage life; all SKF Chains are fully wrapped in plastic prior to being boxed.

- A very large range of plating material is available: Dacromet, nickel, zinc and stainless steel.
- SKF also supplies a full range of conveyor chains for every application.

### Sprockets

- All sprockets are oiled, bagged, sealed and then boxed. This allows the product to reach the customer in perfect condition every time.
- Sprockets are also available with hardened teeth, bored and keyed to size.
- Sprockets with an outside diameter equal to or less than 300 mm are boxed. Sprockets with an outside diameter greater than 300 mm or over 30 kg are placed on a wooden pallet.



### Couplings

- SKF Flex, Jaw, Chain, Gear, Grid FRC, Rigid Couplings, and Universal Joints: no matter which coupling your application requires, SKF offers options for bushings, bored to size or simply piloted.
- All couplings are boxed or bagged for protection; larger units are on a wooden pallet for easy handling and safety.



### Bushings

- Bushings are available in many variants: Taper bushings, QD bushings, FX Keyless bushings, weld-on hubs and bolt-on hubs. They are made from high quality steel and most types are phosphate coated or blackened for improved corrosion resistance.
- All bushings are designed for quick and easy installation and removal with basic tools, resulting in minimum downtime each time they are fitted.











