

LUBRICATION OIL LIST FOR SIMPLEX STERN TUBE BUSHES, INTERMEDIATE SHAFT BEARINGS AND SEALS

The SIMPLEX seal is fitted with sealing rings of NBR or FKM depending on the operating conditions.

The following list is a recommendation list regarding SIMPLEX stern tube bushes, intermediate shaft bearings and seals. It is inapplicable to the behaviour with regards to gears, clutches, roller bearings or other components of the propulsion system.

The technical data has been provided by the oil companies. The suitable sealing ring material is given for every oil listed. If FKM Pod and/or FKM Bio are mentioned below these materials have to be used exclusively, otherwise if FKM is stated all FKM materials from SKF Marine are suitable.

The oils listed here are approved in their pure, exclusively type only. Mixtures with other listed or not listed oils are not approved.

Please keep in mind that the approvals does apply to the formulation provided by the oil manufacturer for specific testing only. These should in general correspond with products available on the marine market. The oil manufactures are responsible to inform SKF Marine of changes in formulation.

For SIMPLEX sterntube bushes, intermediate shaft- and thrust bearings, please use only the viscosity specified by SKF Marine for your application (+/-5% of the stated viscosity grade). For technical advice regarding the viscosity to be used for SIMPLEX sterntube bushes, intermediate shaft- and thrust bearings, please contact SKF Marine.

Oils marked with " * " have to be used in consultation with SKF Marine GmbH only due to restriction in application.

We ask to inform us if oils / lubricants which are not listed are to be used. We shall test these lubricants accordingly.

Brand	Product Name	Sealing Ring Material	Viscosity cSt. 40°C	Classification	Type
Aegeon Marine Petroleum	Alfagear 150	NBR, FKM	150	Mineral	Gear Oil
Aegeon Marine Petroleum	Alfamar 430	NBR, FKM	143	Mineral	Engine Oil
Aegeon Marine Petroleum	Alfasys 305	NBR, FKM	92	Mineral	Engine Oil
Agip / Eni	Acer 100	NBR, FKM	100	Mineral	Hydraulic Oil
Agip / Eni	Blasia 100	NBR, FKM	100	Mineral	Gear Oil
Agip / Eni	Cladium 120 SAE30	NBR, FKM	108	Mineral	Engine Oil
Agip / Eni	Cladium 400 SAE30	FKM	108	Mineral	Engine Oil
Agip / Eni	Cladium 400 SAE40	FKM	160	Mineral	Engine Oil
Agip / Eni	Cladium 50 SAE30	FKM	115	Mineral	Engine Oil
Agip / Eni	Ote 68	FKM	64	Mineral	Hydraulic Oil
Agip / Eni	Ote 80	FKM	75	Mineral	Hydraulic Oil

Caltex	Delo 1000 Marine Oil 30	NBR, FKM	96	Mineral	Engine Oil
Caltex	Meropa 100	NBR, FKM	100	Mineral	Gear Oil
Caltex	Meropa Lubricant 150	NBR, FKM	150	Mineral	Gear Oil
Caltex	Regal Oil R&O 100	NBR, FKM	100	Mineral	Other
Caltex	Regal Oil R&O 68	NBR, FKM	68	Mineral	Other
Castrol	Alpha SP 100	NBR, FKM	100	Mineral	Gear Oil
Castrol	Alpha SP 150	NBR, FKM	150	Mineral	Gear Oil
Castrol	Alpha SP 220	NBR, FKM	220	Mineral	Gear Oil
Castrol	Alpha SP 320	NBR, FKM	320	Mineral	Gear Oil
Castrol	Alpha SP 68	NBR, FKM	68	Mineral	Gear Oil
Castrol	Alpha ZN 100	NBR, FKM	100	Mineral	Gear Oil
Castrol	Alpha ZN 150	NBR, FKM	150	Mineral	Gear Oil
Castrol	Alpha ZN 68	NBR, FKM	68	Mineral	Gear Oil
Castrol	Castrol CDX 30	NBR, FKM	105	Mineral	Engine Oil
Castrol	Coral 2 * (Emergency oil)	NBR, FKM	240	Mineral	Sterntube Oil
Castrol	HLX 30	NBR, FKM	100	Mineral	Engine Oil
Castrol	Hyspin AWH - M 68	NBR, FKM	68	Mineral	Hydraulic Oil
Castrol	Hyspin AWH - M100	NBR, FKM	100	Mineral	Hydraulic Oil
Castrol	MHP 153	NBR, FKM	103	Mineral	Engine Oil
Castrol	MHP 154	NBR, FKM	130	Mineral	Engine Oil
Castrol	Nato 0-274	NBR, FKM	101	Mineral	Engine Oil
Castrol	Perfecto T 100	NBR, FKM	100	Mineral	Other
Castrol	Perfecto T 68	NBR, FKM	68	Mineral	Other
Castrol	RX Super 30	NBR, FKM	108	Mineral	Engine Oil
Castrol	TLX Plus 203	NBR, FKM	101	Mineral	Engine Oil
Castrol	TLX Plus 204	NBR, FKM	138	Mineral	Engine Oil
Castrol	TLX Plus 303	NBR, FKM	103	Mineral	Engine Oil
Castrol	TLX Plus 304	NBR, FKM	135	Mineral	Engine Oil
Castrol	TLX Plus 403	NBR, FKM	94	Mineral	Engine Oil
Castrol	TLX Plus 404	NBR, FKM	134	Mineral	Engine Oil
Castrol	TLX Plus 504	NBR, FKM	135	Mineral	Engine Oil
Castrol	TLX Plus 554	NBR, FKM	130	Mineral	Engine Oil

Castrol	TLX Xtra 203	NBR, FKM	98	Mineral	Engine Oil
Castrol	TLX Xtra 204	NBR, FKM	137	Mineral	Engine Oil
Castrol	TLX Xtra 304	NBR, FKM	125	Mineral	Engine Oil
Castrol	TLX Xtra 404	NBR, FKM	130	Mineral	Engine Oil
Castrol	TLX Xtra 504	NBR, FKM	127	Mineral	Engine Oil
Chevron	Clarity Hydraulic Oil AW 100	NBR, FKM Pod	95	Mineral	Hydraulic Oil
Chevron	Delo 1000 Marine 30	NBR, FKM	103	Mineral	Engine Oil
Chevron	Delo 1000 Marine 40	NBR, FKM	135	Mineral	Engine Oil
Chevron	Pinnacle Marine Gear 220	FKM	220	Synthetic	Gear Oil
Chevron	Rando HDZ 68	NBR, FKM Pod, FKM Bio	68	Mineral	Hydraulic Oil
Chevron	Taro 20 DP 30X	NBR, FKM		Mineral	Engine Oil
Chevron	Taro 20 DP 40X	NBR, FKM	139	Mineral	Engine Oil
Chevron	Taro 30 DP 30X	NBR, FKM	97	Mineral	Engine Oil
Chevron	Taro 30 DP 40X	NBR, FKM	139	Mineral	Engine Oil
Chevron	Taro 40 XL 40X	NBR, FKM	139	Mineral	Engine Oil
Chevron	Taro 50 XL 40X	NBR, FKM	135	Mineral	Engine Oil
Chevron	Turbine Oil GST 100	NBR, FKM	100	Mineral	Other
Chevron	Turbine Oil GST 68	NBR, FKM	68	Mineral	Other
Chevron	Veritas 800 Marine 30	NBR, FKM	111	Mineral	Engine Oil
CPC	CPC Marilube Oil AC-30 SP	FKM	104	Mineral	Engine Oil
ExxonMobil	Mobil Delvac 1330	NBR, FKM	106	Mineral	Engine Oil
ExxonMobil	Mobil Delvac 1340	NBR, FKM	136	Mineral	Engine Oil
ExxonMobil	Mobil Delvac 1630	NBR, FKM	90	Mineral	Engine Oil
ExxonMobil	Mobil Delvac 1640	NBR, FKM	132	Mineral	Engine Oil
ExxonMobil	Mobil Delvac MX15W-40	NBR, FKM	106	Mineral	Engine Oil
ExxonMobil	Mobil DTE 10 Excel 46	NBR, FKM	46	Mineral	Hydraulic Oil
ExxonMobil	Mobil DTE 10	NBR, FKM	68	Mineral	Hydraulic Oil

	Excel 68				
ExxonMobil	Mobil DTE Oil BB	NBR, FKM	218	Mineral	Other
ExxonMobil	Mobil DTE Oil Extra Heavy	NBR, FKM	146	Mineral	Other
ExxonMobil	Mobil DTE Oil Heavy	NBR, FKM	95	Mineral	Other
ExxonMobil	Mobil DTE Oil Heavy Medium	NBR, FKM	65	Mineral	Other
ExxonMobil	Mobil Sterntube Lubricant * (Emergency oil)	FKM	385	Mineral	Sterntube Oil
ExxonMobil	Mobil Vacuoline 528	NBR, FKM	146	Mineral	Other
ExxonMobil	Mobilgard 300 C	NBR, FKM	109	Mineral	Engine Oil
ExxonMobil	Mobilgard 312	NBR, FKM	108	Mineral	Engine Oil
ExxonMobil	Mobilgard 340	NBR, FKM	106	Mineral	Engine Oil
ExxonMobil	Mobilgard 412	NBR, FKM	142	Mineral	Engine Oil
ExxonMobil	Mobilgard 570	NBR, FKM	222	Mineral	Other
ExxonMobil	Mobilgard ADL 40	NBR, FKM	132	Mineral	Engine Oil
ExxonMobil	Mobilgard M 330	NBR, FKM	98	Mineral	Engine Oil
ExxonMobil	Mobilgard M 440	NBR, FKM	126	Mineral	Engine Oil
ExxonMobil	Mobilgard M430	NBR, FKM	126	Mineral	Engine Oil
ExxonMobil	Mobilgard M50	NBR, FKM	120	Mineral	Engine Oil
ExxonMobil	Mobilgear 600 XP 100	NBR, FKM	100	Mineral	Gear Oil
ExxonMobil	Mobilgear 600 XP 150	NBR, FKM	150	Mineral	Gear Oil
ExxonMobil	Mobilgear 600 XP 220	NBR, FKM	220	Mineral	Gear Oil
ExxonMobil	Mobilgear 600 XP 320	NBR, FKM, HNBR	320	Mineral	Gear Oil
ExxonMobil	Mobilgear 600 XP 68	NBR, FKM	68	Mineral	Gear Oil
ExxonMobil	Mobilgear 626	NBR, FKM	68	Mineral	Gear Oil
ExxonMobil	Mobilgear 627	NBR, FKM	100	Mineral	Gear Oil
ExxonMobil	Mobilgear 629	NBR, FKM	150	Mineral	Gear Oil
ExxonMobil	Mobilgear 630	NBR, FKM	220	Mineral	Gear Oil
ExxonMobil	Mobilgear SHC XMP220 *	FKM	220	Synthetic	Gear Oil
ExxonMobil	Mobilgear SHC XMP320 *	FKM	335	Synthetic	Gear Oil

ExxonMobil	Nuto H 68	NBR, FKM	68	Mineral	Hydraulic Oil
ExxonMobil	Teresstic 32	NBR, FKM	32	Mineral	Hydraulic Oil
ExxonMobil	Teresstic 68	NBR, FKM	68	Mineral	Hydraulic Oil
ExxonMobil	UNIVIS N 100	NBR, FKM	98	Mineral	Hydraulic Oil
Fuchs Europe Schmierstoffe	Renolin CLP 100	NBR, FKM Pod	100	Mineral	Gear Oil
Fuchs Europe Schmierstoffe	Renolin CLP 150	NBR, FKM Pod	150	Mineral	Gear Oil
Fuchs Europe Schmierstoffe	Renolin CLP 220	NBR, FKM Pod	220	Mineral	Gear Oil
Fuchs Europe Schmierstoffe	Renolin CLP 320	NBR, FKM Pod	320	Mineral	Gear Oil
Fuchs Europe Schmierstoffe	Renolin CLP 68	NBR, FKM Pod	68	Mineral	Gear Oil
Fuchs Europe Schmierstoffe	Renolin Unisyn CLP 150	NBR, FKM	150	Synthetic	Gear Oil
Fuchs Europe Schmierstoffe	Renolin Unisyn CLP 220	NBR, FKM	220	Synthetic	Gear Oil
Fuchs Europe Schmierstoffe	Renolin Unisyn CLP 320	NBR, FKM	320	Synthetic	Gear Oil
Gulf Oil Marine Ltd.	GulfSea Gear Oil 100	FKM Pod, FKM Bio	100	Mineral	Gear Oil
Gulf Oil Marine Ltd.	GulfSea Gear Oil 68	FKM Pod	68	Mineral	Gear Oil
Gulf Oil Marine Ltd.	GulfSea Power MDO 4015	NBR, FKM		Mineral	Engine Oil
Gulf Oil Marine Ltd.	GulfSea SuperBear 3006	NBR, FKM	99.4	Mineral	Engine Oil
Gulf Oil Marine Ltd.	GulfSea SuperBear 3008	NBR, FKM	99.3	Mineral	Engine Oil
Idemitsu	Daphne Super Gear Oil	NBR, FKM	150	Mineral	Gear Oil
Ina Maziva Rijeka Croatia	Gorgonela S 30	NBR, FKM	106	Mineral	Multipurpose Oil
Ina Maziva Rijeka Croatia	Gorgonela S 40	NBR, FKM	147	Mineral	Multipurpose Oil
Ina Maziva Rijeka Croatia	Rubella 30	NBR, FKM	107	Mineral	Multipurpose Oil
Ina Maziva Rijeka Croatia	Rubella 40	NBR, FKM	148	Mineral	Multipurpose Oil
Ina Maziva Rijeka Croatia	Sagartia 30	NBR, FKM	106	Mineral	Engine Oil
Ina Maziva Rijeka Croatia	Sagartia 40	NBR, FKM	147	Mineral	Engine Oil

Ina Maziva Rijeka Croatia	Turbo 32	NBR, FKM	32	Mineral	Other
Ina Maziva Rijeka Croatia	Turbo 46	NBR, FKM	46	Mineral	Other
Irving Oil	Marine LSX 530	NBR, FKM	108	Mineral	Engine Oil
Irving Oil	Marine MTX 1230	NBR, FKM	107	Mineral	Engine Oil
Irving Oil	Marine MTX 1240	FKM	139	Mineral	Engine Oil
Irving Oil	Marine MTX 2030	NBR, FKM	104	Mineral	Engine Oil
Irving Oil	Marine MTX 2040	NBR, FKM	142	Mineral	Engine Oil
Irving Oil	Marine MTX 3030	NBR, FKM	102	Mineral	Engine Oil
Irving Oil	Marine MTX 3040	NBR, FKM	142	Mineral	Engine Oil
Irving Oil	Marine MTX 4030	NBR, FKM	103	Mineral	Engine Oil
Irving Oil	Marine MTX 4040	NBR, FKM	139	Mineral	Engine Oil
Irving Oil	Marine MTX 5040	NBR, FKM	139	Mineral	Engine Oil
Klüber	Klüberoil GEM 1-100 N	NBR, FKM	100	Mineral	Gear Oil
Klüber	Klüberoil GEM 1-150 N	NBR, FKM	150	Mineral	Gear Oil
Klüber	Klüberoil GEM 1-68 N	NBR, FKM	68	Mineral	Gear Oil
Klüber	Klübersynth GEM 4-150 N	FKM Pod	150	Synthetic	Gear Oil
Klüber	Klübersynth GEM 4-150 N LWC	FKM Pod	150	Synthetic	Gear Oil
Klüber	Klübersynth GEM 4-320 N	FKM Pod	320	Synthetic	Gear Oil
Klüber	Klübersynth GEM 4-320 N LWC	FKM Pod	320	Synthetic	Gear Oil
Lenol	Lenol 10 TPX 30	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 10 TPX 40	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 15 TP 30	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 15 TP 40	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 30 TP 30	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 30 TP 40	NBR, FKM		Mineral	Engine Oil

Lenol	Lenol 40 TP 40	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 50 TP 40	NBR, FKM		Mineral	Engine Oil
Lenol	Lenol 6 S 30	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo 6 CO	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 15/30	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 15/40	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 30/30	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 30/40	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 40/40	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO 50/40	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO Ultra 30	NBR, FKM		Mineral	Engine Oil
Lukoil	Navigo TPEO Ultra 40	NBR, FKM		Mineral	Engine Oil
Neste	Vaihteisto 220 EP	NBR, FKM	220	Mineral	Gear Oil
Neste	Vaihteisto 320 EP	NBR, FKM	320	Mineral	Gear Oil
Nippon Oil Co.	Diamond Marine T 104	FKM	96	Mineral	Engine Oil
Nippon Oil Co.	Diamond Marine T 203 A	FKM	145	Mineral	Engine Oil
Nippon Oil Co.	Diamond Marine T 303 A	NBR, FKM	95.5	Mineral	Engine Oil
Nippon Oil Co.	Diamond Marine T 304 A	FKM	141	Mineral	Engine Oil
Nippon Oil Co.	MDL HDS 30 (ren. Super MDL HDS 30)	NBR, FKM	109	Mineral	Engine Oil
Nippon Oil Co.	MDL PS 30 (ren. Super MDL PS 30)	NBR, FKM	106	Mineral	Engine Oil
Petro-Canada Lubricants	Duron 30	NBR, FKM	92	Mineral	Engine Oil
Petro-Canada Lubricants	Enduratex EP 100	NBR, FKM	101	Mineral	Gear Oil
PetroChina	KunLun DCC 3008	FKM Pod, FKM Bio		Mineral	Engine Oil
Q8 Oils	Verdi 100	NBR, FKM	100	Mineral	Engine Oil

Reginol	Gear GI 1	NBR, FKM	142	Mineral	Gear Oil
Reginol	Hykraft 150	NBR, FKM	137	Mineral	Hydraulic Oil
Reginol	Hykraft 68	FKM	68	Mineral	Hydraulic Oil
Reginol	Industrygear EP 100	FKM	99	Mineral	Gear Oil
Shell	Argina S 30	FKM	110	Mineral	Engine Oil
Shell	Argina S2 40	NBR, FKM	131	Mineral	Engine Oil
Shell	Argina S3 30	NBR, FKM	105	Mineral	Engine Oil
Shell	Argina S3 40	NBR, FKM	130	Mineral	Engine Oil
Shell	Argina S4 40	NBR, FKM	127	Mineral	Engine Oil
Shell	Argina S5 40	NBR, FKM	123	Mineral	Engine Oil
Shell	Gadina AL 30	NBR, FKM	95	Mineral	Engine Oil
Shell	Gadina AL 40	NBR, FKM	140	Mineral	Engine Oil
Shell	Gadina S3 30	NBR, FKM	104	Mineral	Engine Oil
Shell	Gadina S3 40	NBR, FKM	128	Mineral	Engine Oil
Shell	Gadina S4 40	NBR, FKM	129	Mineral	Engine Oil
Shell	Melina S 30	NBR, FKM	104	Mineral	Engine Oil
Shell	Morlina S2 B 100	FKM	100	Mineral	Other
Shell	Morlina S2 B 46	FKM	46	Mineral	Other
Shell	Omala S2 GX 100 (ren. Omala S2 G 100)	NBR, FKM	100	Mineral	Gear Oil
Shell	Omala S2 GX 150 (ren. Omala S2 G 150)	NBR, FKM	150	Mineral	Gear Oil
Shell	Omala S2 GX 220 (ren. Omala S2 G 220)	NBR, FKM	220	Mineral	Gear Oil
Shell	Omala S2 GX 320 (ren. Omala S2 G 320)	NBR, FKM	320	Mineral	Gear Oil
Shell	Omala S2 GX 68 (ren. Omala S2 G 68)	NBR, FKM	68	Mineral	Gear Oil
Shell	Omala S4 GX 68	NBR, FKM Pod	69	Synthetic	Gear Oil
Shell	Rimula R3+ SAE 30	NBR, FKM	93	Mineral	Engine Oil
Shell	Sirius X 30	NBR, FKM	101	Mineral	Engine Oil
Shell	Sirius X 40	NBR, FKM	139	Mineral	Engine Oil
Shell	Tellus S2 M 100	NBR, FKM	100	Mineral	Hydraulic Oil
Shell	Tellus S2 V 100	NBR, FKM	100	Mineral	Hydraulic Oil

Shell	Tellus S2 V 68	NBR, FKM	68	Mineral	Hydraulic Oil
Shell	Turbo T 46	NBR, FKM	46	Mineral	Other
Shell	Turbo T 68	NBR, FKM	68	Mineral	Other
SINOPEC LUBRICANT	SINOPEC Marine System Oil 3005	NBR, FKM		Mineral	Engine Oil
SINOPEC LUBRICANT	SINOPEC Marine System Oil 3005A	NBR, FKM		Mineral	Engine Oil
SK	Supermar AS	NBR, FKM		Mineral	Engine Oil
Statoil	Statoil HydraWay HMA 100	NBR, FKM	100	Mineral	Hydraulic Oil
Statoil	Statoil HydraWay HMA 68	NBR, FKM	68	Mineral	Hydraulic Oil
Statoil	Statoil Loadway EP 100	NBR, FKM	100	Mineral	Gear Oil
Statoil	Statoil Loadway EP 150	NBR, FKM	150	Mineral	Gear Oil
Statoil	Statoil Loadway Marine 100	NBR, FKM	100	Mineral	Gear Oil
Statoil	Statoil Loadway Marine 150	NBR, FKM	150	Mineral	Gear Oil
Statoil	Statoil Loadway Marine 68	NBR, FKM	68	Mineral	Gear Oil
Statoil	Statoil MarWay 1030	NBR, FKM	106	Mineral	Engine Oil
Statoil	Statoil MarWay 1040	NBR, FKM	137	Mineral	Engine Oil
Statoil	Statoil Sternway 220	FKM	220	Mineral	Sterntube Oil
Statoil	Statoil Sternway Bio 100	FKM Pod, FKM Bio	107	Biodegradable	Sterntube Oil
Teboil	Teboil Ward L10T SAE 30	NBR, FKM	106	Mineral	Engine Oil
Texaco	Meropa 100	NBR, FKM	100	Mineral	Gear Oil
Texaco	Meropa 150	FKM	150	Mineral	Gear Oil
Texaco	Meropa 220	NBR, FKM	220	Mineral	Gear Oil
Texaco	Meropa 320	NBR, FKM	320	Mineral	Gear Oil
Texaco	Meropa 460	FKM	460	Mineral	Gear Oil
Texaco	Rando HD 68	NBR, FKM	68	Mineral	Hydraulic Oil
Texaco	Rando HDZ 68	NBR, FKM Pod, FKM Bio	68	Mineral	Hydraulic Oil
Texaco	Regal R&O 100	NBR, FKM	92	Mineral	Other

Texaco	Regal R&O 68	NBR, FKM	68	Mineral	Other
Texaco	Taro 16 XD	NBR, FKM	139	Mineral	Engine Oil
Texaco	Taro 30 DP	NBR, FKM	95	Mineral	Engine Oil
Texaco	Taro 40 DP	NBR, FKM	135	Mineral	Engine Oil
Texaco	Taro 40 XL	NBR, FKM	135	Mineral	Engine Oil
Texaco	Ursa Oil ED 40	NBR, FKM	131	Mineral	Engine Oil
Texaco	Ursa Super Plus 30	NBR, FKM	102	Mineral	Engine Oil
Texaco	Ursa Super Plus 40	NBR, FKM	160	Mineral	Engine Oil
Total automotive	Caprano M 30	NBR, FKM	113	Mineral	Engine Oil
Total automotive	Caprano TD 30	NBR, FKM Pod, FKM Bio	103	Mineral	Engine Oil
Total automotive	Rubia S 30	NBR, FKM	103	Mineral	Engine Oil
Total automotive	Rubia S 40	NBR, FKM	124	Mineral	Engine Oil
Total Lubmarine	Atlanta Marine D 3005	NBR, FKM	105	Mineral	Engine Oil
Total Lubmarine	Aurelia TI 3030	NBR, FKM	110	Mineral	Engine Oil
Total Lubmarine	Aurelia TI 3040	NBR, FKM	112	Mineral	Engine Oil
Total Lubmarine	Aurelia TI 4030	NBR, FKM	140	Mineral	Engine Oil
Total Lubmarine	Aurelia TI 4040	NBR, FKM	140	Mineral	Engine Oil
Total Lubmarine	Aurelia TI 4055	NBR, FKM	140	Mineral	Engine Oil
Total Lubmarine	Disola M 3015	NBR, FKM	110	Mineral	Engine Oil
Total Lubmarine	Disola M 4015	NBR, FKM	145	Mineral	Engine Oil
Total Lubmarine	Disola MT 30	NBR, FKM	85	Mineral	Engine Oil
Total Lubmarine	Disola MT 40	NBR, FKM	141	Mineral	Engine Oil
Total Lubmarine	Epona Z 150 (ren. Elf Epona Z 150)	NBR, FKM	153	Mineral	Gear Oil
Total Lubmarine	Preslia 100 (ren. Turbine T 100)	NBR, FKM	100	Mineral	Other
Total Lubmarine	Preslia 68 (ren. Turbine T 68)	NBR, FKM	68	Mineral	Other
Total Lubmarine	Visga 68	NBR, FKM Pod	71	Mineral	Hydraulic Oil
Vickers Oils	Hydrox 21 * (Emergency oil)	FKM	275	Mineral	Sterntube Oil
Vickers Oils	Hydrox 550 *	NBR, FKM	73	Mineral	Sterntube Oil
Vickers Oils	Hydrox 8 EP	NBR, FKM	105	Mineral	Gear Oil
Vickers Oils	Hydrox EP 150	FKM	150	Mineral	Gear Oil

Vickers Oils	Hydrox EP 550*	NBR, FKM Pod, FKM Bio	100	Mineral	Gear Oil
--------------	----------------	--------------------------	-----	---------	----------

This list is not subject to revision service. The current approval list can be viewed and downloaded on the following website https://skf-simplex.com/lubricant_index.php.