

SKF Grease guns

Manual lubrication tools



Manual grease dispensing tools


A basic element of lubrication plans

The main pitfall of manual lubrication is ensuring accuracy and top cleanliness. Lubricant film in the application can be over 40 times thinner than the smallest visible particle. The SKF range of manual lubrication tools is designed to help you with the storage, handling, dosing and supplying of lubricants for your machinery in a clean and easy way.

A comprehensive range to meet your needs

Grease guns

SKF Grease guns are suitable for agricultural, industrial, automotive and construction industries amongst others. All of them are equipped with a grease filling fitting. This fitting enables the use of SKF Grease filler pumps to refill the guns with loose grease, thus keeping contaminants out of the grease.



Easy grease filling

Grease guns TLGH 1 and 1077600

The SKF Grease guns are ideal for agricultural, industrial and construction industries and for private use. The grease guns are delivered with a 175 mm (6.9 in.) long extension pipe with hydraulic gripping nozzle.

- For use with cartridges and loose grease
- Knurled body for firm and safe grip
- High quality steel is dent-resistant for easy cartridge loading
- Special piston design for smooth emptying of cartridges
- Volume/stroke
 - TLGH 1: 0,9 cm³ (0.055 in.³)
 - 1077600: 1,5 cm³ (0.092 in.³)

Selection chart and technical data – SKF Grease Guns				
Designation	TLGH 1	1077600	1077600/SET	LAGH 400
Drive	Manual	Manual	Manual	Manual One hand
Maximum pressure	400 bar (5 800 psi)	400 bar (5 800 psi)	400 bar (5 800 psi)	300 bar (4 350 psi)
Volume per stroke	Approx. 0,9 cm ³ (0.05 in. ³)	Approx. 1,5 cm ³ (0.09 in. ³)	Approx. 1,5 cm ³ (0.09 in. ³)	Approx. 0,46 cm ³ (0.03 in. ³)
Weight	1,5 kg (3.3 lb)	1,5 kg (3.3 lb)	Complete: 2,4 kg (5.3 lb)	1,3 kg (2.9 lb)
Reservoir	Loose grease (ca. 500 cm ³) or grease cartridges.	Loose grease (ca. 500 cm ³) or grease cartridges.	Loose grease (ca. 500 cm ³) or grease cartridges.	Loose grease (ca. 500 cm ³) or grease cartridges.
Discharge pipe length	175 mm (6.9 in.)	175 mm (6.9 in.)	175 mm (6.9 in.)	-
Flexible hose length	-	-	-	300 mm (12 in.)
Accessories	1077601 ¹⁾	1077601 ¹⁾	1077601 ¹⁾ LAGC S	1077601 ¹⁾ LAGC S

¹⁾ Flexible 500 mm (19.7 in.) long pressure hose with hydraulic gripping nozzle



1077600/SET



LAGH 400

1077600 H

The 1077600 is also available with a with 300 mm (12 in.) high pressure hose with a hydraulic gripping nozzle.

1077600/SET

The 1077600 is also available as a complete set. The set includes: Extension pipe, Snap-on high pressure hose, Snap-on extension pipe with cardan nozzle, Snap-on extension pipe for flat-head grease fittings (Ø16 mm), Female and pointed nozzle.

Easy grease filling with one hand

Grease gun LAGH 400

Suitable for grease filling by grease filler pumps and also suitable for grease cartridges. Ergonomic design, flexible hose and possibility to mount the hose in both vertical and horizontal position make it easy to use.

- Easy-to-use: only one hand is needed to operate the gun
- Refillable: grease filling nipple and de-airing valve allow filling up by filler or grease pump
- Heavy duty: operating pressure up to 300 bar (4 350 psi)
- Flexible hydraulic type hose: can be bent, can be mounted both horizontally and vertically on the gun



LAGC S



LAGM 1000E



LAGF 50

LAGF 18
and LAGH 400

For a seamless and efficient greasing experience

Grease coupler LAGC S

The grease coupler improves safety and simplifies the manual lubrication process. Featuring one-handed operation, the coupler remains attached to the fitting during lubrication. Its reverse-jaw design holds the coupler securely to the seat and eliminates grease spillage.

- Effortless coupling and uncoupling, even under pressure.
- Locking and quick-release mechanism that creates a leak-proof seal
- Compatible with standard grease guns, transfer pumps, and typical industrial grease fittings
- Maximum working pressure 550 bar (8 000 psi)

Accurate grease quantity measurement

Grease meter LAGM 1000E

The SKF Grease Meter LAGM 1000E accurately measures grease discharge in volume or weight in metric (cm^3 or g) or US units (US fl. oz or oz), making conversion calculations unnecessary.

- A rubber sleeve protects the electronics in case of impact and is also oil and grease resistant
- The backlit LCD displays large and clear-to-read digits
- Compact and lightweight design
- Corrosion-resistant aluminium housing
- Fits with all SKF manual grease guns
- Fixed installation in conjunction with a lubrication system possible

Optimum cleanliness when filling your grease guns

Grease filler pumps LAGF series

Best lubrication practices say that each type of grease requires an individual grease gun and the refilling has to be a clean process. SKF Grease Filler Pumps are designed to help achieve this goal.

- Quick filling: low pressure high stroke volume
- Easy installation: all necessary items are included
- Reliable: tested and approved for all SKF greases
- Appropriate as a complement for Bearing packer VKN 550

skf.com | skf.com/lubrication | skf.com/mapro

® SKF is a registered trademark of AB SKF (publ).

© SKF Group 2025 . All rights reserved. Please note that this publication may not be copied or distributed, in whole or in part, unless prior written permission is granted.

Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 13717/3 EN · January 2025