

SKF Bearing Grease

General purpose industrial and automotive bearing grease

LGMT 3

SKF LGMT 3 is mineral oil based, lithium soap thickened grease. This premium quality, general purpose grease is suitable for a wide range of industrial and automotive applications requiring stiff grease.

- Excellent rust inhibiting properties
- High oxidation stability within its recommended temperature range

Typical applications

- Bearings >100 mm (3.9 in.) shaft size
- Outer bearing ring rotation
- Vertical shaft applications
- Continuous high ambient temperatures >35 °C (95 °F)
- Propeller shafts
- Agricultural equipment
- Car, truck and trailer wheel bearings
- Large electric motors



Available pack sizes


Packsize	Designation
420 ml cartridge	LGMT 3.0,4
0,5 kg can	LGMT 3/0.5
1 kg can	LGMT 3/1
5 kg can	LGMT 3/5
18 kg pail	LGMT 3/18
50 kg drum	LGMT 3/50
180 kg drum	LGMT 3/180
Electro-mechanical lubricant dispensers	
TLMR 101 series 380 ml refill (incl. battery)	LGMT 3/MR380B
TLMR 201 series 380 ml refill	LGMT 3/MR380



Technical data

Designation	LGMT 3/(pack size)	
DIN 51825 code	K3K-30	Corrosion protection
NLGI consistency class	3	Emcor: – standard ISO 11007 0–0 – water washout test 0–0
Thickener	Lithium	Water resistance
Colour	Amber	DIN 51 807/1, 3 hrs at 90 °C 1 max.
Base oil type	Mineral	Oil separation
Operating temperature range	–30 to +120 °C (–20 to +250 °F)	DIN 51 817, 7 days at 40 °C, static, % 1–3
Dropping point DIN ISO 2176	>180 °C (>355 °F)	Lubrication ability
Base oil viscosity		R2F, running test B at 120 °C Pass
40 °C, mm ² /s	125	Copper corrosion
100 °C, mm ² /s	12	DIN 51 811 2 max. at 130 °C (265 °F)
Penetration DIN ISO 2137		Rolling bearing grease life
60 strokes, 10 ⁻¹ mm	220–250	R0F test 1 000 min. at 130 °C (265 °F)
100 000 strokes, 10 ⁻¹ mm	280 max.	L ₅₀ life at 10 000 r/min., hrs
Mechanical stability		Shelf life 5 years
Roll stability, 50 hrs at 80 °C, 10 ⁻¹ mm	295 max.	
V2F test	'M'	

These characteristics represent typical values.



Advanced tool for grease selection and relubrication calculation

LubeSelect for SKF greases

Selecting a suitable grease for a particular bearing is a crucial step if the bearing is to meet design expectations in its application. SKF knowledge about bearing lubrication has been encapsulated into a computer program that can be consulted at skf.com/lubeselect

LubeSelect for SKF greases provides you a user friendly tool to select the right grease and suggest frequency and quantity, while taking into account the particular conditions of your application. General guidelines for typical greases for different applications are also available.



Scan or click the QR code, or go to skf.com/lubeselect

skf.com | skf.com/lubrication | skf.com/mapro

© SKF is a registered trademark of the SKF Group.

© SKF Group 2022. All rights reserved. Please note that this publication may not be copied or distributed, in whole or in part, unless prior written permission is granted.

Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 12053/3 EN · November 2022

Certain image(s) used under license from Shutterstock.com.