

SKF Bearing Grease

Extreme pressure low temperature bearing grease

LGWM 1

SKF LGWM 1 is a low consistency mineral oil based grease, using a lithium soap and containing extreme pressure additives. It is extremely suitable for the lubrication of bearings operating under both radial and axial loads.

- Good oil film formation at low temperatures down to -30 °C (-20 °F)
- Good pumpability down to low temperatures
- Good corrosion protection
- · Good water resistance

Typical applications

- Wind turbine main shafts
- · Screw conveyors
- · Centralised lubrication systems
- · Spherical roller thrust bearing applications

Available pack sizes		
Packsize	Designation	
420 ml cartridge	LGWM 1/0.4	
5 kg can	LGWM 1/5	
18 kg pail	LGWM 1/18	
50 kg drum	LGWM 1/50	
180 kg drum	LGWM 1/180	
Electro-mechanical lubricant dispensers		S LGWM 1/18
TLMR 101 series 380 ml refill (incl. battery)	LGWM 1/MR380B	SAF Bearing Small
TLMR 201 series 380 ml refill	LGWM 1/MR380	





Technical data			
Designation	LGWM 1/(pack size)		
DIN 51825 code	KP1G-30	Corrosion protection:	
NLGI consistency class	1	Emcor: – standard ISO 11007 – water washout test	0-0 0-0
Thickener	Lithium	- salt wateer test (0.5% NaCl)	0-0
Colour	Brown	Oil separation	
Base oil type	Mineral	DIN 51 817, 7 days at 40 °C, static, %	8–13
Operating temperature range	−30 to +110 °C (−20 to +230 °F)	Lubrication ability R2F, running test B at 120 °C	Pass at 100 °C <i>(212 °F)</i>
Dropping point DIN ISO 2176	>170 °C (>340 °F)	Copper corrosion	
Base oil viscosity		DIN 51 811	2 max. at 100 °C (>212 °F)
40 °C, mm ² /s 100 °C, mm ² /s	200 15	EP performance Wear scar DIN 51350/5, 1 400 N, mm	1,8 max.
Penetration DIN ISO 2137		4–ball test, welding load DIN 51350/4, N	2 800 min.
60 strokes, 10 ⁻¹ mm	310-340	N	
100 000 strokes, 10 ⁻¹ mm	+50 max.	Rolling bearing grease life	1 000 min. at 110 °C
Water resistance DIN 51 807/1,		R0F test, L50 life at 10 000 r/min., hrs	(230 °F)
3 hrs at 90 °C	1 max.	Shelf life	5 years
These characteristics represent typical va	lues.		




Advanced tool for grease selection and relubrication calculation

LubeSelect for SKF greases

Selecting a suitable grease for a particular bearing is a crucial step if the bearing is to meet design expectations in its application. SKF knowledge about bearing lubrication has been encapsulated into a computer program that can be consulted at skf.com/lubeselect

LubeSelect for SKF greases provides you a user friendly tool to select the right grease and suggest frequency and quantity, while taking into account the

particular conditions of your application. General guidelines for typical greases for different applications are also available.





skf.com | skf.com/lubrication | skf.com/mapro

- $^{\scriptsize{\$}}$ SKF is a registered trademark of AB SKF (publ).
- © SKF Group 2024. All rights reserved. Please note that this publication may not be copied ordistributed, in whole or in part, unless prior written permission is granted.

Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.