

Compact Unit MKU11



- Optimized pressure – for oil systems with piston distributors
- User-friendly – with push button
- Maintenance-friendly – all functions accessible from lid


Quality in a small package

The compact unit MKU11 has two advantages for automated centralized lubrication on small machines: quick return on investment and reliable protection for bearings.


The unit has been especially designed for operation with piston distributors and minimal dosages from 0.01 cm³.

It fits where compact installation dimensions are required and has a pressure outlet that can be easily connected, left or right.

The compact unit MKU11 is available worldwide with complete accessories: gauge, pressure switch, fluid level monitoring, and most importantly, it is SKF quality.



Order No. MKU11-KW2-0005



Technical data

Output 0.1/0.12 l/min
 Operating pressure . . 16 bars
 Reservoir capacity . . 1.8 l

Operating voltage
 . . 230 V, 50/60 Hz or 115 V, 50/60 Hz
 Rated current
 0.96/0.7 A or 1.83/1.33 A
 Rated power input
 75.5/62.5 W or 71.5/58.3 W

Type of enclosure . . . IP54
 Service viscosity (oil) . 20-750 mm²/s

SKF Lubrication Systems Germany GmbH

Motzener Strasse 35/37 · 12277 Berlin · Germany
 PF 970444 · 12704 Berlin · Germany
 Tel. +49 (0)30 72002-0 · Fax +49 (0)30 72002-111
www.skf.com/lubrication

Order No. 1-1212-EN

Subject to change without notice! (07/2014)

® SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

