

# Safety Data Sheet

## LGET 2

### SECTION 1: Identification

#### 1.1. Product identifier used on the label

Trade name: LGET 2

#### 1.2. Recommended use of the chemical and restrictions on use

Recommended uses: Lubricant.

Inadvisable uses: None.

#### 1.3. Details of the supplier of the safety data sheet

##### Supplier

Company: SKF USA Inc.  
Address: 890 Forty Foot Road  
Zip code: 19446  
City: Lansdale, PA  
Country: UNITED STATES OF AMERICA  
Email: Mapro.Repair.USA@skf.com  
Phone: +1 888-753-3477  
Homepage: www.skf.com

##### Manufacturer

Company: SKF MPT  
Address: Meidoornkade 14  
Zip code: 3992 AE  
City: AE Houten  
Country: NETHERLANDS (KINGDOM OF THE)  
Email: support.mpt@skf.com  
Phone: +31 30 6307200  
Homepage: www.skf.com

#### 1.4. Emergency phone number

+31 30 6307200

For Chemical Emergency  
Spill, Leak, Fire, Exposure, or Accident  
Call CHEMTREC Day or Night  
Within USA and Canada: 1-800-424-9300  
1 703-527-3887 (collect calls accepted)

Location:  
CHEMTREC  
2900 Fairview Park Drive  
Falls Church VA 22042-4513  
USA

### SECTION 2: Hazard Identification

# Safety Data Sheet

## LGET 2

### 2.1. Classification of the chemical in accordance with paragraph (d) of §1910.1200

**HazCom classification:** The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures.

**Most serious harmful effects:** May cause slight irritation to the skin and eyes.

### 2.2. Label elements

The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures.

### 2.3. Other hazards which do not result in classification

None known.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

Substance	CAS No	Concentration	Notes
1H-Benzotriazole (1,2,3)	95-14-7	1 -< 5 %	

**Ingredient comments:** The mineral oils in the product contain <3% DMSO extract(IP 346).

The specific chemical identity and/or exact percentage of composition has been withheld as a trade secret.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:** Seek fresh air. Seek medical advice in case of persistent discomfort.

**Ingestion:** Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

**Skin contact:** Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

**Eye contact:** Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

**General:** Bring the safety data sheet or label when seeking medical advice.

### 4.2. Most important symptoms/effects, acute and delayed.

May cause slight irritation to the skin and eyes.

### 4.3. Indication of immediate medical attention and special treatment needed, if necessary.

Treat symptoms. No special immediate treatment required.

## SECTION 5: Fire-fighting measures

### 5.1. Suitable (and unsuitable) extinguishing media.

**Suitable extinguishing media:** Extinguish with powder, foam or water mist. Use water or water mist to cool non-ignited stock.

**Unsuitable extinguishing media:** Do not use a jet of water, as it may spread the fire.

## Safety Data Sheet

LGET 2

### 5.2. Specific hazards arising from the chemical

Not flammable, but combustible. The product decomposes when combusted and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Hydrogen fluoride.

### 5.3. Special protective equipment and precautions for fire-fighters.

If there is a risk of exposure to vapour and flue gases, a self-contained breathing apparatus must be worn.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel:** Stop leak if this can be done without risk. Wear safety goggles if there is a risk of eye splash. Wear gloves.

**For emergency responders:** In addition to the above: Normal protective clothing is recommended.

### 6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

### 6.3. Methods and material for containment and cleaning up

Contain and absorb spills using sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

### 6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

### 7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely out of reach of children and not together with food, feed, medicine and the like. Keep in tightly closed original packaging. Avoid contact with moisture and water. Do not store with the following: Alkaline metals.

### 7.3. Specific end use(s)

None.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational exposure limit

Substance name	Time period	ppm	mg/m <sup>3</sup>	fiber/cm <sup>3</sup>	Remarks	Notations

# Safety Data Sheet

## LGET 2

Mineral oil, excluding metal working fluids	ACGIH TWA		5		Pure, highly and severely refined. OEL value for: Mineral oil, excluding metal working fluids	A4, I
Mineral oil, excluding metal working fluids	OSHA		5		OEL value for: Mineral oil, excluding metal working fluids	

A4 = Not Classifiable as a Human Carcinogen.

I = Inhalable fraktion.

**Measuring methods:** Compliance with the stated occupational exposure limits may be checked by occupational hygiene measurements measurements according to NIOSH/OSHA.

**Legal basis:** ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2024. OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006.

### 8.2. Exposure controls

**Appropriate engineering controls:** Use the product under well-ventilated conditions. Wear the personal protective equipment specified below.

**Personal protective equipment, eyeface protection:** Wear safety goggles if there is a risk of eye splash.

**Personal protective equipment, hand protection:** Plastic or rubber gloves recommended.

**Personal protective equipment, respiratory protection:** Not required.

**Environmental exposure controls:** Ensure compliance with local regulations for emissions.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Parameter	Value/unit
physical state	Paste
Color	White
Odour	No data
Solubility	No data

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	
Initial boiling point and boiling range	> 300 °C	>572°F
Flammability (solid, gas)	No data	
Upper/lower flammability limits	No data	
Explosion limits	No data	
Flash Point	No data	
Auto-ignition temperature	No data	
Decomposition temperature:	> 260 °C	>=500°F

## Safety Data Sheet

### LGET 2

pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	No data	
Viscosity	No data	
Partition coefficient n-octanol/water	No data	
Vapour pressure	< 0.01 hPa	122 °F
Density	1.99 g/cm <sup>3</sup>	68 °F
Relative density	No data	
Relative vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

#### 9.2. Other information

Parameter	Value/unit	Remarks
VOC (Volatile organic compounds):	0 %	

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

Reacts with the following: Alkaline metals.

#### 10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

#### 10.3. Possibility of hazardous reactions

None known.

#### 10.4. Conditions to avoid

Avoid contact with moisture and water.

#### 10.5. Incompatible materials

Alkaline metals.

#### 10.6. Hazardous decomposition products

The product decomposes when combusted or heated to high temperatures and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Hydrogen fluoride.

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

##### Acute toxicity - oral

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 5000 mg/kg			

Ingestion may cause discomfort. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

## Safety Data Sheet

### LGET 2

#### Acute toxicity - dermal

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rabbit	LD50		> 5000 mg/kg			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Acute toxicity - inhalation

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LC50	3 h	1910 mg/m <sup>3</sup>			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Skin corrosion/irritation

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Slightly irritating.		

May irritate the skin - may cause reddening. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Serious eye damage/eye irritation

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Irritating		

May cause eye irritation. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Respiratory sensitization or skin sensitization

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Guinea pig	Respiratory sensitization or skin sensitization			Non-sensitizing	OECD 406	

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Germ cell mutagenicity

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Mouse In vitro tests.				No indications.	OECD 474	
Microorganisms. In vitro tests.	Ames test			No indications.	OECD 471	

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Carcinogenic properties

##### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Not carcinogenic		

# Safety Data Sheet

## LGET 2

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. This product does not contain any carcinogens or potential carcinogens at reportable quantities as listed by OSHA, IARC or NTP.

### Reproductive toxicity

#### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				No indications.		

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

**Single STOT exposure:** The product does not have to be classified. Test data are not available.

**Repeated STOT exposure:** The product does not have to be classified. Test data are not available.

**Aspiration hazard:** The product does not have to be classified. Test data are not available.

### 11.2. Information on other hazards

**Endocrine disrupting properties:** None known.

**Other toxicological effects:** None known.

## SECTION 12: Ecological information

### 12.1. Ecotoxicity

#### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Brachydanio rerio		96hLC50	1300 mg/l			
Crustacea	Daphnia magna		24hEC50	200 mg/l			
Crustacea	Daphnia magna		48hEC50	141.6 mg/l			
Algae	Name of species not specified		96hIC50	15.4 mg/l			
Algae	Scenedesmus subspicatus		72hIC50	91 - 141 mg/l			
Bacteria	Pseudomonas putida		3hEC50	> 1000 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

### 12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

### 12.3. Bioaccumulative potential

#### 1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
			BCF	2.563			
			Log Pow	1.34			

# Safety Data Sheet

## LGET 2

No bioaccumulation expected.

### 12.4. Mobility in soil

Expected to be mobile in soil. Test data are not available.

### 12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

### 12.6. Endocrine disrupting properties

Contains at least one substance considered to have endocrine disrupting properties.

### 12.7. Other adverse effects

None known.

German water pollution classification (WGK): 1

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

## SECTION 14: Transport information

<b>14.1. UN number:</b>	Not applicable.	<b>14.4. Packing group:</b>	Not applicable.
<b>14.2. UN proper shipping name:</b>	Not applicable.	<b>14.5. Environmental hazards:</b>	Not applicable.
<b>14.3. Transport hazard class(es):</b>	Not applicable.		

### 14.6. Special precautions which a user needs to be aware of, or needs to comply with, in connection with transport or conveyance either within or outside their premises.

None.

### 14.7. Transport in bulk (according to IMO instruments)

Not applicable.

**Other Information:** The product is not covered by the rules for transport of dangerous goods.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations specific for the product in question

#### Proposition 65

**Chemicals known to cause cancer:** None of the substances in the formulation is listed in the latest version publicly available.

**Chemicals known to cause reproductive toxicity:** None of the substances in the formulation is listed in the latest version publicly available.

**TSCA:** All substances in the formulation are listed in the latest version publicly available.

#### NFPA ratings

## Safety Data Sheet

### LGET 2

**Health hazard:** 0  
**Flammability:** 1  
**Instability:** 0

#### 15.2. Chemical Safety Assessment

Substance name
1H-Benzotriazole (1,2,3)

#### SECTION 16: Other information

##### Version history and indication of changes

Version	Revision date	Responsible	Changes
2.6.0	5/27/2025	SRU	1,5,7,8,10,12,13,15,16

**Abbreviations:**  
 PBT: Persistent, Bioaccumulative and Toxic  
 vPvB: Very Persistent and Very Bioaccumulative  
 STOT: Specific Target Organ Toxicity

**Other Information:** This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with CFR29, §1910.1200.

**Training advice:** A thorough knowledge of this safety data sheet should be a prerequisite condition.

**Revision date:** 5/27/2025

**Replaces date:** 10/2/2023

**Classification method:** Calculation based on the hazards of the known components.

**Country:** US