

SKF Bearing Grease

# Extremely high viscosity bearing grease with solid lubricants

# LGEV 2


SKF LGEV 2 is a mineral oil based grease, using a lithium-calcium soap. Its high content of molybdenum disulphide and graphite, in conjunction with an extremely high viscosity oil, provide outstanding protection under the harshest conditions involving high loads, slow rotations and severe vibrations.

- Extremely suitable for lubricating large sized spherical roller bearings subject to high loads and slow rotations, a situation where microslip is likely to occur
- Extremely mechanically stable providing good corrosion protection

### Typical applications

- · Trunnion bearings on rotating drums
- Support and thrust rollers on rotary kilns and dryers
- · Bucket wheel excavators
- · Slewing ring bearings
- High pressure roller mills
- Crushers





Available pack sizes	
Packsize	Designation
35 g tube	LGEV 2/0.035
420 ml cartridge	LGEV 2/0.4
5 kg can	LGEV 2/5
18 kg pail	LGEV 2/18
50 kg drum	LGEV 2/50
180 kg drum	LGEV 2/180
Electro-mechanical lubricant dispensers	
TLMR 101 series 380 ml refill (incl. battery)	LGEV2/MR380B
TLMR 201 series 380 ml refill	LGEV 2/MR380



Technical data			
Designation	LGEV 2/(pack size)		
DIN 51825 code	KPF2K-10	Corrosion protection	
NLGI consistency class	2	Emcor: – standard ISO 11007 – water washout test	0-0 0-0
Thickener	Lithium/calcium	Waterresistance	
Colour	Black	DIN 51 807/1,	
Base oil type	Mineral	3 hrs at 90 °C	1 max.
Operating temperature range	–10 to +120 °C <i>(</i> 15 to 250 °F)	Oil separation DIN 51 817, 7 days at 40 °C, static, %	1–5
Dropping point DIN ISO 2176	>180 °C (>355 °F)	Lubrication ability	
Base oil viscosity		R2F, running test B at 120 °C	Pass at 100 °C (210 °F)
40 °C, mm²/s 100 °C, mm²/s	1 300 49	Rolling bearing grease life ROF test, L <sub>50</sub> life at 10 000 r/min., hrs	1 000 min. at 100 °C (210 °F)
Penetration DIN ISO 2137 60 strokes, 10 <sup>-1</sup> mm 100 000 strokes, 10 <sup>-1</sup> mm	265-295 +50 max.	Copper corrosion DIN 51 811	1 max. at 100 °C (210 °F)
Mechanical stability Roll stability, 72 hrs at 100 °C, 10 <sup>-1</sup> mm V2F test	+50 max. 'M'	EP performance Wear scar DIN 51350/5, 1 400 N, mm 4-ball test, welding load DIN 51350/4, N	1,2 max. 3 000 min.
V2. (30t		Shelf life	5 years
These characteristics represent typical values.			



Advanced tool for grease selection and relubrication calculation

## LubeSelect for SKF greases

Selecting a suitable grease for a particular bearing is a crucial step if the bearing is to meet design expectations in its application. SKF knowledge about bearing lubrication has been encapsulated into a computer program that can be consulted at skf.com/lubeselect

LubeSelect for SKF greases provides you a user friendly tool to select the right grease and suggest frequency and quantity, while taking into account the particular conditions of your application. General guidelines for typical greases for different applications are also available.



Scan or click the QR code, or go to skf.com/lubeselect

### skf.com | skf.com/lubrication | skf.com/mapro

- $^{\scriptsize{\$}}$  SKF is a registered trademark of AB SKF (publ).
- © SKF Group 2023. All rights reserved. Please note that this publication may not be copied ordistributed, in whole or in part, unless prior written permission is granted.

Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.