

SKF Gloves

Personal protective equipment



Heat resistant gloves TMBA G11

The TMBA G11 are specially designed for the handling of heated bearings.

- Low lint
- Heat resistant up to 150 °C (302 °F)
- Cut resistant
- Non allergenic
- Fits a wide range of hand sizes
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407)

Technical data	
Designation	TMBA G11
Material outer	Polyester
Material inne	Cotton
Size	9
Colour	White
Max. recommended temperature	150 °C (302 °F)
Pack size	1 pair

Extreme temperature gloves TMBA G11ET

The TMBA G11ET are especially designed for the safe handling of heated bearings or other components for prolonged periods.

- Withstands extreme temperatures of up to 400 °C (752 °F) unless in the presence of hot liquid or steam
- Allows the safe handling of heated components
- High-degree of non-flammability reduces the risk of burning
- Extremely tough Kevlar gloves with high cut, abrasion, puncture and tear resistance for increased safety
- Non-allergenic
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407)



Technical data	
Designation	TMBA G11ET
Material outer	Para-aramid
Material middle	Para-aramid
Material inner	Cotton
Size	10
Colour	Yellow
Max. recommended temperature	400 °C (752 °F)
Pack size	1 pair

Heat and oil resistant gloves TMBA G11H

The TMBA G11H are specially designed for the handling of hot and oily bearings.

- Offers a high degree of heat, cut, oil and water resistance
- Melt and burn resistant
- Heat resistant up to 250 °C (482 °F)
- Abrasion, cut, tear and puncture resistant
- Remains heat resistant when wet
- Suitable for submerging in liquids with a temperature up to 120 °C (248 °F) (e.g. hot oil bath)
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407)
- Non-allergenic
- Fits a wide range of hand sizes



Technical data	
Designation	TMBA G11H
Material outer	Para-aramid
Material middle	Nitrile
Material inner	Cotton
Size	10
Colour	Yellow
Max. recommended temperature	250 °C (482 °F)
Pack size	1 pair



skf.com | skf.com/mapro | skf.com/lubrication

® SKF is a registered trademark of AB SKF (publ).

© SKF Group 2024 . All rights reserved. Please note that this publication may not be copied or distributed, in whole or in part, unless prior written permission is granted.

Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 14368/4 EN · July 2024