

LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name: LGFP 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant.

1.3. Details of the supplier of the safety data sheet

Supplier

Company: SKF MPT

Address: Meidoornkade 14

Zip code: 3992 AE
City: AE Houten
Country: NETHERLANDS
E-mail: support.mpt@skf.com
Phone: +31 30 6307200
Homepage: www.skf.com

1.4. Emergency Telephone Number

Members of the public: 111 (NHS 111 (Scotland: NHS 24)).

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

CLP-classification: The product shall not be classified as hazardous according to the classification and

labeling rules for substance and mixtures.

Most serious harmful effects: May cause slight irritation to the skin and eyes.

2.2. Label elements

The product shall not be classified as hazardous according to the classification and labeling rules for substance and mixtures.

2.3. Other hazards

The product does not contain any PBT or vPvB substances.

Endocrine disrupting properties: None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Contains no substances subject to reporting requirements

Ingredient comments: The mineral oils in the product contain <3% DMSO extract(IP 346).

SECTION 4: First aid measures



LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

4.1. Description of first aid measures

Inhalation: Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion: Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical

advice in case of persistent discomfort.

Skin contact: Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in

case of persistent discomfort.

Eye contact: Flush with water (preferably using eye wash equipment) until irritation subsides. Seek

medical advice if symptoms persist.

General: When obtaining medical advice, show the safety data sheet or label.

4.2. Most important symptoms and effects, both acute and delayed

May cause slight irritation to the skin and eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media: Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool

non-ignited stock.

Unsuitable extinguishing

media:

Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. The product decomposes when combusted and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Nitrous gases/ Sulphur oxides/ Phosphorous oxides/ Aldehydes/ Ketones.

5.3. Advice for firefighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases - seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Wear safety goggles if there is a risk of eye splash. Wear gloves.

For emergency responders: In addition to the above: Normal protective clothing equivalent to EN 469 is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections



Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use the product under well-ventilated conditions. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Keep in tightly closed original packaging. Do not store with the following: Acids/ Oxidisers. Store frost-free. Do not expose to heat (e.g. sunlight). Storage temperature: 0 - 40 °C. Store in a dry, cool, well-ventilated area.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit: Contains no substances subject to reporting requirements

Compliance with occupational exposure limits may be checked by occupational hygiene Measuring methods:

measurements.

Legal basis: EH40/2005 Workplace exposure limits. Last amended January 2020.

8.2. Exposure controls

Appropriate engineering

controls:

Wear the personal protective equipment specified below.

eye/face protection:

Personal protective equipment, Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN

Personal protective equipment, Plastic or rubber gloves recommended.

hand protection:

Personal protective equipment, Not required.

respiratory protection:

Environmental exposure

controls:

Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter	Value/unit
State	Paste
Colour	Yellow
Odour	Characteristic
Solubility	Insoluble in the following: Water.

Parameter Value/unit Remarks	
------------------------------	--



LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

		Version: 2.5.0
Odour threshold	No data	
Melting point	> 250 °C	(1013 hPa)
Freezing point	No data	
Initial boiling point and boiling range	> 250 °C	(1013 hPa)
Flammability (solid, gas)	No data	
Flammability limits	No data	
Explosion limits	No data	
Flash Point	> 200 °C	
Auto-ignition temperature	No data	
Decomposition temperature	No data	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	No data	
Viscosity	No data	
Partition coefficient n-octonol/water	No data	
Vapour pressure	No data	
Density	~ 0,93 g/cm3	(20 °C) DIN 51757
Relative density	No data	
Vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

9.2. Other information

Parameter	Value/unit	Remarks
Explosive properties		Non-explosive
Oxidising properties		Non-oxidising.
VOC (Volatile organic compounds):	<3 %	

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Acids/ Oxidisers.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid heating and contact with ignition sources. Avoid direct sunlight. Avoid temperatures < 0°C.

10.5. Incompatible materials

Acids/ Oxidisers.

10.6. Hazardous decomposition products

The product decomposes when combusted or heated to high temperatures and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Nitrous gases/ Sulphur oxides/ Phosphorous oxides/ Aldehydes/ Ketones.



LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity - oral: The product does not have to be classified. Test data are not available. Ingestion of large

quantities may cause discomfort.

Acute toxicity - dermal: The product does not have to be classified. Test data are not available.

Acute toxicity - inhalation: The product does not have to be classified. Test data are not available.

Skin corrosion/irritation: The product does not have to be classified. Test data are not available. May cause slight

irritation.

Serious eye damage/eye

irritation:

The product does not have to be classified. Test data are not available. Temporary irritation.

Respiratory sensitisation or

skin sensitisation:

The product does not have to be classified. Test data are not available.

Germ cell mutagenicity: The product does not have to be classified. Test data are not available.

Carcinogenic properties: The product does not have to be classified. Test data are not available.

Reproductive toxicity: The product does not have to be classified. Test data are not available.

Single STOT exposure: The product does not have to be classified. Test data are not available.

Repeated STOT exposure: The product does not have to be classified. Test data are not available.

Aspiration hazard: The product does not have to be classified. Test data are not available.

11.2. Information on other hazards

Endocrine disrupting

properties:

None known.

Other toxicological effects: None known.

SECTION 12: Ecological information

12.1. Toxicity

LGFP 2

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Brachydanio rerio		96hLC50	> 100 mg/l			
Crustacea	Daphnia magna		48hEC50	> 100 mg/l			
Algae			96hErC50	> 100 mg/l			
Algae			96hEbC50	> 100 mg/l			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

12.2. Persistence and degradability



LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

Test data are not available.

12.3. Bioaccumulative potential

Test data are not available.

12.4. Mobility in soil

Test data are not available.

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects

None known.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

Category of waste: EWC code: Depends on line of business and use, for instance 12 01 12* spent waxes and

tats

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

hazards:

SECTION 14: Transport information

14.1. UN number or ID number:Not applicable.14.4. Packing group:Not applicable.14.2. UN proper shippingNot applicable.14.5. EnvironmentalNot applicable.

name:

14.3. Transport hazard Not applicable.

class(es):

14.6. Special precautions for user

None

14.7. Maritime transport in bulk according to IMO instruments

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information



LGFP 2

Replaces date: 03/05/2021 Revision date: 02/02/2023

Version: 2.5.0

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special Provisions: None.

15.2. Chemical Safety Assessment

Other Information: Chemical safety assessment has not been performed.

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
2.5.0	02/02/2023	Bureau Veritas HSE/ SRU	1-2, 7, 9, 11-12, 16

Abbreviations: PBT: Persistent, Bioaccumulative and Toxic

vPvB: Very Persistent and Very Bioaccumulative

STOT: Specific Target Organ Toxicity

Other Information: This safety data sheet has been prepared for and applies to this product only. It is based on

our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with Regulation 1907/2006/EC "The Registration, Evaluation and Authorization of Chemicals" as amended by the stationary UK

REACH etc. (EU Exit) as subsequently changed.

Training advice: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Classification method: Calculation based on the hazards of the known components.

Country: GB