

Safety Data Sheet

LGHP 2

SECTION 1: Identification

1.1. Product identifier used on the label

Trade name: LGHP 2

1.2. Recommended use of the chemical and restrictions on use

Recommended uses: Lubricant.

Inadvisable uses: None.

1.3. Details of the supplier of the safety data sheet

Supplier

Company: SKF USA Inc.
Address: 890 Forty Foot Road
Zip code: 19446
City: Lansdale, PA
Country: UNITED STATES OF AMERICA
Email: Mapro.Repair.USA@skf.com
Phone: +1 888-753-3477
Homepage: www.skf.com

Manufacturer

Company: SKF MPT
Address: Meidoornkade 14
Zip code: 3992 AE
City: AE Houten
Country: NETHERLANDS (KINGDOM OF THE)
Email: support.mpt@skf.com
Phone: +31 30 6307200
Homepage: www.skf.com

1.4. Emergency phone number

+31 30 6307200

For Chemical Emergency
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
1 703-527-3887 (collect calls accepted)

Location:
CHEMTREC
2900 Fairview Park Drive
Falls Church VA 22042-4513
USA

SECTION 2: Hazard Identification

Safety Data Sheet

LGHP 2

2.1. Classification of the chemical in accordance with paragraph (d) of §1910.1200

HazCom classification: Reproductive toxicity, Category 2;H361f

Most serious harmful effects: Suspected of damaging fertility.

2.2. Label elements

Pictograms



Signal word: Warning

Contains

Substance: Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene;

Hazard Statements

Suspected of damaging fertility.

Precautionary statements

Obtain special instructions before use.
Do not handle until all safety precautions have been read and understood.
Wear protective gloves/protective clothing/eye protection/face protection.
If exposed or concerned: Get medical advice/attention.
Store locked up.
Dispose of contents/container in accordance with local regulation.

2.3. Other hazards which do not result in classification

None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Substance	CAS No	Concentration	Notes
reaction mass of: 3,3'-dicyclohexyl-1,1'-methylenebis(4,1-phenylene)diurea, 3-cyclohexyl-1-(4-(4-(3-octadecylureido)benzyl)phenyl)urea, 3,3'-dioctadecyl-1,1'-methylenebis(4,1-phenylene)diurea	-	3 -< 5 %	
3,3'-dicyclohexyl-1,1'-methylenebis(4,1-phenylene)diurea	58890-25-8	3 -< 5 %	
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	68411-46-1	3 -< 5 %	
3,3'-dioctadecyl-1,1'-methylenebis(4,1-phenylene)diurea	43136-14-7	1 -< 3 %	

Safety Data Sheet

LGHP 2

Ingredient comments:

The mineral oils in the product contain <3% DMSO extract(IP 346).

The specific chemical identity and/or exact percentage of composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion:

Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

Skin contact:

Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

Eye contact:

Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

General:

Bring the safety data sheet or label when seeking medical advice.

4.2. Most important symptoms/effects, acute and delayed.

Suspected of damaging fertility.

4.3. Indication of immediate medical attention and special treatment needed, if necessary.

Treat symptoms. No special immediate treatment required.

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media.

Suitable extinguishing media:

Extinguish with powder, foam or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media:

Do not use a jet of water, as it may spread the fire.

5.2. Specific hazards arising from the chemical

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

5.3. Special protective equipment and precautions for fire-fighters.

Wear Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely. Wear gloves.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel:

Wear safety goggles if there is a risk of eye splash. Wear gloves. Stay upwind/keep distance from source. Stop leak if this can be done without risk. Keep unnecessary personnel away. Wear suitable protective clothing.

For emergency responders:

In addition to the above: Protective suit is recommended.

Safety Data Sheet

LGHP 2

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spills using sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Running water and eye wash equipment must be available. Wash hands before breaks, before using restroom facilities, and at the end of work. A risk assessment must ensure that employees are not exposed to effects which might pose a risk by pregnancy or breastfeeding. A risk assessment must assure that employees are not exposed to effects from carcinogenic, mutagenic, or reproductive toxic substances. Special work clothes must be worn. Neither smoking, eating nor drinking is allowed in the work room. Work clothes, personal protective equipment and private clothes must be stored separately. Do not carry work clothes and personal protective equipment during lunch breaks. There must be an easy access to washing and toilet facilities.

7.2. Conditions for safe storage, including any incompatibilities

To be stored safely out of reach of children and not together with food, feed, medicine and the like. Keep in tightly closed original packaging. Do not store with the following: Oxidizers.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit

Substance name	Time period	ppm	mg/m ³	fiber/cm ³	Remarks	Notations
Mineral oil, excluding metal working fluids	ACGIH TWA		5		Pure, highly and severely refined. OEL value for: Mineral oil, excluding metal working fluids	A4, I
Mineral oil, excluding metal working fluids	OSHA		5		OEL value for: Mineral oil, excluding metal working fluids	

A4 = Not Classifiable as a Human Carcinogen.

I = Inhalable fraktion.

Measuring methods:

Compliance with occupational exposure limits may be checked by occupational hygiene measurements according to NIOSH/OSHA.

Safety Data Sheet

LGHP 2

Legal basis: ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2025.
OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006.

8.2. Exposure controls

Appropriate engineering controls:	Use the product under well-ventilated conditions. Wear the personal protective equipment specified below.
Personal protective equipment, eye/face protection:	Wear safety goggles if there is a risk of eye splash.
Personal protective equipment, skin protection:	Wear suitable protective clothing.
Personal protective equipment, hand protection:	Wear gloves. Nitrile rubber/ Neoprene rubber/ PVC. Breakthrough time has not been determined for the product. Change gloves often. The suitability and durability of a glove is dependant on usage, e.g. frequency and duration of contact, glove material thickness, functionality and chemical resistance. Always seek advice from the glove supplier.
Personal protective equipment, respiratory protection:	Not required. In case of risk of formation of spray mist, wear respiratory protective equipment with P2 filter.
Environmental exposure controls:	Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter	Value/unit	
physical state	Paste Fat.	
Color	Light blue	
Odour	Characteristic	
Solubility	Insoluble in the following: Water.	

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	
Initial boiling point and boiling range	No data	
Flammability (solid, gas)	No data	
Upper/lower flammability limits	No data	
Explosion limits	No data	
Flash Point	210 °C	410 °F
Auto-ignition temperature		Not spontaneously flammable
Decomposition temperature:	No data	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	No data	
Viscosity	No data	
Partition coefficient n-octanol/water	No data	
Vapour pressure	No data	
Density	0,90 g/cm³	(77 °F)
Relative density	No data	

Safety Data Sheet

LGHP 2

Relative vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

9.2. Other information

Parameter	Value/unit	Remarks
-----------	------------	---------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Oxidizers.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid heating and contact with ignition sources.

10.5. Incompatible materials

Oxidizers.

10.6. Hazardous decomposition products

The product decomposes when combusted or heated to high temperatures and the following toxic gases can be formed: Carbon monoxide and carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral:	The product does not have to be classified. Test data are not available. Ingestion of large quantities may cause discomfort.
Acute toxicity - dermal:	The product does not have to be classified. Test data are not available.
Acute toxicity - inhalation:	The product does not have to be classified. Test data are not available.
Skin corrosion/irritation:	The product does not have to be classified. Test data are not available. Degreases the skin. Long-term exposure may cause irritation and possible infection.
Serious eye damage/eye irritation:	The product does not have to be classified. Test data are not available. Temporary irritation.
Respiratory sensitization or skin sensitization:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.

Safety Data Sheet

LGHP 2

Carcinogenic properties:	The product does not have to be classified. Test data are not available. This product does not contain any carcinogens or potential carcinogens at reportable quantities as listed by OSHA, IARC or NTP.
Reproductive toxicity:	Suspected of damaging fertility.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.

11.2. Information on other hazards

Endocrine disrupting properties: None known.

Other toxicological effects: None known.

SECTION 12: Ecological information

12.1. Ecotoxicity

The product does not have to be classified. Test data are not available. The product contains small quantities of environmentally hazardous substances.

12.2. Persistence and degradability

Test data are not available. Not expected to be biodegradable.

12.3. Bioaccumulative potential

Test data are not available.

12.4. Mobility in soil

Test data are not available.

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Safety Data Sheet

LGHP 2

Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14: Transport information

14.1. UN number:	Not applicable.	14.4. Packing group:	Not applicable.
14.2. UN proper shipping name:	Not applicable.	14.5. Environmental hazards:	Not applicable.
14.3. Transport hazard class(es):	Not applicable.		

14.6. Special precautions which a user needs to be aware of, or needs to comply with, in connection with transport or conveyance either within or outside their premises.

None.

14.7. Transport in bulk (according to IMO instruments)

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations specific for the product in question

Proposition 65

Chemicals known to cause cancer: None of the substances in the formulation is listed in the latest version publicly available.

Chemicals known to cause reproductive toxicity: None of the substances in the formulation is listed in the latest version publicly available.

TSCA: All substances in the formulation are listed in the latest version publicly available.

NFPA ratings

Health hazard: 1

Flammability: 1

Instability: 0

15.2. Chemical Safety Assessment

Substance name
reaction mass of: 3,3'-dicyclohexyl-1,1'-methylenebis(4,1-phenylene)diurea, 3-cyclohexyl-1-(4-(4-(3-octadecylureido)benzyl)phenyl)urea, 3,3'-dioctadecyl-1,1'-methylenebis(4,1-phenylene)diurea
3,3'-dicyclohexyl-1,1'-methylenebis(4,1-phenylene)diurea
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene
3,3'-dioctadecyl-1,1'-methylenebis(4,1-phenylene)diurea

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
2.1.0	5/28/2025	SRU	1,5,6,7,8,11,13,16

Abbreviations: PBT: Persistent, Bioaccumulative and Toxic
vPvB: Very Persistent and Very Bioaccumulative

Safety Data Sheet

LGHP 2

STOT: Specific Target Organ Toxicity

Other Information:

This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with CFR29, §1910.1200.

Training advice:

A thorough knowledge of this safety data sheet should be a prerequisite condition.

Revision date:

5/28/2025

Replaces date:

3/20/2023

Classification method:

Calculation based on the hazards of the known components.

Country:

US