


Silicone rubber (MVQ) - 85A

SKF Ecosil

DIN: MVQ

Property	Unit	Value	Standard
Standard color	–	Reddish brown 	
Durometer hardness	Shore A	85 ±5	DIN ISO 48-4
Density	g/cm ³	1,42 ±0,03	DIN EN ISO 1183-1
Tensile strength	MPa	≥ 6,5	DIN 53504
Elongation at break	%	≥ 130	DIN 53504
100% modulus	MPa	≥ 4,5	DIN 53504
Compression set: 175 °C / 24 h	%	≤ 20	DIN ISO 815
Tear strength	N/mm	9	DIN ISO 34-1
Heat resistance, air 168 h / 225 °C			
Change in durometer hardness	Shore A	+3	DIN ISO 48-4
Change in tensile strength	%	–10	DIN 53504
Change in elongation at break	%	–40	DIN 53504
Minimum service temperature	°C	–60	–
Maximum service temperature	°C	+200	–
Short term	°C	+220	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards. The values density, durometer hardness (Shore A) and those marked with the symbols, greater than or equal to (≥) and smaller than or equal to (≤), are nominal values and must be fulfilled for each batch. These values are tested on selected samples.

skf.com/seals

® SKF is a registered trademark of the SKF Group.

© SKF Group 2020

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB BU/P1 12483/3 EN · April 2024