


K21-P



Ordering dimensions in **blue**

Surface roughness	$R_{t\max}$	R_a
	µm	

Sliding surface ≤ 2,5 0,05–0,2

Bottom of groove ≤ 6,3 ≤ 1,6

Groove face ≤ 15 ≤ 3

Bearing area: 50–95% and a cutting depth of 0,5 R_z based on $C_{ref} = 0\%$

D H9 over	d h10 incl.	Standard dimensions			$R_{t\max}$	c	Maximal radial extrusion gap			
		L + 0,2		s*			20 bar	100 bar	200 bar	400 bar
mm										mm
13	25	D – 8	6,0	0,4	3,5	0,33	0,18	0,11	0,05	
25	50	D – 10	7,0	0,4	4,0	0,37	0,22	0,16	0,10	
50	75	D – 12	8,0	0,4	4,5	0,42	0,27	0,20	0,14	
75	150	D – 15	10,0	0,4	5,0	0,46	0,31	0,25	0,19	
150	300	D – 20	12,0	0,4	6,0	0,54	0,39	0,32	0,26	
300	500	D – 25	18,0	0,4	8,5	0,61	0,46	0,39	0,33	
500	600	D – 30	20,0	0,4	10,0	0,67	0,52	0,45	0,39	

* Extrusion gap values shown above are valid for a temperature of 70 °C, higher temperatures require lower values.

Ordering example

Profile

D x d x L [mm]

Sealing material / Energizer

Piston seal K21-P

100 x 85 x 10

ECOPUR / NBR 70

Operating parameters

Material Seal	Energizer	Temperature		Speed ¹⁾	Pressure ²⁾
		from	to	max	max
		°C		m/s	bar (MPa)
■ ECOPUR	NBR 70	-30	+100	0,5	400 (40)
■ H-ECOPUR	NBR 70	-20	+100	0,5	400 (40)
■ S-ECOPUR	NBR 70	-20	+100	0,5	400 (40)
■ T-ECOPUR	MVQ 70	-50	+100	0,5	400 (40)

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

1) Surface speed limit values are valid only in the presence of a lubrication film.

2) Pressure ratings depend on the size of the extrusion gap.