


# S06-R



Ordering dimensions in **blue**

Surface roughness	$R_{tmax}$	$R_a$
	μm	
<b>Sliding surface</b>	≤ 2,5	0,05–0,3
<b>Bottom of groove</b>	≤ 6,3	≤ 1,6
<b>Groove face</b>	≤ 15	≤ 3

Bearing area: 50–95% and a cutting depth of 0,5  $R_z$  based on  $C_{ref} = 0\%$

Standard dimensions						Maximal radial extrusion gap		
d	f8	D	L	$R_{max}$	c	$s^*$		
over	incl.	H10	+ 0,2			20 bar	100 bar	160 bar
mm						mm		
<b>6</b>	<b>25</b>	d + 8	6,3	0,4	3,5	0,23	0,16	0,14
<b>25</b>	<b>50</b>	d + 10	8,0	0,4	4,0	0,26	0,19	0,17
<b>50</b>	<b>150</b>	d + 15	10,0	0,4	5,0	0,31	0,24	0,22
<b>150</b>	<b>300</b>	d + 20	14,0	0,4	6,0	0,34	0,27	0,25
<b>300</b>	<b>500</b>	d + 25	17,0	0,4	8,5	0,37	0,30	0,29
<b>500</b>	<b>700</b>	d + 30	25,0	0,4	10,0	0,40	0,34	0,32
<b>700</b>		d + 40	32,0	0,4	13,0	0,40	0,34	0,32

\* Extrusion gap values shown above are valid for a temperature of 70 °C, higher temperatures require lower values.

## Ordering example

Profile  
d x D x L [mm]  
Sealing material

Rod seal S06-R  
100 x 115 x 10  
SKF Ecorubber-1

## Operating parameters

Material Seal	Temperature		Speed <sup>1)</sup>	Pressure <sup>2)</sup>
	from	to	max	max
	°C		m/s	bar (MPa)
■ SKF Ecorubber-1	-30	+100	0,5	160 (16)
■ SKF Ecorubber-H	-25	+150	0,5	160 (16)
■ SKF Ecorubber-2	-20	+200	0,5	160 (16)
■ SKF Ecorubber-3	-50	+150	0,5	160 (16)
■ SKF Ecoflas	-10	+200	0,5	160 (16)
■ SKF Ecosil <sup>3)</sup>	-60	+200	–	–

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

<sup>1)</sup> Surface speed limit values are valid only in the presence of a lubrication film.

<sup>2)</sup> Pressure ratings depend on the size of the extrusion gap.

<sup>3)</sup> Only recommended for static or quasi-static applications.