

Safety Data Sheet

LGHC 2

SECTION 1: Identification

1.1. Product identifier used on the label

Trade name: LGHC 2

1.2. Recommended use of the chemical and restrictions on use

Recommended uses: Lubricant.

Inadvisable uses: None.

1.3. Details of the supplier of the safety data sheet

Supplier

Company: SKF USA Inc.
Address: 890 Forty Foot Road
Zip code: 19446
City: Lansdale, PA
Country: UNITED STATES OF AMERICA
Email: Mapro.Repair.USA@skf.com
Phone: +1 888-753-3477
Homepage: www.skf.com

Manufacturer

Company: SKF MPT
Address: Meidoornkade 14
Zip code: 3992 AE
City: AE Houten
Country: NETHERLANDS (KINGDOM OF THE)
Email: support.mpt@skf.com
Phone: +31 30 6307200
Homepage: www.skf.com

1.4. Emergency phone number

+31 30 6307200

For Chemical Emergency
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
1 703-527-3887 (collect calls accepted)

Location:
CHEMTREC
2900 Fairview Park Drive
Falls Church VA 22042-4513
USA

SECTION 2: Hazard Identification

Safety Data Sheet

LGHC 2

2.1. Classification of the chemical in accordance with paragraph (d) of §1910.1200

HazCom classification: The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures..

Most serious harmful effects: May cause slight irritation to the skin and eyes.

2.2. Label elements

The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures..

2.3. Other hazards which do not result in classification

None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Substance	CAS No	Concentration	Notes
Calcium dodecylbenzenesulphonate	26264-06-2	< 2.5 %	

Ingredient comments: The mineral oils in the product contain <3% DMSO extract(IP 346).

The specific chemical identity and/or exact percentage of composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation: Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion: Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

Skin contact: Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

Eye contact: Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

General: Bring the safety data sheet or label when seeking medical advice.

4.2. Most important symptoms/effects, acute and delayed.

May cause slight irritation to the skin and eyes.

4.3. Indication of immediate medical attention and special treatment needed, if necessary.

Treat symptoms. No special immediate treatment required.

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media.

Suitable extinguishing media: Extinguish with powder, foam or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media: Do not use a jet of water, as it may spread the fire.

Safety Data Sheet

LGHC 2

5.2. Specific hazards arising from the chemical

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

5.3. Special protective equipment and precautions for fire-fighters.

If there is a risk of exposure to vapour and flue gases, a self-contained breathing apparatus must be worn.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Stay upwind/keep distance from source. Wear gloves. Wear safety goggles if there is a risk of eye splash. Provide good ventilation.

For emergency responders: In addition to the above: Normal protective clothing is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spills using sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely out of reach of children and not together with food, feed, medicine and the like. Keep in tightly closed original packaging. Store in a cool, dry place. Do not store with the following: Strong oxidizers.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit

Substance name	Time period	ppm	mg/m ³	fiber/cm ³	Remarks	Notations

Safety Data Sheet

LGHC 2

Mineral oil, excluding metal working fluids	ACGIH TWA		5		Pure, highly and severely refined. OEL value for: Mineral oil, excluding metal working fluids	A4, I
Mineral oil, excluding metal working fluids	OSHA		5		OEL value for: Mineral oil, excluding metal working fluids	

A4 = Not Classifiable as a Human Carcinogen.

I = Inhalable fraktion.

Measuring methods: Compliance with occupational exposure limits may be checked by occupational hygiene measurements according to NIOSH/OSHA.

Legal basis: ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2025. OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006.

8.2. Exposure controls

Appropriate engineering controls: Wear the personal protective equipment specified below. Use the product under well-ventilated conditions, preferably outdoors.

Personal protective equipment, eyeface protection: Wear safety goggles if there is a risk of eye splash.

Personal protective equipment, hand protection: Plastic or rubber gloves recommended.

Personal protective equipment, respiratory protection: Not required.

Environmental exposure controls: Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter	Value/unit
physical state	Paste / Gel.
Color	Beige
Odour	No data
Solubility	Insoluble in the following: Water.

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	
Initial boiling point and boiling range	No data	
Flammability (solid, gas)	No data	
Upper/lower flammability limits	No data	
Explosion limits	No data	
Flash Point	150 °C	(302 °F)
Auto-ignition temperature	No data	
Decomposition temperature:	No data	

Safety Data Sheet

LGHC 2

pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	> 20.5 mm ² /s	(104 °F)
Viscosity	No data	
Partition coefficient n-octanol/water	No data	
Vapour pressure	No data	
Density	< 1000 kg/m ³	(77 °F)
Relative density	No data	
Relative vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

9.2. Other information

Parameter	Value/unit	Remarks
Explosive properties		Non-explosive

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Strong oxidizers.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Do not expose to heat (e.g. sunlight).

10.5. Incompatible materials

Strong oxidizers.

10.6. Hazardous decomposition products

None, if stored at the recommended storage conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

LGHC 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		10119.40 mg/kg		Calculated	

Calcium dodecylbenzenesulphonate, cas-no 26264-06-2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		4445 mg/kg			

Safety Data Sheet

LGHC 2

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. Ingestion may cause discomfort.

Acute toxicity - dermal

LGHC 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		4040.60 mg/kg		Calculated	

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - inhalation: The product does not have to be classified. Test data are not available.

Skin corrosion/irritation: The product does not have to be classified. Test data are not available. May cause slight irritation.

Serious eye damage/eye irritation: The product does not have to be classified. Test data are not available. Temporary irritation.

Respiratory sensitization or skin sensitization: The product does not have to be classified. Test data are not available.

Germ cell mutagenicity: The product does not have to be classified. Test data are not available.

Carcinogenic properties: The product does not have to be classified. Test data are not available. This product does not contain any carcinogens or potential carcinogens at reportable quantities as listed by OSHA, IARC or NTP.

Reproductive toxicity: The product does not have to be classified. Test data are not available.

Single STOT exposure: The product does not have to be classified. Test data are not available.

Repeated STOT exposure: The product does not have to be classified. Test data are not available.

Aspiration hazard: The product does not have to be classified. Test data are not available.

11.2. Information on other hazards

Endocrine disrupting properties: None known.

Other toxicological effects: None known.

SECTION 12: Ecological information

12.1. Ecotoxicity

Calcium dodecylbenzenesulphonate, cas-no 26264-06-2

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Oncorhynchus mykiss		96hLC50	10.8 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Safety Data Sheet

LGHC 2

12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

12.3. Bioaccumulative potential

No bioaccumulation expected. Test data are not available.

12.4. Mobility in soil

Not expected to be mobile in soil. Test data are not available.

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14: Transport information

14.1. UN number: Not applicable.

14.2. UN proper shipping name: Not applicable.

14.3. Transport hazard class(es): Not applicable.

14.4. Packing group: Not applicable.

14.5. Environmental hazards: Not applicable.

14.6. Special precautions which a user needs to be aware of, or needs to comply with, in connection with transport or conveyance either within or outside their premises.

None.

14.7. Transport in bulk (according to IMO instruments)

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations specific for the product in question

Special Provisions: None.

Safety Data Sheet

LGHC 2

Proposition 65

Chemicals known to cause cancer: None of the substances in the formulation is listed in the latest version publicly available.

Chemicals known to cause reproductive toxicity: None of the substances in the formulation is listed in the latest version publicly available.

TSCA: All substances in the formulation are listed in the latest version publicly available.

NFPA ratings

Health hazard: 0

Flammability: 1

Instability: 0

15.2. Chemical Safety Assessment

Substance name
Calcium dodecylbenzenesulphonate

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
6.0.0	3/24/2025	SRU	1,2,3,4,5,6,7,8,9,10,11,13,15,16

Abbreviations:
 PBT: Persistent, Bioaccumulative and Toxic
 vPvB: Very Persistent and Very Bioaccumulative
 STOT: Specific Target Organ Toxicity

Other Information: This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with CFR29, §1910.1200.

Training advice: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Issued: 7/31/2019

Revision date: 3/24/2025

Replaces date: 9/11/2023

Classification method: Calculation based on the hazards of the known components. Test data.

Country: US