


# S07-F

Ordering dimensions in **blue**

Surface roughness $R_{t\max}$	$R_a$
µm	

**Sliding surface** ≤ 2 0,05–0,2**Bottom of groove** ≤ 6,3 ≤ 1,6**Groove face** ≤ 15 ≤ 3Bearing area: 50–95% and a cutting depth of 0,5  $R_z$  based on  $C_{ref} = 0\%$ 

d f8 over	D H10 incl.	L + 0,2	$R_{t\max}$	c	Maximal radial extrusion gap			
					s*	20 bar	100 bar	200 bar
mm								
5	25	d + 8	6,3	0,4	3,5	0,40	0,20	0,15
25	50	d + 10	8,0	0,4	4,0	0,45	0,22	0,17
50	150	d + 15	10,0	0,4	5,0	0,75	0,40	0,33
150	300	d + 20	14,0	0,4	6,0	0,87	0,48	0,38
300	500	d + 25	17,0	0,4	8,5	0,87	0,48	0,38
500	600	d + 30	25,0	0,4	10,0	0,87	0,48	0,38
mm								

\* Extrusion gap values shown above are valid for a temperature of 70 °C, higher temperatures require lower values.

**Ordering example**

Profile

d x D x L [mm]

Sealing material / Energizer

**Rod seal S07-F**

100 x 115 x 10

SKF Ecoflon 3 / FPM 75

### Operating parameters

Material Seal	Energizer	Temperature		Speed <sup>1)</sup>	Pressure <sup>2)</sup>
		from	to	max	max
		°C		m/s	bar (MPa)
SKF Ecoflon 1	NBR 70	-30	+100	1,0	200 (20)
SKF Ecoflon 1	MVQ 70	-55	+200	1,0	200 (20)
SKF Ecoflon 2	NBR 70	-30	+100	1,0	400 (40)
SKF Ecoflon 2	FPM 75	-20	+200	1,0	400 (40)
SKF Ecoflon 2	EPDM 70	-50	+150	1,0	400 (40)
SKF Ecoflon 2	MVQ 70	-55	+200	1,0	400 (40)
SKF Ecoflon 3	NBR 70	-30	+100	1,0	400 (40)
SKF Ecoflon 3	FPM 75	-20	+200	1,0	400 (40)
SKF Ecoflon 3	EPDM 70	-50	+150	1,0	400 (40)
SKF Ecoflon 3	MVQ 70	-55	+200	1,0	400 (40)
SKF Ecoflon 4	NBR 70	-30	+100	1,0	400 (40)
SKF Ecoflon 4	FPM 75	-20	+200	1,0	400 (40)
SKF Ecoflon 4	EPDM 70	-50	+150	1,0	400 (40)
SKF Ecoflon 4	MVQ 70	-55	+200	1,0	400 (40)
SKF Ecowear	NBR 70	-30	+90	0,5	200 (20)
SKF Ecowear	MVQ 70	-55	+90	0,5	200 (20)

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

<sup>1)</sup> Surface speed limit values are valid only in the presence of a lubrication film.

<sup>2)</sup> Pressure ratings depend on the size of the extrusion gap.