

## Safety Data Sheet

LFFM 100

### SECTION 1: Identification

#### 1.1. Product identifier

Trade name: LFFM 100

#### 1.2. Recommended use and restrictions on use

Recommended uses: Lubricant.

Inadvisable uses: None.

#### 1.3. Initial supplier identifier

##### Supplier

Company: SKF Canada limited  
Address: 40 Executive Court, , ON,  
Zip code: M1S 4N4  
City: Toronto  
Country: CANADA  
Email: christian.urday@skf.com  
Phone: 416-892-5569

##### Manufacturer

Company: SKF MPT  
Address: Meidoornkade 14  
Zip code: 3992 AE  
City: AE Houten  
Country: NETHERLANDS (KINGDOM OF THE)  
Email: support.mpt@skf.com  
Phone: +31 30 6307200  
Homepage: www.skf.com

#### 1.4. Emergency telephone number

+31 30 6307200

For Chemical Emergency  
Spill, Leak, Fire, Exposure, or Accident  
Call CHEMTREC Day or Night  
Within USA and Canada: 1-800-424-9300  
1 703-527-3887 (collect calls accepted)

Location:  
CHEMTREC  
2900 Fairview Park Drive  
Falls Church VA 22042-4513  
USA

### SECTION 2: Hazard identification

#### 2.1. Classification of the substance or mixture

# Safety Data Sheet

## LFFM 100

**HPR classification:** The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures..

**Most serious harmful effects:** May cause slight irritation to the skin and eyes.

### 2.2. Label elements

The product shall not be classified as hazardous according to the classification and labeling rules for substances and mixtures..

### 2.3. Other hazards known to the supplier

None known.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

Contains no substances subject to reporting requirements.

**Ingredient comments:** The mineral oils in the product contain <3% DMSO extract(IP 346).

## SECTION 4: First-aid measures

### 4.1. Description of necessary first-aid measures

**Inhalation:** Seek fresh air. Seek medical advice in case of persistent discomfort.

**Ingestion:** Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

**Skin contact:** Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

**Eye contact:** Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

**General:** When obtaining medical advice, show the safety data sheet or label.

### 4.2. Most important symptoms and effects, whether acute or delayed

May cause slight irritation to the skin and eyes.

### 4.3. Indication of immediate medical attention and special treatment needed, if necessary

Treat symptoms. No special immediate treatment required.

## SECTION 5: Fire-fighting measures

### 5.1.Suitable and unsuitable extinguishing media

**Suitable extinguishing media:** The product is not directly flammable. Choose extinguishing agents based on the surrounding fire.

**Unsuitable extinguishing media:** Do not use water stream, as it may spread the fire.

### 5.2. Specific hazards arising from the hazardous product

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

### 5.3. Special protective equipment and precautions for fire-fighters

## Safety Data Sheet

### LFFM 100

If there is a risk of exposure to vapour and flue gases, a self-contained breathing apparatus must be worn.

#### SECTION 6: Accidental release measures

##### 6.1. Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel:** Keep unnecessary personnel away. Stay upwind/keep distance from source. Stop leak if this can be done without risk. Wear safety goggles if there is a risk of eye splash.

**For emergency responders:** In addition to the above: Normal protective clothing is recommended.

##### 6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

##### 6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

##### 6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

#### SECTION 7: Handling and storage

##### 7.1. Precautions for safe handling

Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

##### 7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely out of reach of children and not together with food, feed, medicine and the like. Keep in tightly closed original packaging. Store in a dry area. Store at temperatures below 45°C. Do not store with the following: Strong oxidizers.

##### 7.3. Specific end use(s)

None.

#### SECTION 8: Exposure controls/personal protection

##### 8.1. Control parameters

###### Occupational exposure limit

Substance name	Time period	ppm	mg/m <sup>3</sup>	fiber/cm <sup>3</sup>	Remarks	Notations
Mineral oil, excluding metal working fluids	OSHA		5		Oil mist, mineral oil	
Mineral oil, excluding metal working fluids	ACGIH TWA		5		Pure, highly and severely refined	A4, I

A4 = Not Classifiable as a Human Carcinogen.

I = Inhalable fraktion.

# Safety Data Sheet

## LFFM 100

<b>Measuring methods:</b>	Compliance with occupational exposure limits may be checked by occupational hygiene measurements.
<b>Legal basis:</b>	ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2025. OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006. There might be additional exposure limits due to regional and local laws and regulations. Local regulations may be more stringent than regional or national requirements.

### 8.2. Exposure controls

<b>Appropriate engineering controls:</b>	Wear the personal protective equipment specified below. Use the product under well-ventilated conditions.
<b>Personal protective equipment, eye/face protection:</b>	Wear safety goggles if there is a risk of eye splash.
<b>Personal protective equipment, hand protection:</b>	Plastic or rubber gloves recommended.
<b>Personal protective equipment, respiratory protection:</b>	Not required.  In case of risk of formation of spray mist, wear respiratory protective equipment with P2 filter.
<b>Environmental exposure controls:</b>	Ensure compliance with local regulations for emissions.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Parameter	Value/unit	
physical state	Liquid	
Color	Colourless	
Odour	No data	
Solubility	Not miscible with the following: Water.	

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	
Initial boiling point and boiling range	No data	
flammability, in the case of solids and gases	No data	
upper and lower flammability limits	No data	
Explosion limits	No data	
Flash Point	> 150 °C	
Auto-ignition temperature	No data	
Decomposition temperature:	No data	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	100 mm <sup>2</sup> /s	(40 °C)
Viscosity	No data	
partition coefficient — n-octanol/water	No data	
Vapour pressure	No data	
Density	< 1000 kg/m <sup>3</sup>	(25 °C)

## Safety Data Sheet

### LFFM 100

Relative density	No data	
Relative vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

#### 9.2. Other information

Parameter	Value/unit	Remarks
Explosive properties		Non-explosive

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

Reacts with the following: Strong oxidizers.

#### 10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

#### 10.3. Possibility of hazardous reactions

None known.

#### 10.4. Conditions to avoid

Avoid temperatures >45°C.

#### 10.5. Incompatible materials

Strong oxidizers.

#### 10.6. Hazardous decomposition products

None, if stored at the recommended storage conditions.

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

##### Acute toxicity - oral

##### LFFM 100

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE (mix)		5053.30 mg/kg			

Ingestion may cause discomfort. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

##### Acute toxicity - dermal

##### LFFM 100

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE (mix)		5135.40 mg/kg			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

**Acute toxicity - inhalation:** The product does not have to be classified. Test data are not available.

## Safety Data Sheet

### LFFM 100

<b>Skin corrosion/irritation:</b>	May cause slight irritation. The product does not have to be classified. Test data are not available.
<b>Serious eye damage/eye irritation:</b>	Temporary irritation. The product does not have to be classified. Test data are not available.
<b>Respiratory sensitization or skin sensitization:</b>	The product does not have to be classified. Test data are not available.
<b>Germ cell mutagenicity:</b>	The product does not have to be classified. Test data are not available.
<b>Carcinogenic properties:</b>	The product does not have to be classified. Test data are not available.
<b>Reproductive toxicity:</b>	The product does not have to be classified. Test data are not available.
<b>Single STOT exposure:</b>	The product does not have to be classified. Test data are not available.
<b>Repeated STOT exposure:</b>	The product does not have to be classified. Test data are not available.
<b>Aspiration hazard:</b>	The product does not have to be classified. Test data are not available.

#### 11.2. Information on other hazards

<b>Endocrine disrupting properties:</b>	None known.
<b>Other toxicological effects:</b>	None known.

### SECTION 12: Ecological information

#### 12.1. Ecotoxicity

The product does not have to be classified. Test data are not available.

#### 12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

#### 12.3. Bioaccumulative potential

No bioaccumulation expected. Test data are not available.

#### 12.4. Mobility in soil

Test data are not available.

#### 12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

#### 12.6. Endocrine disrupting properties

None known.

#### 12.7. Other adverse effects

None known.

German water pollution classification (WGK): 1

# Safety Data Sheet

LFFM 100

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

## SECTION 14: Transport information

**14.1. UN number:** Not applicable.

**14.2. United Nations proper shipping name:** Not applicable.

**14.3. Transport hazard class:** Not applicable.

**14.4. Packing group:** Not applicable.

**14.5. Environmental hazards:** Not applicable.

### 14.6. Special precautions for user

None.

**14.7. Transport in bulk (according to Annex II of the International Convention for the Prevention of Pollution From Ships, 1973, as modified by the Protocol of 1978 (MARPOL 73/78), and the International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk (IBC Code))**

Not applicable.

**Other Information:** The product is not covered by the rules for transport of dangerous goods.

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations, made within or outside Canada, specific to the product in question**

**Special Provisions:** None.

### 15.2. Chemical Safety Assessment

**Other Information:** Chemical safety assessment has not been performed.

## SECTION 16: Other information

### Version history and indication of changes

Version	Revision date	Responsible	Changes
1.3.0	2025-03-03	SRU	1,5,7,8,13,16

**Abbreviations:**  
 PBT: Persistent, Bioaccumulative and Toxic  
 vPvB: Very Persistent and Very Bioaccumulative  
 STOT: Specific Target Organ Toxicity

**Other Information:** This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with Hazardous Products Regulations as subsequently changed.

## Safety Data Sheet

### LFFM 100

<b>Training advice:</b>	A thorough knowledge of this safety data sheet should be a prerequisite condition.
<b>Issued:</b>	2020-08-04
<b>Revision date:</b>	2025-03-03
<b>Replaces date:</b>	2023-04-13
<b>Classification method:</b>	Calculation based on the hazards of the known components.
<b>Country:</b>	CA