

Safety Data Sheet

LGEP 1

SECTION 1: Identification

1.1. Product identifier

Trade name: LGEP 1

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant.

1.3. Details of the supplier of the safety data sheet

Supplier

Company: SKF USA Inc.
Address: 890 Forty Foot Road
Zip code: 19446
City: Lansdale, PA
Country: UNITED STATES OF AMERICA
E-mail: Mapro.Repair.USA@skf.com
Phone: +1 888-753-3477
Homepage: www.skf.com

Manufacturer

Company: SKF MPT
Address: Meidoornkade 14
Zip code: 3992 AE
City: AE Houten
Country: NETHERLANDS
E-mail: support.mpt@skf.com
Phone: +31 30 6307200
Homepage: www.skf.com

1.4. Emergency Telephone Number

+31 30 6307200

For Chemical Emergency
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
1 703-527-3887 (collect calls accepted)

Location:
CHEMTREC
2900 Fairview Park Drive
Falls Church VA 22042-4513
USA

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

Safety Data Sheet

LGEP 1

HazCom classification: Skin sensitization, Category 1;H317

Most serious harmful effects: May cause an allergic skin reaction.

2.2. Label elements

Pictograms



Signal word: Warning

Contains

Substance: Naphthenic acids, zinc salts; Dipentylammonium dipentylthiocarbamate;

Hazard Statements

May cause an allergic skin reaction.

Precautionary statements

Wear protective gloves.

2.3. Other hazards

None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Substance	CAS No./ EC No./ REACH Reg. No.	Concentration	Notes
Naphthenic acids, zinc salts	12001-85-3 234-409-2	1 -< 2.5 %	
Dipentylammonium dipentylthiocarbamate	71902-20-0 276-172-8 01-2120793078-43	0.1 -< 0.25 %	
zinc oxide	1314-13-2 215-222-5 01-2119463881	0 -< 0.25 %	

Ingredient comments: The mineral oils in the product contain <3% DMSO extract(IP 346).

The specific chemical identity and/or exact percentage of composition has been withheld as a trade secret.

SECTION 4: First-aid measures

4.1. Description of first aid measures

Inhalation: Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion: Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

Skin contact: Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

Safety Data Sheet

LGEP 1

Eye contact: Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

General: Bring the safety data sheet or label when seeking medical advice.

4.2. Most important symptoms and effects, both acute and delayed

May cause sensitization by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Fire-fighting measures

5.1. Extinguishing media

Suitable extinguishing media: Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media: Do not use a jet of water, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. The product decomposes when combusted and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Nitrous gases/ Sulphur oxides/ Aldehydes.

5.3. Advice for firefighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapor and smoke gases - seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Stay upwind/keep distance from source. Wear safety goggles if there is a risk of eye splash. Wear gloves. Provide good ventilation.

For emergency responders: In addition to the above: Protective suit is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spills using sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

Safety Data Sheet

LGEP 1

7.1. Precautions for safe handling

The product should be used under well-ventilated conditions and preferably under process ventilation. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

Store safely, out of reach of children and away from food, animal feeding stuffs, drugs, etc. Keep in tightly closed original packaging. Store in a cool, dry place. Do not store with the following: Oxidizers/ Acids. Storage temperature: 32 - 104 °F. Do not expose to heat (e.g. sunlight).

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit

Substance name	Time period	ppm	mg/m ³	fiber/cm ³	Remarks	Notations
zinc oxide	ACGIH STEL		10			R
zinc oxide	OSHA		5		Fume.	
zinc oxide	OSHA		15		Total dust	
zinc oxide	OSHA		5		Respirable fraction.	R
zinc oxide	ACGIH TWA		2			
Mineral oil, excluding metal working fluids	ACGIH TWA		5		Pure, highly and severely refined. OEL value for: Mineral oil, excluding metal working fluids	A4, I
Mineral oil, excluding metal working fluids	OSHA		5		OEL value for: Mineral oil, excluding metal working fluids	

A4 = Not Classifiable as a Human Carcinogen.

R = Respirable fraction.

I = Inhalable fraktion.

Measuring methods:

Compliance with occupational exposure limits may be checked by occupational hygiene measurements.

Legal basis:

ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2022. OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006.

8.2. Exposure controls

Appropriate engineering controls:

Wear the personal protective equipment specified below.

Personal protective equipment, eye/face protection:

Wear safety goggles if there is a risk of eye splash.

Personal protective equipment, hand protection:

Wear gloves. Type of material and thickness: Nitrile rubber/ 0,4 mm. Penetration time: 4 hours.
The suitability and durability of a glove is dependant on usage, e.g. frequency and duration

Safety Data Sheet

LGEP 1

of contact, glove material thickness, functionality and chemical resistance. Always seek advice from the glove supplier.

Personal protective equipment, respiratory protection: Not required.

In case of risk of formation of spray mist, wear respiratory protective equipment with P2 filter.

Environmental exposure controls: Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter	Value/unit
physical state	Paste
Color	Yellow
Odour	Characteristic
Solubility	Insoluble in the following: Water.

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	> 170 °C	> 338 °F (1013 hPa)
Freezing point	No data	
Initial boiling point and boiling range	> 250 °C	> 482 °F (1013 hPa)
Flammability (solid, gas)	No data	
Upper/lower flammability limits	No data	
Explosion limits	No data	
Flash Point	> 200 °C	> 392 °F
Auto-ignition temperature	No data	
Decomposition temperature	No data	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	No data	
Viscosity	No data	
Partition coefficient n-octanol/water	No data	
Vapour pressure	No data	
Density	~ 0.93 g/cm ³	(68 °F)
Relative density	No data	
Vapor density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

9.2. Other information

Parameter	Value/unit	Remarks
Oxidizing properties		Non-oxidizing.
VOC (Volatile organic compounds):	<3 w/w %	

SECTION 10: Stability and reactivity

10.1. Reactivity

Safety Data Sheet

LGEP 1

Reacts with the following: Oxidizers/ Acids.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid heating and contact with ignition sources. Avoid direct sunlight.

10.5. Incompatible materials

Oxidizers/ Acids.

10.6. Hazardous decomposition products

The product decomposes when combusted or heated to high temperatures and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Nitrous gases/ Sulphur oxides/ Aldehydes.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

zinc oxide, cas-no 1314-13-2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		7950 - 10000 mg/kg			

Ingestion may cause discomfort. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - dermal

zinc oxide, cas-no 1314-13-2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 2000 mg/kg			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - inhalation

zinc oxide, cas-no 1314-13-2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LC50	4 h	> 5700 mg/m ³			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Skin corrosion/irritation:

May cause slight irritation. The product does not have to be classified. Test data are not available.

Serious eye damage/eye irritation:

Temporary irritation. The product does not have to be classified. Test data are not available.

Safety Data Sheet

LGEP 1

Respiratory sensitization or skin sensitization:	May cause sensitization by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available. This product does not contain any carcinogens or potential carcinogens at reportable quantities as listed by OSHA, IARC or NTP.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.

11.2. Information on other hazards

Endocrine disrupting properties: None known.

Other toxicological effects: None known.

SECTION 12: Ecological information

12.1. Toxicity

LGEP 1

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Brachydanio rerio		96hLC50	> 100 mg/l			
Crustacea	Daphnia magna		48hEC50	> 100 mg/l			
Algae	Desmodesmus subspicatus		72hEC50	> 100 mg/l			
Algae	Desmodesmus subspicatus		72hNOEC	> 100 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

12.2. Persistence and degradability

Test data are not available.

12.3. Bioaccumulative potential

Test data are not available.

12.4. Mobility in soil

Test data are not available.

12.5. Results of PBT and vPvB assessment

Safety Data Sheet

LGEP 1

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Empty, cleansed packaging should be disposed of for recycling. Uncleansed packaging is to be disposed of via the local waste-removal scheme.

SECTION 14: Transport information

14.1. UN number or ID number: Not applicable.

14.4. Packing group: Not applicable.

14.2. UN proper shipping name: Not applicable.

14.5. Environmental hazards: Not applicable.

14.3. Transport hazard class(es): Not applicable.

14.6. Special precautions for user

None.

14.7. Maritime transport in bulk according to IMO instruments

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Proposition 65

Chemicals known to cause cancer: None of the substances in the formulation is listed in the latest version publicly available.

Chemicals known to cause reproductive toxicity: None of the substances in the formulation is listed in the latest version publicly available.

TSCA: All substances in the formulation are listed in the latest version publicly available.

NFPA ratings

Health hazard: 2

Flammability: 1

Instability: 0

15.2. Chemical Safety Assessment

Safety Data Sheet

LGEP 1

Substance name
zinc oxide
Dipentylammonium dipentylidithiocarbamate

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
1.1.0	8/23/2022	Bureau Veritas HSE/ SRU	1, 3, 7-9, 11-12, 15-16

Abbreviations:
 PBT: Persistent, Bioaccumulative and Toxic
 vPvB: Very Persistent and Very Bioaccumulative
 STOT: Specific Target Organ Toxicity

Other Information: This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with CFR29, §1910.1200.

Training advice: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Issued: 1/12/2021

Revision date: 8/23/2022

Replaces date: 1/12/2021

Classification method: Calculation based on the hazards of the known components.
 Test data.

Country: US