

	Safety Data She	et
	LGFG 2	
Replaces date: 24/08/2022		Revision date: 02/10/2023 Version: 1.2.0
SECTION 1: Identificat	tion of the substance/mixture and of	the company/undertaking
1.1. Product identifier		
Trade name:	LGFG 2	
1.2. Relevant identified u	uses of the substance or mixture and us	es advised against
Recommended uses:	Lubricant.	
1.3. Details of the suppli	er of the safety data sheet	
Supplier		
Company:	SKF MPT	
Address:	Meidoornkade 14	
Zip code:	3992 AE	

City:	AE Houten
Country:	NETHERLANDS (KINGDOM OF THE)
E-mail:	support.mpt@skf.com
Phone:	+31 30 6307200
Homepage:	www.skf.com

1.4. Emergency Telephone Number

Members of the public: 111 (NHS 111 (Scotland: NHS 24)).

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

CLP-classification:	The product shall not be classified as hazardous according to the classification and labeling rules for substance and mixtures.
Most serious harmful effects:	May cause slight irritation to the skin and eyes.
2.2. Label elements	
Supplemental information	
EUH210	Safety data sheet available on request.
2.3. Other hazards	
The product does not contain an Endocrine disrupting properties:	

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Substance

CAS No./ EC No./ REACH Reg. No.

Concentration

Notes

CLP-classification



Revision date: 02/10/2023

Safety Data Sheet LGFG 2

Version				
Calcium dodecylbenzenesulphon ate	26264-06-2 247-557-8 01-2119560592-37	< 2.5 %	Skin Irrit. 2;H315 Eye Dam. 1;H318 Aquatic Chronic 3;H412 C ≥ 10.5%: Eye Dam. 1;H318	
Benzenamine, N- phenyl-, reaction products with 2,4,4- trimethylpentene	68411-46-1 270-128-1 01-2119491299-23	< 1 %	Repr. 2;H361f Aquatic Chronic 3;H412 LD50 (Acute toxicity - oral): > 5000 mg/kg bw LD50 (Acute toxicity - dermal): > 2000 mg/kg bw	
N-methyl-N- oleoylglycine	701-177-3 01-21194889 91-20	< 1 %	Skin Irrit. 2;H315 Eye Dam. 1;H318 Acute Tox. 4;H322 Aquatic Acute 1;H400 Aquatic Chronic 3;H412 M (chronic): 1	

Please see section 16 for the full text of H- / EUH-phrases.

Ingredient comments:

Replaces date: 24/08/2022

The mineral oils in the product contain <3% DMSO extract(IP 346).

SECTION 4: First aid measures

Inhalation:	Seek fresh air. Seek medical advice in case of persistent discomfort.
Ingestion:	Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.
Skin contact:	Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.
Eye contact:	Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.
General:	When obtaining medical advice, show the safety data sheet or label.

May cause slight irritation to the skin and eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

media:

Suitable extinguishing media:	Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.
Unsuitable extinguishing	Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

5.3. Advice for firefighters



LGFG 2

Replaces date: 24/08/2022

Revision date: 02/10/2023 Version: 1.2.0

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases - seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Wear safety goggles if there is a risk of eye splash. Wear gloves.

For emergency responders: In addition to the above: Normal protective clothing equivalent to EN 469 is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use the product under well-ventilated conditions. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Keep in tightly closed original packaging. Do not store with the following: Strong oxidisers. Storage temperature: <45 °C.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit:	Contains no substances subject to reporting requirements.
Measuring methods:	Compliance with occupational exposure limits may be checked by occupational hygiene measurements.
Legal basis:	EH40/2005 Workplace exposure limits. Last amended January 2020.
8.2. Exposure controls	
Appropriate engineering controls:	Wear the personal protective equipment specified below.
Personal protective equipment, eye/face protection:	Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 166.



LGFG 2

Replaces date: 24/08/2022

Revision date: 02/10/2023 Version: 1.2.0

Personal protective equipment, Plastic or rubber gloves recommended. **hand protection:**

Personal protective equipment, Not required. respiratory protection:

Environmental exposure Ensure compliance with local regulations for emissions. **controls:**

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter		Value/unit			
State	Paste Gel.				
Colour	Light brown	Light brown			
Odour	Characteristic				
Solubility	Insoluble in the following	g: Water.			
Parameter	Value/unit	Remarks			
Odour threshold	No data				
Melting point	No data				
Freezing point	No data				
Initial boiling point and boiling range	No data				
Flammability (solid, gas)	No data				
Flammability limits	No data				
Explosion limits	No data				
Flash Point	> 150 °C				
Auto-ignition temperature	No data				
Decomposition temperature	No data				
pH (solution for use)	No data				
pH (concentrate)	No data				
Kinematic viscosity	> 20.5 mm2/s	(40 °C)			
Viscosity	No data				
Partition coefficient n-octonol/water	No data				
Vapour pressure	No data				
Density	< 1000 kg/m³	(25 °C)			
Relative density	No data				
Vapour density	No data				
Relative density (sat. air)	No data				
Particle characteristics	No data				

9.2. Other information

Parameter	Value/unit	Remarks
Explosive properties		Non-explosive
VOC (Volatile organic compounds):	1,85 %	

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Strong oxidisers.



LGFG 2

Replaces date: 24/08/2022

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Do not expose to heat (e.g. sunlight).

10.5. Incompatible materials

Strong oxidisers.

10.6. Hazardous decomposition products

Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity - oral

LGFG 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		6324.60 mg/kg			

Calcium dodecylbenzenesulphonate, cas-no 26264-06-2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		1086 mg/kg			

Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene, cas-no 68411-46-1

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 5000 mg/kg bw			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. Ingestion of large quantities may cause discomfort.

Acute toxicity - dermal

LGFG 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		2784.20 mg/kg			
Benzenamine, N-phenyl-, reaction products with 2.4.4-trimethylpentene, cas-no 68411-46-1						

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 2000 mg/kg bw			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - inhalation: The product does not have to be classified. Test data are not available.

Skin corrosion/irritation: The product does not have to be classified. Test data are not available. May cause slight irritation.

Serious eye damage/eye The product does not have to be classified. Test data are not available. Temporary irritation. irritation:

Revision date: 02/10/2023 Version: 1.2.0



	Safaty Data Shaat
	Safety Data Sheet
	LGFG 2
Replaces date: 24/08/2022	Revision date: 02/10/2023 Version: 1.2.0
Respiratory sensitisation or skin sensitisation:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.
11.2. Information on other h	azards
Endocrine disrupting properties:	None known.
Other toxicological effects:	None known.

SECTION 12: Ecological information

12.1. Toxicity

Calcium dodecy	/lbenzenesulı	phonate.	cas-no	26264-06-2

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Oncorhynchus mykiss		96hLC50	10.8 mg/l			
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene, cas-no 68411-46-1							
Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Danio rerio		96hLC50	> 100 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

12.3. Bioaccumulative potential

No bioaccumulation expected. Test data are not available.

12.4. Mobility in soil

Expected to be mobile in soil. Test data are not available.

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects



LGFG 2

Replaces date: 24/08/2022

None known.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

Category of waste:

EWC code: Depends on line of business and use, for instance 13 08 99* wastes not otherwise specified

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

SECTION 14: Transport information

14.1. UN number or ID number: 14.2. UN proper shipping name:	Not applicable. Not applicable.	14.4. Packing group: 14.5. Environmental hazards:	Not applicable. Not applicable.
14.3. Transport hazard class(es):	Not applicable.		

14.6. Special precautions for user

None.

14.7. Maritime transport in bulk according to IMO instruments

None.

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special Provisions:

15.2. Chemical Safety Assessment

REACH Reg. No.	Substance name
01-21194889 91-20	N-methyl-N-oleoylglycine
01-2119491299-23	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene
01-2119560592-37	Calcium dodecylbenzenesulphonate

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
1.2.0	02/10/2023	Bureau Veritas HSE / DOL	3,11,16

Revision date: 02/10/2023 Version: 1.2.0



Safety Data Sheet				
	LGFG 2			
Replaces date: 24/08/2022	Revision date: 02/10/2023 Version: 1.2.0			
Abbreviations:	PBT: Persistent, Bioaccumulative and Toxic vPvB: Very Persistent and Very Bioaccumulative STOT: Specific Target Organ Toxicity			
Other Information:	This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with Regulation 1907/2006/EC "The Registration, Evaluation and Authorization of Chemicals" as amended by the stationary UK REACH etc. (EU Exit) as subsequently changed.			
Training advice:	A thorough knowledge of this safety data sheet should be a prerequisite condition.			
Classification method:	Calculation based on the hazards of the known components.			
Hazard statements				
H315	Causes skin irritation.			
H318	Causes serious eye damage.			
H332	Harmful if inhaled.			
H361f	Suspected of damaging fertility.			
H400	Very toxic to aquatic life.			
H412	Harmful to aquatic life with long lasting effects.			
Supplemental hazard information				
EUH210	Safety data sheet available on request.			
Country:	GB			