


SKF S2M Magnetic Bearings for combined heat and power generation plant

The challenge is the direct coupling of a 9 MW gas turbine to a high speed electric generator (6,090 r/min) connected to a frequency converter, suppressing the need of a gearbox and oil lubrication.

How to support this 10,000 kg, rigid, shaft line (turbine-generator)?

The SKF solution: 4 radial magnetic bearings, and a thrust magnetic bearing, controlled thanks to our know-how and experience in large turbomachinery applications.



View of a 400 mm diameter radial magnetic bearing

Advantage

- Oil-free and contact-free rotation
- High efficiency
- High reliability
- Optimized rotor dynamics
- Increased safety of the plant

Features

- Grid power: 9 MW
- Speed: 6 090 r/min
- Total rotor weight: 10 tons
- Total rotor length: 10 m



The gas turbine drives the electric generator and provides heat (hot water) in a cogeneration plant

© SKF is a registered trademark of the SKF Group.

© SKF Group 2015

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB M7/S9 15571 EN - March 2015

Certain image(s) used by courtesy of Energomash

