

SKF Lincoln Compact lubrication pump series CLP Basic / CLP Basic Plus

A new standard in lubrication performance

For use in small progressive lubrication systems in mobile and industrial applications







A new standard in lubrication performance

The new SKF Lincoln Compact lubrication pump series (CLP) is the first of the new SKF eLube generation. It works in small progressive lubrication systems.

The lightweight, simple and easy-to-use pump stands out with its compact design and reliable functionality in mobile and industrial applications. To fit the specific needs of the applications, several electrical and monitoring features have been tailored. All models of the Lincoln Compact lubrication pump (CLP) series are suitable for grease applications and come with a follower plate to support continuous grease flow. To refill the pumps easily, they are equipped with an easy-to-access standard grease nipple.



CLP Basic

CLP Basic Plus



The Lincoln Compact progressive pump (CLP) series has different monitoring options. CLP Basic Plus variants feature integrated empty-level monitoring that informs the user before the pump runs out of lubricant.

Both Basic and Basic Plus variants can be controlled via an external lubrication controller or the machine control system. Basic Plus variants for mobile use include a manual lubrication button to start an extra lubrication cycle. This helps to check the proper function of the system quickly.

The fill level can be visually monitored at each pump model. Basic Plus variants feature integrated empty-level monitoring that informs the user before the pump runs out of lubricant. Both Basic and Basic Plus variants can be controlled via an external lubrication controller or the machine control system.

Basic Plus variants for mobile use come with a manual lubrication button to start an extra lubrication cycle. This helps to quickly check proper function of the system.

Common main features

- Lubricant: greases NLGI 0 to 2
- 1-liter reservoir
- Filling from bottom by grease nipple
- Visual-level monitoring
- Follower plate
- Control via external lubrication controller or machine control system
- Pump element 6 mounted on the right side, providing a delivery volume of ~3 cm³/min

Features depending on model *:

- Power supply 12/24 V DC
- · Additional electrical empty-level monitoring
- Additional manual lubrication button
- Electrical connections on the left side:
 - Bayonet plug, 7 pole A coded (power, signal and manual lubrication)
 - Bayonet plug, 4 pole A coded (power supply)
 - Square plug, A coded (power supply)
- Electrical connection on the right side:
 - M12×1,4 pole A coded (signal output)

* Double check the description per model

Pre-defined models make ordering easy and improve lead time

The easiest and fastest way to order the new Compact lubrication pumps (CLP) is to choose a pre-defined package. By ordering a pre-defined, standard model, you get a fully equipped pump specifically configured for mobile or industrial use. These packages meet all standard requirements of these applications.



Comparison of model features						
	CLP Basic			CLP Basic Plus		
		NET				
Material number	CLP-EGXXX1- 0000020	CLP-EGXXX2- 0000020	CLP-XGXXX2- 0000022	CLP-EG1XY1- 0000021	CLP-EG1XY2- 0000021	CLP-XG1XX2- 0000023
Application Voltage Compliance	Mobile 12 V DC E1/CE	Mobile 24 V DC E1/CE	Industry 24 V DC CE	Mobile 12 V DC E1/CE	Mobile 24 V DC E1/CE	Industry 24 V DC CE
Visual level monitoring Electrical empty-level monitoring Manual lubrication button	• - -	• - -	• - -	•	•	• •
Electrical connection left Bayonet plug 4 pole A coded 7 pole A coded Square plug, A coded	• 1) _ _	• 1) _ _	- - • 1)	- • 1) 2) 4) -	- • 1) 2) 4) -	- - • 1)
Electrical connection right M12×1, 4 pole A coded	-	-	-	-	-	• 3)
Grease NLGI 0 to 2 Standard filling from front Follower plate Pump element 6 (right)	• • •	• • •	• • •	• • •	• • •	• • •

Power
 Signal input
 Signal output
 Manual lubrication

Technical data

Function principle	iple Electrically operated lubrication pump			
Max. working pressure Operating temperature Usable reservoir volume Number of pump elements Pump element ¹⁾ Lubricant output ²⁾ IP-protection class ³⁾ Corrosion class Voltages Operating current Relative duty cycle Electrical protection class Outlet connection	270 bar -25 to +65°C 11 max. 2 6 -3 cm ³ /min IP 6K9K C3 12 / 24 V DC up to 3 A (max. peak), nominal 1, 15% ED S3 30 minutes III G ¹ / ₄	3 916 psi -13 to +149°F 0.26 gal 2 A		
Mounting position	Upright			
Dimensions depending on model (m CLP Basic mobile CLP Basic industry CLP Basic Plus mobile CLP Basic Plus industry	nax. H×W×D 4)) 212×187×190 mm 212×187×190 mm 212×187×190 mm 235×187×190 mm	8.34×7.36×7.48 in 8.34×7.36×7.48 in 8.34×7.36×7.48 in 9.25×7.36×7.48 in		
Weight (empty)	5 kg	11 lb		

Pump element 6 is included in the standard packages (→page 4). Other pump elements can be ordered using the spare part / additional component list (→page 6/7)
 Lubricant output depending on pump element
 Protection class depending on electrical connection
 Depth with standard filling nippel

Spare parts / Additional components 1)

Pump elements ²⁾		Nominal	output			
		cm ³ /min	in³/min			
600-26875-2 600-26876-2 600-26877-2 655-28716-1	Pump element 5 Pump element 6 Pump element 7 Pump element R	1.90 3.04 4.18 0.7-3.3	0.12 0.19 0.26 0.04-0.2			
Adapters and closure screw ²⁾						
519-33840-1 519-33959-1 519-33955-1 519-60445-1	Adapter with lubrication fitting ST 1/4 NPTF Adapter with lubrication fitting A2 AR 1/4 Adapter with lubrication fitting ST AR 1/4 Closure screw M22x 1,5					
Pressure control valve						
270 864 624-77803-1 624-77802-1	SVTSV-270-R1/4-1/8NPTFI-NIP00R-A SVTSV-270-R1/4-6-NIP00L SVTSV-270-R1/4-6-NIP00R					
Power cables						
664-34167-9 664-34428-3 664-36078-7	Bayonet socket, 4 pole with Bayonet socket, 7 pole with Square socket with cable 10	cable 10 m cable 10 m) m (black)	1			
Others						
5590-00000002 5590-00000015 5590-00000014	Filling connection cartridge Mounting bracket kit Venting kit					
 The spare parts assemblies may be used exclusively for replacement of identical defective parts. Modifications with spare parts on existing products are not allowed. Exceptions to this are the pump elements and the optional filling connection. Gasket always included 						



For **accessories and spare parts,** please refer to the product catalogue "Progressive automatic lubrication systems"

 \rightarrow PUB LS/P1 16964 EN, page 16ff

skf.com/lubrication | skf.com/clp-basic

® SKF and Lincoln are registered trademarks of the SKF Group.

[™] eLube is a trademark of the SKF Group.

© SKF Group 2024 The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB LS/P2 18918 EN · January 2024

Certain image(s) used under license from Shutterstock.com.