

## E11/BT/P

The E11/BT/P seal is a rotary shaft seal with the sealing lips working at the outer diameter with an additional dust lip, sufficiently robust to keep contamination out of the sealing system and prevent damage of the main lip.



It is mostly used in wind energy, pulp and paper as well as aluminium industries. The seal also is applicable for any application, where corrosion, sizes and overall dimensions can cause issues for traditional metal case seals.

Designed for external sealing, the E11/BT/P seal has a flexible sealing lip made of elastomer and a back reinforced with high resistant textile rubber.

For windmill applications, the E11/BT/P features a half O-ring on the top of its back for a better static sealing performance.

A vulcanized finger spring provides a uniform distribution of pressure on the shaft exerted by the sealing lip.

All the inconveniences shown by garter spring seals are avoided, such as lip overturning, the spring popping out from its housing and consequent damages of bearing and shaft.

The E11/BT/P can cope with a maximum pressure of 1 bar.

Exclusive features of E11/BT/P seals are:

- Sealing function at the outer diameter
- Mechanical locking of seal due to a rubber button (integrated half O-ring)
- Increased sealing capability at the static seal area due to the rubber button
- Additional barrier against external contaminants due to additional dust lip
- Vulcanized finger spring
- Uniform distribution of the sealing lip pressure on the shaft
- Spring fixed in groove – therefore no inconveniences related to the spring coming out of its position e.g. during mounting

The E11/BT/P is also available as split version (E11/BT/P/SPLIT) enabling easier assembly (no pressure applicable) in applications, where it would be difficult or even impossible to use an endless design. Due to the sealing function at the outer diameter, please contact TENUTE Technical Department / SKF Seals Application Engineering to agree on the clamping situation as well as how to glue the seal connection.

Both solutions, E11/BT/P endless and E11/BT/P/SPLIT, require a retainer plate for a correct operation.

Possible size range for E11/BT/P seals:  $\text{ØD}_{\text{min}} = 55 \text{ mm}$ ;  $\text{Ød}_{\text{max}} = 2\,540 \text{ mm}$  (please also see the drawing at the next page).

## Materials

The standard material for the E11/BT/P is nitril elastomer NBR loaded with PTFE, but for particular working conditions the seals also are available in hydrogenated nitril elastomer (HNBR), fluorocarbon elastomer (FKM) or silicone elastomer (VMQ) materials. Other combinations are available on request.

Standard production		Special production on demand	
Lip	NBR	Lip	HNBR, FKM, EPDM, MVQ
Spring	AISI 301	Spring	AISI 301 – AISI 316

The table below shows working temperature ranges (minimum, maximum, peak (\*)) applicable to each type of compound as well as possible spring configurations.

Material	Temperature	
	min	max
	°C	°C (*)
<b>NBR</b>	-30	+100 (+120)
<b>HNBR</b>	-40	+150 (+175)
<b>VMQ</b>	-50	+200 (+250)
<b>FKM</b>	-20	+200 (+250)


## Assembly of E11/BT/P seals

The drawing shows the details of the housing dimensions and the assembly of the E11/BT/P seal.

Particular applications or requirements different from those details shall be agreed with the TENUTE Technical Department / SKF Seals Application Engineering.

$$C_{\text{maximum}} = 0,2 \times F$$

$$E_{\text{minimum}} = 0,3 \times F; E_{\text{maximum}} = 0,5 \times F$$



## Cylinder and housing diameter tolerance

Housing diameter Ød		Tolerance	Cylinder diameter ØD		Tolerance
Over	Up to		Over	Up to	
mm	mm		mm	mm	
55	1 600	h10	75	1 600	H11
1 600	2 480	h9	1 600	2 540	H10

## Housing height tolerance

Housing height H	Tolerance
mm	mm
Up to 15	+0 / -0,1
Over 15	+0,1 / -0,1

## Cylinder and housing chamfers

Housing diameter Ød		Housing chamfers		Cylinder diameter ØD		Cylinder chamfer A
Over	Up to	H	B	Over	Up to	minimum
mm	mm	mm	mm	mm	mm	mm
55	250	15	1,5	75	250	3
250	800	20	2	250	800	4,5
800	1 500	30	3	800	1 500	6
1 500	2 480	40	4	1 500	2 540	7,5

## Cylinder and housing surface finishing

A roughness of Ra from 0,2 to 0,6 µm is recommended for the shaft in standard applications, while in case of high speeds, a finishing to Ra from 0,2 to 0,4 µm is recommended. Plunge grinding is required. For the housing bore a finish turning is sufficient.

## Cylinder hardness

Up to 15 m/s	Over 15 m/s
40 HRC	50 HRC and above

[skf.com](https://skf.com) | [skf.com/seals](https://skf.com/seals)

© SKF and TENUITE are registered trademarks of the SKF Group

© SKF Group 2024

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication, but no liability can be accepted for any loss or damage whether direct, indirect, or consequential arising out of the use of the information contained herein. All data mentioned in this publication are given as an indication. SKF Seals Application Engineering / TENUITE Technical Department reserves the right to change and improve its products according to application specifications and test results.