

SKF Food Grade Lubricants

# Food grade dry film lubricant

# LDTS 1

SKF Dry Film Lubricant LDTS 1 has been specially developed for automatic lubrication of plastic flat top chain conveyors in the beverage processing industry. The lubricant consists of synthetic oil and is doped with PTFE solid lubricant.

After storage a separation of the ingredients could be observed in the container, this is normal. Shaking the product will bring it to a normal status. Automatic lubrication systems must have an stirring mechanism.

Designation

LDTS 1/5

- Cost savings by eliminating high volume of water and soluble lubricant
- Improved operator safety by reducing slip hazards
- Quality of packaging is maintained by elimination of moisture
- Reduced risk of product contamination by minimising microbiological growth
- Enhanced line efficiency by avoiding replacement costs and associated unplanned production stops
- Reduced cleaning costs
- NSF H1 registered

## **Typical applications**

Available pack sizes

Packsize

5 l can

• Conveyors in bottling lines using PET, carton, glass or can packages.







LDTS 1		
Composition Mineral oils, hydrocarbons,	Density 25 °C (77 °F)	ca. 841 kg/m <sup>3</sup>
additives, PTFE	Flash point of the preparation	ca. 100 °C ( <i>210 °F</i> )
White	Flash point after evaporation	
–5 to +60 °C (25 to 140 °F)	of the solvent	>170 °C (340 °F)
ca. 28 mm²/s	NSF Reg. No.	139739
<0 °C	Shelf life	2 years
	Mineral oils, hydrocarbons, additives, PTFE White -5 to +60 °C ( <i>25 to 140 °F</i> ) ca. 28 mm <sup>2</sup> /s	Mineral oils, hydrocarbons, additives, PTFEDensity 25 °C (77 °F)WhiteFlash point of the preparation-5 to +60 °C (25 to 140 °F) ca. 28 mm²/sNSF Reg. No.

These characteristics represent typical values.

100 100 100	Inter-section and	
Autori conditioni	Select on application condi-	bons
to and the second second	transmission .	ering tase (annutic) (annutic) (annutic) (annutic)
obert Long Marine Mary Long Marine Long Ma	Fire States 2 set Service 2 set Service 3 set Ser	
		C Bigli Jacof S Bigli Jacof S Jacobi Bagana ord C Dissertion (CC) Bigli Bagana of C C Bigli Dissertion (CC) Dissertion (CC)

Advanced tool for grease selection and relubrication calculation

# LubeSelect for SKF greases

Selecting a suitable grease for a particular bearing is a crucial step if the bearing is to meet design expectations in its application. SKF knowledge about bearing lubrication has been encapsulated into a computer program that can be consulted at skf.com/lubeselect

LubeSelect for SKF greases provides you a user friendly tool to select the right grease and suggest frequency and quantity, while taking into account the particular conditions of your application. General guidelines for typical greases for different applications are also available.



Scan or click the QR code, or go to skf.com/lubeselect

### skf.com | skf.com/lubrication | skf.com/mapro

® SKF is a registered trademark of the SKF Group.

#### © SKF Group 2022

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

#### PUB MP/P8 12041/3 EN · December 2022

Certain image(s) used under license from Shutterstock.com.